

Search within category **GO**

**BUY NOW**

**DESIGN / INSTALL**



**PLT2I-C186**

Pan-Ty® cable tie, metal detectable polypropylene, intermediate cross section, 8.0" (203mm) length, dark blue.

Specs	Packaging Details	Tools	Documents	★ Add to Favorites	🛒 Add to BOM
Material	Metal Impregnated Polypropylene				
Color	Dark Blue				
Cross Section	Intermediate				
Locking Style	Locking				
Min. Loop Tensile Strength Lbs. (N)	18 (80)				
Continuous Use Temperature Range	-76°F (-60°C) - 239°F (115°C)				
Plenum-Rated	No				
Tool	GTS-E, GS2B, PTS, PPTS, STS2				
Length In (mm)	8.0 (203)				
Thickness In (mm)	0.047 (1.2)				
Width In (mm)	0.135 (3.4)				
Bundle Diameter Range In. (mm)	0.13 (3.3) - 2.00 (51)				
CE Compliant	No				
CSA Certified	No				
Mil. Std. Part Number	—				
UL 62275 Compliant (Type 1, 11)	No				
UL 62275 Compliant (Type 2, 21)	No				
UL Listed (File #E56854)	No				
UL Recognized (File #E56854)	No				
Application	Metal Detectable				
Environment	Indoor				
Installation Temperature	-4°F (-20°C) - 32°F (0°C)				
Min. Loop Tensile Strength (N)	80				
Operating Temperature	-76°F (-60°C) - 185°F (85°C)				
Part Features	One-piece locking wedge for consistent performance and reliability. Low thread force and high loop tensile strength.				
RoHS Compliant Status	Compliant				
Min. Order Qty.	100.0000				