



DIRECTION OF WIND: FACTORY OPTION  
 WIRE DIA: 0.012 in  
 OUTSIDE DIA: 0.079 ± .003 in  
 TO WORK IN HOLE: 0.084 in MAX  
 INSIDE DIA: DIA: 0.055 in REF  
 TO WORK OVER ROD: 0.050 in MIN  
 FREE LENGTH: 0.197 ± .016 in  
 TOTAL COILS: 8.48 REF  
 SPRING RATE: 13.311 ± 1.331 lbs/in  
 SOLID HEIGHT: 0.114 in +5%/NO LOWER LIMITS  
 LOAD AT SOLID HEIGHT: 1.11 lbs REF  
 END TYPE: SQUARED, NOT GROUND

Units: inch, lbs

<b>PROPRIETARY AND CONFIDENTIAL</b>		NAME	DATE	<b>COMPRESSION SPRING-INSTRUMENT SERIES</b>	
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF LEE SPRING COMPANY LLC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF LEE SPRING IS PROHIBITED.		DRAWN	E YEE	01/1/2017	LEE SPRING 140 58TH ST Ste. 3C, BROOKLYN, NY 11220 Ph: 888-SPRINGS FAX: 888-426-6655 E: SALES@LEESPRING.COM
		CHECKED	S BECK	08/31/2023	
		ENG APPR.			
		MFG APPR.			
		Q.A.			
MATERIAL: STAINLESS STEEL TYPE 302 / 304 PER ASTM A313 OR EQUIVALENT INTERNATIONAL STANDARD				SIZE	DWG. NO.
FINISH: PASSIVATED PER ASTM A967				A	CIM030AA 02S
				9.5 : 1	REV NR