

FEATURES

- Flexible 1/2 in coolant hose kit
- Contains 2 x 5.5-in hoses for a total length of 11 in
- Made from durable, heat-resistant polyoxymethylene
- Internal diameter of 12.7 mm
- External diameter of 25 mm
- Minimum diameter of 80 mm at full bend
- Maximum pressure (liquid / air) of 60 psi
- Blue colour (Pantone 3025C)

RS PRO 1/2in Hose Kit

RS Stock No.: 623-5094



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Machine Tool Coolant Systems



Product Description

This 1/2 in flexible coolant hose kit from RS PRO contains a pair of 5.5 in hoses for a total length of 11 inches. It's useful for preventing overheating in industrial and manufacturing environments. The kit features a 1/2 in hose made from a durable and heat-resistant polyoxymethylene material. It has an internal diameter of 12.7 mm and an external diameter of 25 mm. At full bend, this flexible hose has a minimum diameter of 85 mm. The coolant hose operates at a maximum pressure of up to 60 pounds per square inch (psi) for both liquid and air.

General Specifications

Туре	Hose Kit
Systems	1/2in
Material	Acetal Copolymer
Kit Contents	5 1/2 in Hose (x2)

Mechanical Specifications

Total Length	11in
Size	1/2in
Internal Diameter	12.7mm
External Diameter	25mm
Flow	30m³/hour
Minimum Diameter Of Full Bend	85mm

Operation Environment Specifications

Maximum Pressure Liquid/Air	60Psi
-----------------------------	-------

Machine Tool Coolant Systems



Approvals

Compliance/Certifications

ANSI/ESD S20.20:2014 and BS EN 61340-5-1:2007



