

AH49H

General Description

The AH49H is a small, versatile linear Hall-effect device that is operated by the magnetic field from a permanent magnet or an electromagnet. The output voltage is set by the supply voltage and varies in proportion to the strength of the magnetic field.

The integrated circuitry features low noise output, which makes it unnecessary to use external filtering components. It also includes precision resistors to provide increased temperature stability and accuracy. The operating temperature range of these linear Hall sensors is -40°C to 105°C, appropriate for commercial, consumer, and industrial environments.

The AH49H is available in standard TO-92S-3 and SOT-23-3 packages.

Features

- Miniature Construction
- Power Consumption of 2mA at V_{CC}=3.3V for Energy Efficiency
- Single Current Sourcing Output
- Linear Output for Circuit Design Flexibility
- Low Noise Output Virtually Eliminates the Need for Filtering
- A Stable and Accurate Output
- Temperature Range: -40°C to 105°C
- Responds to Either Positive or Negative Gauss
- The Maximum Instantaneous Supply Voltage Up to 50V
- High ESD Rating: 6000V (Human Body Model)
 400V (Machine Model)

Application

- Current Sensing
- Motor Control
- Position Sensing
- Magnetic Code Reading
- Rotary Encoder
- Ferrous Metal Detector
- Vibration Sensing
- Liquid Level Sensing
- Weight Sensing




Figure 1. Package Types of AH49H



AH49H

Pin Configuration




Figure 2. Pin Configuration of AH49H

Pin Description

Pin Number		Din Nome	Function		
TO-92S-3	SOT-23-3	Pin Name	Function		
1	1	VCC	Power supply pin		
2	3	GND	Ground pin		
3	2	OUT	Output pin		



AH49H

Functional Block Diagram





Figure 3. Functional Block Diagram of AH49H

Ordering Information



Package	Temperature Range	Part Number	Marking ID	Packing Type	
TO-92S-3	40 to 1059C	AH49HZ3-G1	49HG	Bulk	
SOT-23-3	-40 to 105°C	AH49HNTR-G1	GT7	Tape & Reel	

BCD Semiconductor's Pb-free products, as designated with "G1" in the part number, are RoHS compliant and green.



AH49H

Absolute Maximum Ratings (Note 1)

Parameter		Symbol	Value	Unit	
Supply Voltage		V_{CC}	10	V	
Instantaneous Supply Voltage		V _{CC_INST}	50	V	
Power Dissipation	TO-92S-3	D	400	mW	
	SOT-23-3	P_{D}	230		
Ambient Temperature		T_{A}	-40 to 125	°C	
Storage Temperature		T_{STG}	-50 to 150	°C	
ESD (Human Body Model)			6000	V	
ESD (Machine Mode)			400	V	

Note 1: Stresses greater than those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "Recommended Operating Conditions" is not implied. Exposure to "Absolute Maximum Ratings" for extended periods may affect device reliability.

Recommended Operating Conditions (T_A=25°C)

Parameter	Symbol	Min	Max	Unit
Supply Voltage	V_{CC}	3	8	V
Operating Temperature	T_{OP}	-40	105	°C



AH49H

Electrical Characteristics

V_{CC}=3.3V, T_A=25°C, unless otherwise specified.

Parameter	Symbol	Conditions	Min	Тур	Max	Unit
Supply Current	I_{CC}		1.2	2	3.2	mA
Quiescent Output Voltage	V_{NULL}	B=0 (Gauss)	1.45	1.7	1.85	V
Output Voltage Sensitivity	$V_{\rm SEN}$	B=±600 (Gauss)		0.33		mV/Gauss
Output Voltage Span	V _{OUT S}			0.85 to 2.6		V
Output Resistor	R_{OUT}		30	50	70	Ω
Linear Magnetic Range	В			±3000		Gauss
Output Noise		Bandwidth=10Hz to 10kHz		90		μV

Transferring Characteristics (V_{CC}=3.3V)

When there is no outside magnetic field (B=0Gauss), the quiescent output voltage is one-half the supply voltage in general.

For TO-92S-3 package, if a south magnetic pole approaches the front face (the side with marking ID) of the Hall effect sensor, the circuit will drive the output voltage higher. In contrary, a north magnetic pole will drive the output voltage lower. The variations of voltage level up or down are symmetrical. Because the SOT-23-3 is reversed packaging with TO-92S-3, so the magnetic performance is also reversed. Therefore, if the reversed magnetic pole approaches the front face, the output is the same as TO-92S-3 package. Greatest magnetic sensitivity is obtained with a supply voltage of 8V, but at the cost of increased supply current and a slight loss of output symmetry. So, it is not

For TO-92S-3

recommended to work in such condition unless the output voltage magnitude is a main issue. The output signal can be capacitively coupled to a next-level amplifier for further amplifying if the changing frequency of the magnetic field is high.




Figure 4. Transferring Characteristic of AH49H




For SOT-23-3

Figure 5. Magnetic Characteristic of AH49H



AH49H

Typical Performance Characteristics







Figure 6. Supply Current vs. Supply Voltage

Figure 7. Output Voltage vs. Magnetic Field






Figure 8. Output Voltage vs. Supply Voltage

Figure 9. Output Voltage vs. Ambient Temperature



AH49H

Typical Performance Characteristics (Continued)




Figure 10. Power Dissipation vs. Ambient Temperature





AH49H


Unit: mm(inch)

Mechanical Dimensions

TO-92S-3










AH49H

Mechanical Dimensions (Continued)

SOT-23-3 Unit: mm(inch)







BCD Semiconductor Manufacturing Limited

http://www.bcdsemi.com

IMPORTANT NOTICE

BCD Semiconductor Manufacturing Limited reserves the right to make changes without further notice to any products or specifications herein. BCD Semiconductor Manufacturing Limited does not assume any responsibility for use of any its products for any particular purpose, nor does BCD Semiconductor Manufacturing Limited assume any liability arising out of the application or use of any its products or circuits. BCD Semiconductor Manufacturing Limited does not convey any license under its patent rights or other rights nor the rights of others.

MAIN SITE

- Headquarter

BCD (Shanghai) Micro-electronics Limited

No. 1600, Zi Xing Road, Shanghai ZiZhu Science-based Industrial Park, 200241, P. R.C. Tel: +86-021-2416-2266, Fax: +86-021-2416-2277

REGIONAL SALES OFFICE

Shenzhen Office

Shanghai SIM-BCD Semiconductor Manufacturing Co., Ltd., Shenzhen Office Unit A Room 1203,Skyworth Bldg., Gaoxin Ave.1.S., Nanshan District Shenzhen 518057, China

Tel: +86-0755-8660-4900 Fax: +86-0755-8660-4958

Taiwan Office (Hsinchu) BCD Semiconductor (Taiwan) Company Limited 8F, No.176, Sec. 2, Gong-Dao 5th Road, East District HsinChu City 300, Taiwan, R.O.C Tel: +886-3-5160181, Fax: +886-3-5160181

- Wafer Fab

Shanghai SIM-BCD Semiconductor Manufacturing Co., Ltd.

800 Yishan Road, Shanghai 200233, China Tel: +021-6485-1491, Fax: +86-021-5450-0008

Taiwan Office (Taipei)

BCD Semiconductor (Taiwan) Company Limited 3F, No.17, Lane 171, Sec. 2, Jiu-Zong Rd., Nei-Hu Dist., Taipei(114), Taiwan, R.O.C Tel: +886-2-2656 2808

Fax: +886-2-2656-2806/26562950

BCD Semiconductor Corp. 48460 Kato Road, Fremont, CA 94538, USA Tel: +1-510-668-1950 Fax: +1-510-668-1990

BCD Semiconductor Limited Korea office. Room 101-1112, Digital-Empire II, 486 Sin-dong, Yeongtong-Gu, Suwon-city, Gyeonggi-do, Korea Tel: +82-31-695-8430

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

AH49HNTR-G1 AH49HZ3-G1