



NOTES:

- ROHS COMPLIANT
- 2. HEADER: DAP (DIALLYL PHTHALATE) WITH FLAMMABILITY RATING UL 94V-0 OR BETTER.
- 3. STORAGE TEMPERATURE: -20°C TO +125°C
- 4. COMPLIANCE TO J-STD:
 - A. J-STD-002: SOLDERABILITY AT 245°C REFLOW PROFILE
 - B. J-STD-020: LEVEL 1, NO MOISTURE SENSITIVE
 - C. J-STD-075: R7, 245°C MAXIMUM THROUGH REFLOW SOLDER
- 5. TO ORDER TAPE & REEL PACKAGING ADD A "T" SUFFIX TO THE PART NUMBER(i.e H2009FNL BECOMES H2009FNLT).








FINAL OUTLINE

@ Copyright, 2014. Pulse Electronics Corp. All rights reserved. Pulse confidential & proprietary. (06/17/14)

MDL,DUAL,100P,1:1,SM,TU H2009FNL-10 PS-2745.001-A 1 OF 3 H2009FNL	PRODUCT DESCRIPTION	TLA DRAWING	PS DRAWING	SHEET	PART NO.	DATASHEET REV.
	MDL,DUAL,100P,1:1,SM,TU		PS-2745.001-A	1 11-5	H2009FNL	A







ELECTRICAL CHARACTERISTICS AT +25°C UNLESS OTHER SPECIFIED MEETS IEEE 802.3 SPECIFICATION

PARAMETER	SPECIFICATIONS				
OPERATING TEMPERATURE	0°C - 70 °C				
TURNS RATIO	1.00 ± 2%				
POLARITY		PER SCHEMATIC			
	100 KHz	100 KHz 1-100 MHz			
INSERTION LOSS	-1.2 dB MAX	-0.2-0.002*f^1.4 dB MAX			
RETURN LOSS	.1-30 MHz	30-60 MHz	60-80 MHz		
$(Z OUT = 100 OHM \pm 15\%)$	-16 dB MIN	-10+20*LOG ₁₀ (f/60 MHz) dB MIN	-10 dB MIN		
INDUCTANCE (OCL) (MEDIA SIDE ACROSS PINS 13-15, 16-18, 19-21, 22-24), 0°C-70°C	350 uH MIN (MEASURED AT 100 KHz, 100 mVRMS)				
CDOCCTALIK AD IACENT	1 MHz	10-100 MHz			
CROSSTALK, ADJACENT CHANNELS	-50 dB MIN	-55+22*LOG ₁₀ (f/10) dB MIN			
DIFFERENTIAL TO COMMON	2 MHz	2 MHz 30-200 MHz			
MODE REJECTION	-50 dB MIN	-43+22*LOG ₁₀ (f/30) dB MIN			
DC RESISTANCE, 1/2 WINDING	.65 OHMS MAX (MEASURED AT PINS 24-23/23-22; 21-20/20-19; 18-17/17-16; 15-14/14-13)				
DC RESISTANCE IMBALANCE	PIN(21-20) - PIN(18-17) -	- PIN (23-22) = ±.06 - PIN (20-19) = ±.06 - PIN (17-16) = ±.06 - PIN (14-13) = ±.06	5 OHMS MAX		
INPUT — OUTPUT ISOLATION	1500	VRMS MIN @ 60 SE	CONDS		


NOTE: f IS FREQUENCY IN MHz.


@ Copyright, 2014. Pulse Electronics Corp. All rights reserved. Pulse confidential & proprietary. (06/17/14)

PRODUCT DESCRIPTION	TLA DRAWING	PS DRAWING	SHEET	PART NO.	DATASHEET REV.
MDL,DUAL,100P,1:1,SM,TU	H2009FNL-10	PS-2745.001-A	2 OF 3	H2009FNL	A











SUGGESTED LAND PATTERN





DIMENSIONS ARE IN INCHES [MILLIMETERS] WITH THE FOLLOWING TOLERANCES: [MILLIMETERS] ARE FOR REFERENCE ONLY. .XX= \pm .01 [\pm 0.25] .XXX= \pm .005 [\pm 0.13]

© Copyright, 2014. Pulse Electronics Corp. All rights reserved. Pulse confidential & proprietary. (06/17/14)

PRODUCT DESCRIPTION	TLA DRAWING	PS DRAWING	SHEET	PART NO.	DATASHEET REV.
MDL,DUAL,100P,1:1,SM,TU	H2009FNL-10	PS-2745.001-A	3 OF 3	H2009FNL	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

H2009FNLT H2009FNL