





- Material: UL approved Nylon 66, 94V-2
- Color: Black
- Cust assembly cost, prolongs cords life. Used extensively for protecting cords of computer, apparatus...etc.



	Cross Section Shape	Item No.	Wires Accommodate		Mounting Hole		Part Length	Available Thickness	Packing
			UL Wire	Size	A	B	D	F	
	Flat	<input type="checkbox"/> SR-F21	SPT-1#18	2.3x4.5 2.8x5.3	9.5	8.7	10.3	0.5 ~ 1.6	100 pcs / Bag
		<input type="checkbox"/> SR-F23	SPT-1#18	2.3x4.5 2.8x5.3	9.5	8.7	10.3	1.8 ~ 3.2	
		<input type="checkbox"/> SR-F31	SPT-1#18	3.0x5.6	11.2	9.9	10.3	1.0 ~ 1.6	
		<input type="checkbox"/> SR-F32	SPT-1#18	3.0x5.6	11.0	9.9	10.3	1.9 ~ 2.5	
		<input type="checkbox"/> SR-F41	SPT-2#18	3.0x7.1 3.8x7.6	12.7	11.8	10.3	0.5 ~ 1.6	
		<input type="checkbox"/> SR-F42	SPT-2#18	3.0x7.1 3.8x7.6	12.7	11.8	10.3	1.8 ~ 2.5	
		<input type="checkbox"/> SR-F51	SPT-3#18	5.0x10.4	14.3	12.9	15.2	0.5 ~ 1.6	
		<input type="checkbox"/> SR-F53	SPT-3#18	5.0x10.4	14.3	12.9	15.2	1.8 ~ 3.5	
		<input type="checkbox"/> SR-F83	Alt Condition Wire 3C 2mm2	6.0x13.0	21.6	21.3	20.4	20.0 ~ 3.4	
	Round	<input type="checkbox"/> SR-5R1	SVI, SVT 3C#18	6.2Φ~7.4Φ	12.8	11.5	11.0	0.5 ~ 1.6	
		<input type="checkbox"/> SR-5R2	SVI, SVT 3C#18	6.2Φ~7.4Φ	13.0	11.5	11.0	1.8 ~ 2.5	
		<input type="checkbox"/> SR-6W2	SJT 3C#18	7.6Φ	12.7	11.8	11.0	1.8 ~ 2.3	
		<input type="checkbox"/> SR-6P1	SJT 3C#18	7.4Φ~8.2Φ	15.9	14.0	14.8	0.5 ~ 1.6	
		<input type="checkbox"/> SR-6P3	SJT 3C#18	7.4Φ~8.2Φ	15.9	14.0	14.8	1.9 ~ 3.2	
		<input type="checkbox"/> SR-6R1	SJ, SJT 3C#16	8.2Φ~9.2Φ	15.9	14.0	14.8	0.5 ~ 1.6	
		<input type="checkbox"/> SR-6R3	SJ, SJT 3C#16	8.2Φ~9.2Φ	15.9	14.0	14.8	1.9 ~ 3.2	
		<input type="checkbox"/> SR-7R1	SJT 3C#14	9.2Φ~10.5Φ 11Φ	19.9	17.0	19.0	0.5 ~ 1.6	
		<input type="checkbox"/> SR-7R3	SJT 3C#14	9.2Φ~10.5Φ 11Φ	19.7	17.0	19.0	1.9 ~ 3.2	
		<input type="checkbox"/> SR-8R3	SJT 3C#12	12.0Φ~15.2Φ	21.6	21.3	20.6	1.9 ~ 3.2	
		<input type="checkbox"/> SR-9R1	#18 20~30 pcs	11.0Φ~15.0Φ	15.0	19.0	17.5	0.5 ~ 1.6	
	<input type="checkbox"/> SR-9R7	SJT 3C#10	15.2Φ~16.3Φ 17.5Φ	28.0/30.2	25.5	25.2	1.0 ~ 3.2		