

Fuseholders

MAXI™ Fuse In-Line Fuseholder

The In-Line Fuseholder provides an efficient, simple installation method for MAXI™ Fuse applications.

Specifications

Terminal: Copper Alloy

Body: Black Thermoplastic (UL94HB)

Cover: Translucent Thermoplastic

Ambient Temp.: -10°C to +80°C

Maximum number of fuseblocks tied together is two for all ratings, up to and including 50A.



Part Number	Description
152001	Fuseholder – Rated at 60A
152900	Cover
913-653	Ring tongue terminal for 2.5 – 6mm ² (12 – 10AWG) wire*
913-654	Ring tongue terminal for 5 – 10mm ² (10 – 8AWG) wire*
913-550	M5 x 8 Screw per DIN 7985-4.8

*It is recommended that cross linked polyethylene (GLX) insulated wire be used, as described in SAE J1128 (Type, FLY in DIN 76722) or equivalent.

MAXI™ Fuse In-Line Fuseholder with Protective Cap

Supplied with two 6" leads – 6 gauge wire for up to 60 amp MAXI Fuse applications, this In-Line Fuseholder also provides a protective cover for harsh under-the-hood environments. Mounting hole also permits easy bulkhead installation.

Part Number: MAH 1



ATO® Blade Fuse Splashproof In-Line Fuseholder

The Splashproof Fuseholder provides a protective cover to permit the use of ATO® Fuses in harsh environments.

Specifications

Body: Black Alcryn Thermoplastic

Cover: Black Alcryn Thermoplastic

Ambient Temp.: -10°C to +80°C

Part Number	Description
FHAC001	#16AWG (1.0mm ²) stranded black wire with terminals rated for 20A
FHAC002	#12 AWG (3.0mm ²) stranded orange wire with terminals rated for 30A

