




## Sockets

### PB 4



Product	PB 4
description	4 mm diameter test socket for measuring and testing printed boards during operation. The test socket may also be mounted on the printed board using a BZ 2.2 DIN7971 pan-head, self-tapping screw. Tin-plated brass through-hole 4 mm diameter socket.
operating instruction	BA406
article-no. / *colour	9735821xx <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  00 black         </div> <div style="text-align: center;">  01 red         </div> </div> <div style="text-align: right; border: 1px solid black; padding: 2px; margin-top: 5px;">Sn</div>
drawing	
technical data	
connection	solder connection
rated voltage <sup>(1)</sup>	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O <sup>(3)</sup>
rated current <sup>(1)</sup> (consider derating curve)	16 A
material socket	brass, tin plated
housing material	PC
temperature range acc. To IEC61010 <sup>(2)</sup>	-25 °C to +85 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	HB
standard	IEC 61010

4 mm system

- <sup>(1)</sup> for normal environmental conditions -5°C to +40°C  
<sup>(2)</sup> contact the manufacturer for applications at deviating temperature ranges  
<sup>(3)</sup> without rated measurement category, for other circuits that are not directly connected to mains  
stand: 17.09.2018