NUMBER	GS-12-265	Product Specification		FCI
TITLE	USB A TY	PE CONNECTOR	PAGE 1 of 7	REVISION J
			AUTHORIZED BY Allen Chang	DATE 06/11/08
			CLASSIFICATION UNRESTRIC	TED

1.0 GENERAL

This specification defines the performance, tests and quality requirements for the USB A TYPE connector. This document is composed of the following sections.

- 1. General
- 2. Scope
- 3. Applicable Documents
- 4. Requirements
 - ♦ Design and Construction
 - ♦ Material
 - ♦ Finish
- 5. Test Methods and Requirements
- 6. Test Plan
- 7. Applicable Part Number and Product Drawing

2.0 SCOPE

This specification is applicable to the termination characteristics of the USB A TYPE family of products which provides interconnection of computer peripherals.

3.0 APPLICABLE DOCUMENTS

- 3.1 Military Standards:
 - 3.1.1 MIL-STD-202F: Test methods for electronic and electrical component parts.
 - 3.1.2 MIL-STD-1344A: Test methods for electrical connectors.
 - 3.2 Industry Specification/Other Standards:
 - 3.2.1 UL-94: Tests for flammability of plastic materials.
 - 3.2.2 EIA 364: Electrical connector/socket test procedures including environmental classifications.
 - 3.2.3 USB: Universal Serial Bus Specification.

4.0 **REQUIREMENT**

4.1 Design and Construction:

Connectors shall be of the design construction and physical dimensions specified on the applicable product drawing and shall be capable of meeting the qualification test requirements specified herein.

4.2 Materials

- 4.2.1 Housing:
 - ♦ The insulators shall be rated flame retardant 94V-O in accordance with UL-94.
- 4.2.2 Terminal:
 - ♦ Copper Alloy.
- 4.2.3 Shell:
 - ♦ Copper Alloy.

4.3 Finish:

The finish for applicable components shall be specified on the applicable product drawing

- 4.3.1 Contact Area: Gold plating with Nickel under-plate.
- 4.3.2 Solder Tail Area: Tin/Lead plating with Nickel under-plate.
- 4.3.3 Shell: Tin/Lead plating or Nickel plating.

Copyright FCI

Form E-3334 Rev F

NUMBER	GS-12-265	Product Specification		FCI
TITLE	USB A TY	PE CONNECTOR	PAGE 2 of 7	REVISION
			AUTHORIZED BY Allen Chang	DATE 06/11/08
			CLASSIFICATION UNRESTRIC	TED

5.0 TEST METHODS AND REQUIREMENTS:

5.1Examination of product:

Item	Test Description	Test Methods	Requirement
5.1.1	Examination of product	EIA 364-18	1).Outward appearance shall be
	\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \		good without such injurious problem.
	Structure)	Shall be confirmed by using proper	Structure shall be meet the design and dimensional requirements of
		measuring instruments.	drawing.

5.2 Electrical Performance:

Item	Test Description	Test Methods	Requirement
5.2.1	Low Level Contact	EIA 364-23 (or MIL-STD-1344A,	1).Initial: 30 mΩ Maximum
	Resistance	Method 3002.1, Test Condition B)	2).After test: 40 m Ω Maximum
		Subject mated contacts assembled in	
		housing to 20mV maximum open	
		circuit at 100 mA maximum	
5.2.2	Insulation Resistance	EIA 364-21 (or MIL-STD-202F, Method	1).Initial: 1000 MΩ Minimum
		302, Test Condition B)	2).After test: 1000 M Ω Minimum
		Test between adjacent contacts of	
		mated and unmated connector	
		assemblies.	
5.2.3	Dielectric Withstanding	EIA 364-20 (or MIL-STD-202F, Method	500 V AC for one minute at sea level
	Voltage	301, Test Condition B)	
		Test between adjacent contacts of	1).No flashover or insulation
		mated and unmated connector	breakdown
		assemblies.	2).Leakage current: 0.5mA
			Maximum.
5.2.4	Contact Capacitance	EIA 364-30	2 pF Maximum per Contact
		Test between adjacent circuits of	
		unmated connector at 1 KHz.	
5.2.5	Contact Current Rating	EIA 364-70 Method B	1.5A at 250Vac minimum.
		When measured at an ambient	
		temperature of 25℃. With Power	
		applied to the contacts, the ΔT shall	
		not exceed + 30 $^\circ\!$	
		USB connector under test.	

Copyright FCI

Form E-3334 Rev F

NUMBER	GS-12-265	Product Specification		FCJ
TITLE	USB A TY	PE CONNECTOR	PAGE 3 of 7	REVISION J
			AUTHORIZED BY Allen Chang	DATE 06/11/08
			CLASSIFICATION UNRESTRIC	TED

5.3Mechanical Performance:

Item	Test Description	Test Methods	Requirement
5.3.1	Random Vibration	EIA 364-28 Test Condition V Test Letter A, (or MIL-STD-202F, Method 214, Test Condition 1, Test Letter A) Subject mated connectors to 5.35 G's rms. Fifteen minutes in each of three mutually perpendicular planes.	 No discontinuities of 1 μ sec or longer duration Shall meet visual requirement, show no physical damage. Shall meet requirements of additional tests as specified in TEST SEQUENCE in Section 6
5.3.2	Physical Shock	EIA 364-27 Test Condition H (or MIL-STD-202F, Method 214B) Subject mated connectors to 30G's half-sine shock pulses of 11ms duration. Three shocks in each direction applied along three mutually perpendicular planes, 18 total shock.	 No discontinuities of 1 μ sec or longer duration Shall meet visual requirement, show no physical damage. Shall meet requirements of additional tests as specified in TEST SEQUENCE in Section 6
5.3.3	Durability	EIA 364-09 Mate and unmate Connector assemblies for 1500cycles at maximum rated of 200 cycles per hour.	1).Shall meet visual requirement, show no physical damage. 2).Shall meet requirements of additional tests as specified in TEST SEQUENCE in Section 6
5.3.4	Connector Insertion Force	EIA 364-13 Shall be measured with TENSION GAUGE or TENSION TESTER. Measure force necessary to mate assemblies at maximum rate of 12.5mm (or 0.492") per minute.	1).Initial : 35 Newtons Maximum 2).After test: 35 Newtons Maximum
5.3.5	Connector Extraction Force	EIA 364-13 Shall be measured with TENSION GAUGE or TENSION TESTER. Measure force necessary to mate assemblies at maximum rate of 12.5mm (or 0.492") per minute.	1).Initial : 10 Newtons Minimum 2).After test: 10 Newtons Minimum
5.3.6	Cable Pull-Out Force	EIA 364-38 Apply axial load of 40 Newtons to the cable for 1 minute. Shall be measured with TENSION GAUGE or TENSION TESTER.	1).Cable or connector shall be not dislodge from cable.

Form E-3334 Rev F

NUMBER	GS-12-265	Product Specification		FC
TITLE	USB A TY	PE CONNECTOR	PAGE 4 of 7	REVISION J
			AUTHORIZED BY Allen Chang	06/11/08
			CLASSIFICATION UNRESTRIC	CTED

5.4Environmental Performance:

Item	Test Description	Test Methods	Requirement
5.4.1	Thermal Shock	EIA 364-32, Test Condition I, (or MIL-202F, Method 107G Condition A.) Subject mated connectors to five cycles between −55°C to +85°C.	1).Shall meet visual requirement, show no physical damage. 2).Shall meet requirements of additional tests as specified in TEST SEQUENCE in Section 6
5.4.2	Humidity Tomporature Life	EIA 364-31, Test Condition A Method III, (or MIL-202F, Method 103B Test Condition B.) Subject mated connectors to 168 Hours (seven complete cycles) EIA 364-17 Test Condition 3 Method	1).Shall meet visual requirement, show no physical damage. 2).Shall meet requirements of additional tests as specified in TEST SEQUENCE in Section 6
5.4.3	Temperature Life	B, Subject mated connectors to temperature life at 85°C for 250hours	1).Shall meet visual requirement, show no physical damage. 2).Shall meet requirements of additional tests as specified in TEST SEQUENCE in Section 6
5.4.4	Solderability	EIA 364-52 After one hour steam aging. Or MIL-STD-202F, Method 208G. 245℃ for 5 seconds.	The surface of the portion to be soldered shall at least 95% covered with new solder coating, as specified in Category 2.

NUMBER	GS-12-265	Product Specification		FCI
TITLE	USB A TY	PE CONNECTOR	PAGE 5 of 7	REVISION J
			AUTHORIZED BY Allen Chang	DATE 06/11/08
<u>, </u>			CLASSIFICATION UNRESTRIC	CTED

6.0 TEST PLAN:

		TEST GROUP					
TEST ITEM	PARA.	Α	В	С	D	E	F
				TEST	SEQUENC	CE	
Examination of Product	5.1.1	1,11	1,5	1,9	1,4	1,3	
L/L Contact Resistance	5.2.1	4,8	2,4				
Insulation Resistance	5.2.2			3,7			
Dielectric Withstand Voltage	5.2.3			4,8			
Contact Capacitance	5.2.4			2			
Contact Current Rating	5.2.5				2		
Random Vibration	5.3.1	6					
Physical Shock	5.3.2	7					
Durability	5.3.3	5					
Insertion Force	5.3.4	2,9					
Extraction Force	5.3.5	3,10					
Cable Pull-Out Force	5.3.6					2	
Thermal Shock	5.4.1			5			
Humidity	5.4.2			6			
Temperature Life	5.4.3		3				
Solderability	5.4.4				3		
Sample Size		5	5	5	5	5	

NUMBER	GS-12-265	Product Specification		FC
TITLE	USB A TY	PE CONNECTOR	PAGE 6 of 7	REVISION J
			AUTHORIZED BY Allen Chang	06/11/08
			CLASSIFICATION UNRESTRIC	CTED

Note:

- a. Samples shall be prepare in accordance with applicable manufacture's instructions and shall be selected at random from current production.
- b. The numbers in the table indicate sequence in which tests are performed.
- c. Precondition samples with 10 cycles durability.
- d.All the tests shall be performed in the sequence, indicated by the number in the columns.

7.0 APPLICABLE PART NUMBER & PRODUCT DRAWING:

Part Number	Product Description	Drawing Number	Remark
10080773-XXXXXX	USB A Type Plug connector,	10080773	
	SMT Type(Dip Holddown Length 1.35mm) USB A Type Plug connector, SMT Type(Dip Holddown Length 2.5mm)	10083503	
	USB A Type Plug connector, SMT Type(Dip Holddown Length 1.80mm)	10082997	
	SWIT Type(DIPTIOIddOWIT Length 1.00min)		

Copyright FCI

Form E-3334 Rev F

NUMBER	GS-12-265	Product Specification		FC
TITLE	USB A TYPE CONNECTOR		PAGE 7 of 7	REVISION J
			AUTHORIZED BY Allen Chang	DATE 06/11/08
			CLASSIFICATION UNRESTRICTED	

Revision Record

Revision	Page	Description	ECR no	<u>Date</u>
Α	All	New released	T03-0398	9/16/2003
В	7	Add new P/N	T03-0478	10/28/2003
С	ALL	Add new P/N	T07-1118	07/23/2007
D	ALL	Add new P/N	T07- 1149	10/29/2007
E	ALL	Add new P/N	T07- 1178	12/05/2007
F	ALL	Add new P/N	T08-1019	02/04/2008
G	ALL	Remove p/n 10082141	T08-1020	02/05/2008
Н	ALL	Remove p/n 10034010 & 10033425	T08-1098	06/05/2008
J	ALL	Remove p/n 10034837	T08-1108	06/11/2008

Copyright FCI

Form E-3334 Rev F