


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	PACKAGE QTY	MAX BUNDLE DIAMETER	LENGTH "L" ±.3 [7]
MLT2H-LP	50	2" [51]	7.9" [201]
MLT2.7H-LP	50	2.7" [69]	10.2" [259]
MLT4H-LP	50	4" [102]	14.3" [362]
MLT6H-LP	50	6" [152]	20.5" [521]
MLT8H-LP	50	8" [203]	26.8" [679]
MLT10H-LP	50	10" [254]	33.0" [838]
MLT12H-Q	25	12" [304]	39.3" [998]
MLT14H-Q	25	14" [355]	45.5" [1156]
MLT2H-TL	250	2" [51]	7.9" [201]
MLT4H-TL	250	4" [102]	14.3" [362]



NOTES:

1. APPLICATION TOOLS - GS4MT, PPTMT, ST2MT, ST3MT, HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 450 LBS. (2000 NEWTONS) WHEN TESTED ON A 1.5" MANDREL.
3. BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:
 .XXX = ±.010 [.25] .XX = ±.02 [.5]
 .X = ±.03 [.8] ANGLES = ±2°
5. MATERIAL: 304 STAINLESS STEEL

FULLY ROUNDED
EDGES ALONG
STRAP BODY


SECTION A-A
SCALE 6:1

06A	2/12	MIM	RGRO
REV	DATE	BY	CHK

NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY

DESCRIPTION

TM



PANDUIT

TINLEY PARK, ILLIONS

METAL LOCKING TIE
HEAVY SERIES -304 STAINLESS STEEL
- CUSTOMER DRAWING -

DRAWN BY JAMB	CHK'D DPN	SCALE 2x	DRAWING NO. N41115BS_DC
------------------	--------------	-------------	----------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[MLT4H-LP](#) [MLT2.7H-LP](#) [MLT2H-LP](#) [MLT6H-LP](#) [MLT10H-LP](#) [MLT14H-Q](#) [MLT2H-TL](#) [MLT2LH-LP](#) [MLT4H-TL](#)
[MLT4LH-LP](#) [MLT6LH-LP](#) [MLT8H-LP](#) [MLT8LH-LP](#) [MLT12H-Q](#)