

PRODUCT DATASHEET

DP 1500 46W 840 IP65 GY

DAMP PROOF | Damp-proof luminaires, classic shape



Areas of application

- Industrial and storage facilities
- Car parks and underpasses
- Garages
- Workshops, assembly lines

Product benefits

- Low flicker $\leq 10\%$
- Evenly distributed light
- Energy savings of up to 60 % (compared to luminaires that use fluorescent lamps)
- Easy installation, no tools required for connection
- 5 years guarantee

Product features

- High luminous efficacy: up to 135 lm/W
- Beam angle: 110°



TECHNICAL DATA

Electrical data

Nominal wattage	46.00 W
Operating mode	Integrated LED driver
Nominal voltage	220...240 V
Nominal current	222 mA
Inrush current	12.7 A
Inrush current time T_{h50}	220 μ s
Power factor λ	> 0,90
Max. no. of lum. on circuit break. B16 A	26
Max. no. of lum. on circuit break. C10 A	23
Max. no. of lum. on circuit break. C16 A	38
Total harmonic distortion	< 20 %

Luminaire control gear data

Low flicker	Yes
-------------	-----


Photometrical data

Color temperature	4000 K
Luminous flux	6400 lm
Luminous efficacy	115 lm/W
Light color (designation)	Cool White
Standard deviation of color matching	4 sdc _m
Color rendering index Ra	> 80

Light technical data

Beam angle	110 °
------------	-------

Dimensions & weight



Length	1500.00 mm
Height	68.00 mm

Width	82.00 mm
Product weight	1690.000 g

Colors & materials

Body material	Polycarbonate (PC)
Product color	Gray
Housing color	Gray
Cover material	Polycarbonate (PC)
Light emitting surface material	Polycarbonate

Temperatures & operating conditions

Ambient temperature range	-25...+40 °C
---------------------------	--------------

Lifespan

Number of switching cycles	100000
Lifespan L70/B50 at 25 °C	70000 h
Lifespan L80/B10 at 25 °C	50000 h
Lifespan L90/B10 at 25 °C	34000 h

Additional product data

Mounting location	Ceiling / Wall
Low flicker	Yes
Note about the product	

Capabilities

Dimmable	No
Type of connection	Terminal, 3-pin
ErP LEDmod replaceable	Not replaceable
Ball shot safe	No


Certificates & standards

Protection class IK (shock resistance)	IK08
Glow Wire Test according to IEC 69	850 °C
Protection class	I
Type of protection	IP65
Standards	CE / CB / ENEC / TÜV SÜD / EAC / RoHS
Luminaire with limited surface temperature, class "D"	Yes





LDC typ cone



LDC typ polar

LOGISTICAL DATA

Temperature range at storage

-25...+80 °C

EQUIPMENT / ACCESSORIES

- Stainless steel clamps with safety screws included
- Mounting accessories included (suspension kit, theft protection kit)

DOWNLOAD DATA

DOWNLOAD DATA



User instruction
UI_DampProof_IP65_Gen2



Declarations of conformity
DP IP65 GY



IES file (IES)
DP 1500 46W 840 IP65 GY

DOWNLOAD DATA



LDT file (Eulumdat)
DP 1500 46W 840 IP65 GY



R3D file (Relux 3D Model)
DP 1500



M3D file (3D Model)
DP 1500

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075541207	Folding box 1	1,512 mm x 87 mm x 74 mm	1725.00 g	9.73 dm ³
4058075541214	Shipping box 6	1,532 mm x 191 mm x 245 mm	11581.00 g	71.69 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

– For Guarantee see www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.