



SPECIFICATION

VOLTAGE 240VAC
FREQUENCY 50/60Hz
CURRENT 32A @ 40 °C
OVERLOAD CURRENT 150% 1MIN. 200% 1SEC
TEMPERATURE -25 TO 85 °C
LEAKAGE CURRENT:-
AS PER IEC950 = 90mA @ 240V 50Hz
HUMIDITY 90% RH
VIBRATION 10-200Hz 1.8G
ELECTRIC STRENGTH 2500VAC/1min.
POWER LOSS (FULL LOAD) = 20W
TERMINALS M4 SCREW CROSS/SLOT 2 x 2.5mmsq
WEIGHT 1.6kg
BACK MOUNTING 4x M4
SIDE MOUNTING 2x M6

CONSTRUCTION

PERFORATED ALUMINIUM BODY FOR AIR COOLING,
ALL COMPONENTS PCB MOUNTED
INSULATING TERMINAL BOOTS SUPPLIED WITH
FILTER

ATTENUATION

COMMON MODE - 80dB AT 150kHz
DIFFERENTIAL MODE - 50dB AT 150kHz

RoHS
2002/95/EC

Compliant