# RICOH

# **R3114x SERIES**

## 0.8% LOW VOLTAGE DETECTOR

NO.EA-160-160226

#### **OUTLINE**

The R3114x series are CMOS-based voltage detector ICs with high detector threshold accuracy and ultra-low supply current, which can be operated at an extremely low voltage and is used for system reset as an example.

Each of these ICs consists of a voltage reference unit, a comparator, resistors for detector threshold setting, an output driver and a hysteresis circuit. The detector threshold is fixed with high accuracy internally and does not require any adjustment.

Two output types, Nch open drain type and CMOS type are available.

The R3114x series are operable at a lower voltage than that of the R3111x series, and can be driven by a single battery.

Three types of packages, SOT-23-5, SC-82AB, and DFN(PLP)1010-4 are available.

#### **FEATURES**

Supply Current	Τyp. 0.35μA (-Vdet=1.5V, Vdd=-Vdet+1V)
Operating Voltage Range	0.5V to 6.0V (Topt=25°C)
Detector Threshold Range	0.7V to 5.0V (0.1V steps)
	(For other voltages, please refer to MARK INFORMATIONS.)
Detector Threshold Accuracy	$\pm 0.8\%$ (-VDET $\geq 1.5$ V)
• Temperature-Drift Coefficient of Detector Threshold	Typ. ±30ppm/°C
Output Types	Nch Open Drain "L" and CMOS
Packages	DFN(PLP)1010-4, SC-82AB, SOT-23-5


#### **APPLICATIONS**

- CPU and Logic Circuit Reset
- Battery Checker
- Window Comparator
- · Wave Shaping Circuit
- · Battery Back-up Circuit
- Power Failure Detector

# **BLOCK DIAGRAMS**

#### Nch Open Drain Output (R3114xxx1A)

#### CMOS Output (R3114xxx1C)



#### **SELECTION GUIDE**

The package type, the detector threshold, the output type and the taping type for the ICs can be selected at the users' request.

Product Name	Package	Quantity per Reel	Pb Free	Halogen Free
R3114Kxx1*-TR	DFN(PLP)1010-4	10,000 pcs	Yes	Yes
R3114Qxx1*-TR-FE	SC-82AB	3,000 pcs	Yes	Yes
R3114Nxx1*-TR-FE	SOT-23-5	3,000 pcs	Yes	Yes


xx: The detector threshold can be designated in the range from 0.7V(07) to 5.0V(50) in 0.1V steps. (For other voltages, please refer to MARK INFORMATIONS.)

- \* : Designation of Output Type
  - (A) Nch Open Drain
  - (C) CMOS


## **PIN CONFIGURATIONS**


## • DFN(PLP)1010-4\*

Top View
4 3



• SOT-23-5





## **PIN DESCRIPTIONS**

## • DFN(PLP)1010-4\*

Pin No.	Symbol	Description
1	OUT	Output Pin ("L" at detection)
2	NC	No Connection
3	GND	Ground Pin
4	V <sub>DD</sub>	Input Pin

\*) Tab is GND level. (They are connected to the reverse side of this IC.)

The tab is better to be connected to the GND, but leaving it open is also acceptable.

#### • SOT-23-5

Pin No.	Symbol	Description
1	OUT	Output Pin ("L" at detection)
2	$V_{DD}$	Input Pin
3	GND	Ground Pin
4	NC	No Connection
5	NC	No Connection

#### • SC-82AB

Pin No.	Symbol	Description
1	OUT	Output Pin ("L" at detection)
2	$V_{DD}$	Input Pin
3	NC	No Connection
4	GND	Ground Pin

## **ABSOLUTE MAXIMUM RATINGS**

Symbol	Item	Rating	Unit
V <sub>DD</sub>	Supply Voltage	7.0	V
Vout	Output Voltage (Nch Open Drain Output)	Vss-0.3 to 7.0	V
<b>V</b> 001	Output Voltage (CMOS Output)	Vss-0.3 to VDD+0.3	V
Іоит	Output Current	20	mA
	Power Dissipation (SOT-23-5)*	420	
PD	Power Dissipation (SC-82AB)*	380	mW
	Power Dissipation (DFN(PLP)1010-4)*	400	
Topt	Operating Temperature Range	-40 to 85	°C
Tstg	Storage Temperature Range	–55 to 125	°C

<sup>\*)</sup> For Power Dissipation, please refer to PACKAGE INFORMATION.

#### **ABSOLUTE MAXIMUM RATINGS**

Electronic and mechanical stress momentarily exceeded absolute maximum ratings may cause the permanent damages and may degrade the life time and safety for both device and system using the device in the field.

The functional operation at or over these absolute maximum ratings is not assured.

#### RECOMMENDED OPERATING CONDITIONS (ELECTRICAL CHARACTERISTICS)

All of electronic equipment should be designed that the mounted semiconductor devices operate within the recommended operating conditions. The semiconductor devices cannot operate normally over the recommended operating conditions, even if when they are used over such conditions by momentary electronic noise or surge. And the semiconductor devices may receive serious damage when they continue to operate over the recommended operating conditions.

## **ELECTRICAL CHARACTERISTICS**

• R3114xxx1A/C values indicate −40°C ≤ Topt ≤ 85°C, unless otherwise noted. Topt=25°C

Symbol	Item	Conditions					Тур.	Max.	Unit	
		Topt=25	5°C	1.5V < -	$V_{\text{DET}} \leq 5.0 V$	-V <sub>DET</sub> × 0.992		-V <sub>DET</sub> ×1.008	V	
-V <sub>DET</sub>	Detector Threshold			0.7V ≤ -	$V_{\text{DET}} \leq 1.5 V$	-12		+12	mV	
- V DET	Detector Tilleshold		≤ Topt ≤	1.5V < -	$V_{\text{DET}} \leq 5.0 V$	-V <sub>DET</sub> × 0.985		-V <sub>DET</sub> × 1.015	V	
		85°C		0.7V ≤ -	$V_{\text{DET}} \leq 1.5 V$	-22.5		+22.5	mV	
V <sub>HYS</sub>	Detector Threshold Hysteresis				-V <sub>DET</sub> × 0.04		$\begin{array}{c} \text{-V}_{\text{DET}} \\ \times \ 0.07 \end{array}$	V		
				0.7V ≤ -	V <sub>DET</sub> < 1.6V			1.40		
		\/ \/	0.1\/	1.6V ≤ -\	V <sub>DET</sub> < 3.1V			1.50		
		V DD=-V	DET -0.1V	3.1V ≤ -\	V <sub>DET</sub> < 4.1V			1.60		
Iss	Supply Current			4.1V ≤ -\	$V_{\text{DET}} \leq 5.0 V$			1.70	^	
ISS	Supply Current			0.7V ≤ -\	V <sub>DET</sub> < 1.6V			1.20	μΑ	
		\/ \/		1.6V ≤ -\	V <sub>DET</sub> < 3.1V			1.20		
		V <sub>DD</sub> =-V <sub>DET</sub> +1.0V		3.1V ≤ -\	V <sub>DET</sub> < 4.1V			1.30	]	
				4.1V ≤ -\	$V_{\text{DET}} \leq 5.0 V$			1.40		
V <sub>DDH</sub>	Maximum Operating Voltage							6	V	
V <sub>DDL</sub>	Minimum Operating	Topt=25	5°C					0.50	٧	
VDDL	Voltage*1	-40°C :	$-40^{\circ}C \leq Topt \leq 85^{\circ}C$					0.55	V	
			$V_{DD}=0.55V, V_{DS}=0.05V$			7			μΑ	
			10 // / /prz / 1 1\/		V <sub>DD</sub> =0.6V V <sub>DS</sub> =0.5V	0.02				
		Nch	1.1V ≤ -V <sub>DET</sub>	$1.1V \le -V_{DET} < 1.6V$ $V_{DS}=1.0V$ $V_{DS}=0.5V$		0.40			A	
Іоит	Output Current (Driver Output Pin)		1.6V ≤ -V <sub>DET</sub> < 3.1V		V <sub>DD</sub> =1.5V V <sub>DS</sub> =0.5V	1.00			mA	
	(Briver Galpat Firi)		$3.1V \le -V_{DET} \le 5.0V$		V <sub>DD</sub> =3.0V V <sub>DS</sub> =0.5V	2.40				
		D 1 *2	0.7V ≤ -V <sub>DET</sub>	< 4.0V	V <sub>DD</sub> =4.5V V <sub>DS</sub> =-2.1V	0.65			1	
		Pch*2	4.0V ≤ -V <sub>DET</sub>	$4.0V \le -V_{DET} \le 5.0V$ $V_{DS}=-2.1V$ $V_{DS}=-2.1V$		0.90			mA	
ILEAK	Nch Driver Leakage Current*3	V <sub>DD</sub> =6.0V, V <sub>DS</sub> =7.0V						80	nA	
Δ-V <sub>DET</sub> / ΔTopt	Detector Threshold Temperature Coefficient						±30	-	ppm /°C	
<b>t</b> PLH	Output Delay Time	V <sub>DD</sub> =0.5	55V to -V <sub>DET</sub> +2	.0V or 6.0	V		40		μS	


All of unit are tested and specified under load conditions such that Topt=25°C except for Detector Threshold Temperature Coefficient.

<sup>\*1:</sup> Minimum operating voltage means the value of input voltage when output voltage maintains 0.1V or less. (In case of Nch Open Drain Output type, the output pin is pulled up with a resistance of  $470k\Omega$  to 5.0V)

<sup>\*2:</sup> In case of CMOS type

<sup>\*3:</sup> In case of Nch Open Drain type

#### **TIMING CHART**



#### **DEFINITION OF OUTPUT DELAY TIME**


Output Delay Time (tplh) is defined as follows:


1. In the case of Nch Open Drain Output:

Under the condition of the output pin (OUT) is pulled up through a resistor of  $470k\Omega$  to 5V, the time interval between the rising edge of V<sub>DD</sub> pulse from 0.55V to (-V<sub>DET</sub>)+2.0V or the time interval of 6.0V pulse voltage is supplied, the becoming of the output voltage to 2.5V.

2. In the case of CMOS Output:

The time interval between the rising edge of  $V_{DD}$  pulse from 0.55V to  $(-V_{DET})+2.0V$  or the time interval of 6.0V pulse voltage is supplied, the becoming of the output voltage to  $((-V_{DET})+2.0V)/2$  or 3.0V.





## **ELECTRICAL CHARACTERISTICS BY DETECTOR THRESHOLD**

#### • R3114x071A/C to R3114x501A/C

Bold values are checked and guaranteed by design engineering at −40°C ≤ Topt ≤ 85°C, unless otherwise noted.

Topt=25°C

	Detector Threshold1				Detector Threshold Supply Current1			Supply Current1   Supply Current		Current2	Мах. Ор.	Min. Op.	
Part											Voltage	Voltage	
Number	<b>-V</b> DE	T1 <b>[V]</b>	-VDE	г2 <b>[V]</b>	VHY	s [V]	ISS1	[µA]	ISS2	[µA]	VDDH [V]	VDDL [V]	
	Min.	Max.	Min.	Max.	Min.	Max.	Cond.	Max.	Cond.	Max.	Max.	Max.	
R3114x071A/C	0.6880	0.7120	0.6775	0.7225	0.028	0.049							
R3114x081A/C	0.7880	0.8120	0.7775	0.8225	0.032	0.056							
R3114x091A/C	0.8880	0.9120	0.8775	0.9225	0.036	0.063							
R3114x101A/C	0.9880	1.0120	0.9775	1.0225	0.040	0.070							
R3114x111A/C	1.0880	1.1120	1.0775	1.1225	0.044	0.077		1.400					
R3114x121A/C	1.1880	1.2120	1.1775	1.2225	0.048	0.084							
R3114x131A/C	1.2880	1.3120	1.2775	1.3225	0.052	0.091							
R3114x141A/C	1.3880	1.4120	1.3775	1.4225	0.056	0.098							
R3114x151A/C	1.4880	1.5120	1.4775	1.5225	0.060	0.105							
R3114x161A/C	1.5872	1.6128	1.5760	1.6240	0.064	0.112							
R3114x171A/C	1.6864	1.7136	1.6745	1.7255	0.068	0.119							
R3114x181A/C	1.7856	1.8144	1.7730	1.8270	0.072	0.126				1.200			
R3114x191A/C	1.8848	1.9152	1.8715	1.9285	0.076	0.133				1.200			
R3114x201A/C	1.9840	2.0160	1.9700	2.0300	0.080	0.140							
R3114x211A/C	2.0832	2.1168	2.0685	2.1315	0.084	0.147							
R3114x221A/C	2.1824	2.2176	2.1670	2.2330	0.088	0.154							
R3114x231A/C	2.2816	2.3184	2.2655	2.3345	0.092	0.161		1.500					
R3114x241A/C	2.3808	2.4192	2.3640	2.4360	0.096	0.168							
R3114x251A/C	2.4800	2.5200	2.4625	2.5375	0.100	0.175						0.50	
R3114x261A/C	2.5792	2.6208	2.5610	2.6390	0.104	0.182			VDD= -VDET +1.0V	-VDET	6	0.50	
R3114x271A/C	2.6784	2.7216	2.6595	2.7405	0.108	0.189	V <sub>DD</sub> =						
R3114x281A/C	2.7776	2.8224	2.7580	2.8420	0.112	0.196	-VDD=					0.55	
R3114x291A/C	2.8768	2.9232	2.8565	2.9435	0.116	0.203	-0.1V				U	0.00	
R3114x301A/C	2.9760	3.0240	2.9550	3.0450	0.120	0.210	-0.10				-		
R3114x311A/C	3.0752	3.1248	3.0535	3.1465	0.124	0.217						*Note1	
R3114x321A/C	3.1744	3.2256	3.1520	3.2480	0.128	0.224							
R3114x331A/C	3.2736	3.3264	3.2505	3.3495	0.132	0.231							
R3114x341A/C	3.3728	3.4272	3.3490	3.4510	0.136	0.238							
R3114x351A/C	3.4720	3.5280	3.4475	3.5525	0.140	0.245		1.600		1.300			
R3114x361A/C	3.5712	3.6288	3.5460	3.6540	0.144	0.252		1.000		1.300			
R3114x371A/C	3.6704	3.7296	3.6445	3.7555	0.148	0.259							
R3114x381A/C	3.7696	3.8304	3.7430	3.8570	0.152	0.266							
R3114x391A/C	3.8688	3.9312	3.8415	3.9585	0.156	0.273							
R3114x401A/C	3.9680	4.0320	3.9400	4.0600	0.160	0.280							
R3114x411A/C	4.0672	4.1328	4.0385	4.1615	0.164	0.287							
R3114x421A/C	4.1664	4.2336	4.1370	4.2630	0.168	0.294							
R3114x431A/C	4.2656	4.3344	4.2355	4.3645	0.172	0.301							
R3114x441A/C	4.3648	4.4352	4.3340	4.4660	0.176	0.308							
R3114x451A/C	4.4640	4.5360	4.4325	4.5675	0.180	0.315		1.700		1.400			
R3114x461A/C	4.5632	4.6368	4.5310	4.6690	0.184	0.322		1.700		1.400			
R3114x471A/C	4.6624	4.7376	4.6295	4.7705	0.188	0.329							
R3114x481A/C	4.7616	4.8384	4.7280	4.8720	0.192	0.336							
R3114x491A/C	4.8608	4.9392	4.8265	4.9735	0.196	0.343							
R3114x501A/C	4.9600	5.0400	4.9250	5.0750	0.200	0.350					1		

<sup>\*</sup>Note1) V<sub>DD</sub> value when output voltage is equal or less than 0.1V. In the case of Nch Open Drain output type, the output pin is pulled up to 5.0V through 470kΩ resistor.

Curr		Nch Drive Curr	er Output ent2	Cur	er Output rent [mA]	Leakage	Driver Current	Detector Threshold Temperature Coefficient  △-VDET/△Topt [ppm/°C]	Output Tim	ne
	IOUT1 [μΑ] Cond. Min.		Min.	Cond.	Min.	Cond.	[nA] Max.		Cond.	
Conu.	Willi.	V <sub>DD</sub> = 0.6V V <sub>DS</sub> = 0.5V	0.020	Cona.	With.	Cona.	iviax.	Тур.	Cond.	Тур.
		V <sub>DD</sub> = 1.0V V <sub>DS</sub> = 0.5V	0.400							
V <sub>DD</sub> = 0.55V V <sub>DS</sub> = 0.05V	7	V <sub>DD</sub> = 1.5V V <sub>DS</sub> = 0.5V	1.000	V <sub>DD</sub> = 4.5V V <sub>DS</sub> = -2.1V	0.650	V <sub>DD</sub> = 6.0V V <sub>DS</sub> = 7.0V	80	±30	V <sub>DD</sub> = 0.55V ↓ -V <sub>DET</sub> +2.0V *Note2	40
0.03V		V <sub>DD</sub> = 3.0V V <sub>DS</sub> =	2.400			7.00				
		0.5V		V <sub>DD</sub> = 6.0V V <sub>DS</sub> = -2.1V	0.900				V <sub>DD</sub> = 0.55V ↓ 6.0V *Note2	

#### \*Note2) 1. In the case of CMOS output type:


When the voltage is forced from 0.55V to  $(-V_{DET})+2.0V$  or a 6.0V pulse voltage is added to  $V_{DD}$ , time interval that the output voltage reaches  $((-V_{DET})+2.0V)/2$  or a 3.0V.

2. In the case of Nch Open Drain output type:

The output pin is pulled up to 5.0V through  $470k\Omega$ , and when the voltage is forced from 0.55V to (-VDET)+2.0V or a 6.0V pulse voltage is added to VDD, time interval that the output voltage reaches 2.5V.


#### **OPERATION**

#### • Operation of R3114xxx1A



OUT pin should be pulled-up to VDD or an external voltage level.


#### Block Diagram (R3114xxx1A)




#### • Explanation of operation

- Step 1. The output voltage is equal to the pull-up voltage.
- Step 2. At Point "A", Vref ≥ VDD×(Rb+Rc)/(Ra+Rb+Rc) is true, as a result, the output of comparator is reversed from "L" to "H", therefore the output voltage becomes the GND level. The voltage level of Point A means a detector threshold voltage (-VDET).
- Step 3. When the supply voltage is lower than the minimum operating voltage, the operation of the output transistor becomes indefinite. The output voltage is equal to the pull-up voltage.
- Step 4. The output voltage is equal to the GND level.
- Step 5. At Point "B", Vref ≤ V<sub>DD</sub>×Rb/(Ra+Rb) is true, as a result, the output of comparator is reversed from "H" to "L", then the output voltage is equal to the pull-up voltage. The voltage level of Point B means a released voltage (+V<sub>DET</sub>).
- \*) The difference between a released voltage and a detector threshold voltage is a detector threshold hysteresis.

#### Operation of R3114xxx1C



Block Diagram (R3114xxx1C)





#### Explanation of operation

- Step 1. The output voltage is equal to the supply voltage (VDD).
- Step 2. At Point "A", Vref ≥ VDD×(Rb+Rc)/(Ra+Rb+Rc) is true, as a result, the output of comparator is reversed from "L" to "H", therefore the output voltage becomes the GND level. The voltage level of Point A means a detector threshold voltage (-VDET).
- Step 3. When the supply voltage is lower than the minimum operating voltage, the operation of the output transistor becomes indefinite.
- Step 4. The output voltage is equal to the GND level.
- Step 5. At Point "B", Vref ≤ V<sub>DD</sub>×Rb/(Ra+Rb) is true, as a result, the output of comparator is reversed from "H" to "L", then the output voltage is equal to the supply voltage (V<sub>DD</sub>). The voltage level of Point B means a released voltage (+V<sub>DET</sub>).
- \*) The difference between a released voltage and a detector threshold voltage is a detector threshold hysteresis.


## Detector Operation vs. glitch input voltage to the VDD pin

When the R3114x is at released, if the pulse voltage which the detector threshold or lower voltage, the graph below means that the relation between pulse width and the amplitude of the swing to keep the released state for the R3114x.






\*Vop: Over Drive Voltage




**VDD Input Waveform** 

This graph shows the maximum pulse conditions to keep the released voltage. If the pulse with larger amplitude or wider width than the graph above, is input to V<sub>DD</sub> pin, the reset signal may be output.


## **TEST CIRCUITS**




**Supply Current Test Circuit** 



**Detector Threshold Test Circuit** (Pull-up circuit is not necessary for CMOS Output type.)




**Nch Driver Output Current Test Circuit** 




Pch Driver Output Current Test Circuit

\*Apply to CMOS Output type only



Nch Driver Leakage Current Test Circuit


\*Apply to Nch Driver Output type only





Output Delay Time Test Circuit (Pull-up circuit is not necessary for CMOS Output type.)


## TYPICAL CHARACTERISTICS

#### 1) Supply Current vs. Input Voltage













#### 2) Detector Threshold vs. Temperature







#### R3114x








#### 3) Output Voltage vs. Input Voltage
























#### 4) Nch Driver Output Current vs. Input Voltage (VDS=0.5V)







## R3114x







## 5) Nch Driver Output Current vs. VDS













#### 6) Pch Driver Output Current vs. Input Voltage (VDS=-2.1V)













#### 7) Pch Driver Output Current vs. VDS







## R3114x







## 8) Output Delay Time vs. External Capacitance











## TYPICAL APPLICATION

• R3114xxx1A CPU Reset Circuit 1 (Nch Open Drain Output)


Case1. Input Voltage to R3114xxx1A is equal to Input Voltage to CPU




Case2. Input Voltage to R3114xxx1A is unequal to Input Voltage to CPU




• R3114xxx1C CPU Reset Circuit (CMOS Output)




 R3114xxx1A Output Delay Time Circuit 1 (Nch Open Drain Output)



 R3114xxx1A Output Delay Time Circuit 2 (Nch Open Drain Output)




• Memory Back-up Circuit




#### R3114x

 Voltage level Indicator Circuit (lighted when the power runs out) (Nch Open Drain Output)




 Detector Threshold Adjustable Circuit 1 (Nch Open Drain Output)



Adjustable Detector Threshold=(-VDET)×(Ra+Rb)/Rb

Hysteresis Voltage=(VHYS)×(Ra+Rb)/Rb

- \*1) To prevent oscillation, set  $Ra \le 1k\Omega$ ,  $Rb \le 100\Omega$ .
- \*2) If the value of Ra is set excessively large, voltage drop may occur caused by the supply current of IC itself, and detector threshold and hysteresis voltage may vary.
- \*3) If Vup and VDD are connected, the voltage dropdown caused by Rup, may cause difference in the hysteresis voltage.
- Detector Threshold Adjustable Circuit 2 (Nch Open Drain Output)





Adjustable Detector Threshold=(-VDET)×(Ra+Rb)/Rb

Hysteresis Voltage=(VHYS)×(Ra+Rb)/Rb


- \*1) To prevent oscillation, set Ra  $\leq$  100k $\Omega$ , C  $\geq$   $\leq$  0.01 $\mu$ F.
- \*2) If the value of Ra is set excessively large, voltage drop may occur caused by the supply current of IC itself, and detector threshold and hysteresis voltage may vary.
- \*3) If Vup and VDD are connected, the voltage dropdown caused by Rup, may cause difference in the hysteresis voltage.
- \*4) If the value of Ra, Rb and C are set excessively large, the delay of the start-up may become too long.

## Window Comparator Circuit (Nch Open Drain Output)





## • Over-charge Preventing Circuit




#### **TECHNICAL NOTES**

#### When connecting resistors to the device's input pin

When connecting a resistor (R1) to an input of this device, the input voltage decreases by [Device's Consumption Current] x [Resistance Value] only. And, the cross conduction current\*1, which occurs when changing from the detecting state to the release state, is decreased the input voltage by [Cross Conduction Current] x [Resistance Value] only. And then, this device will enter the re-detecting state if the input voltage reduction is larger than the difference between the detector voltage and the released voltage.

When the input resistance value is large and the VDD is gone up at mildly in the vicinity of the released voltage, repeating the above operation may result in the occurrence of output.

As shown in Figure A/B, set R1 to become 100 k $\Omega$  or less as a guide, and connect  $C_{IN}$  of 0.1  $\mu$ F and more to between the input pin and GND. Besides, make evaluations including temperature properties under the actual usage condition, with using the evaluation board like this way. As a result, make sure that the cross conduction current has no problem.



<sup>\*1</sup> In the CMOS output type, a charging current for OUT pin is included.

<sup>\*2</sup> Note the bias dependence of capacitors.



- 1. The products and the product specifications described in this document are subject to change or discontinuation of production without notice for reasons such as improvement. Therefore, before deciding to use the products, please refer to Ricoh sales representatives for the latest information thereon.
- 2. The materials in this document may not be copied or otherwise reproduced in whole or in part without prior written consent of Ricoh.
- 3. Please be sure to take any necessary formalities under relevant laws or regulations before exporting or otherwise taking out of your country the products or the technical information described herein.
- 4. The technical information described in this document shows typical characteristics of and example application circuits for the products. The release of such information is not to be construed as a warranty of or a grant of license under Ricoh's or any third party's intellectual property rights or any other rights.
- 5. The products listed in this document are intended and designed for use as general electronic components in standard applications (office equipment, telecommunication equipment, measuring instruments, consumer electronic products, amusement equipment etc.). Those customers intending to use a product in an application requiring extreme quality and reliability, for example, in a highly specific application where the failure or misoperation of the product could result in human injury or death (aircraft, spacevehicle, nuclear reactor control system, traffic control system, automotive and transportation equipment, combustion equipment, safety devices, life support system etc.) should first contact us.
- 6. We are making our continuous effort to improve the quality and reliability of our products, but semiconductor products are likely to fail with certain probability. In order to prevent any injury to persons or damages to property resulting from such failure, customers should be careful enough to incorporate safety measures in their design, such as redundancy feature, fire containment feature and fail-safe feature. We do not assume any liability or responsibility for any loss or damage arising from misuse or inappropriate use of the products.
- 7. Anti-radiation design is not implemented in the products described in this document.
- 8. The X-ray exposure can influence functions and characteristics of the products. Confirm the product functions and characteristics in the evaluation stage.
- 9. WLCSP products should be used in light shielded environments. The light exposure can influence functions and characteristics of the products under operation or storage.
- 10. There can be variation in the marking when different AOI (Automated Optical Inspection) equipment is used. In the case of recognizing the marking characteristic with AOI, please contact Ricoh sales or our distributor before attempting
- 11. Please contact Ricoh sales representatives should you have any questions or comments concerning the products or the technical information.



Ricoh is committed to reducing the environmental loading materials in electrical devices with a view to contributing to the protection of human health and the environment.

Halogen Free

Ricoh has been providing RoHS compliant products since April 1, 2006 and Halogen-free products since April 1, 2012.

#### RICOH RICOH ELECTRONIC DEVICES CO., LTD.

#### https://www.e-devices.ricoh.co.jp/en/

#### Sales & Support Offices

Ricoh Electronic Devices Co., Ltd.

Shin-Yokohama Office (International Sales)
2-3, Shin-Yokohama 3-chome, Kohoku-ku, Yokohama-shi, Kanagawa, 222-8530, Japan
Phone: +81-50-3814-7687 Fax: +81-45-474-0074

Ricoh Americas Holdings, Inc

way, Suite 200 Campbell, CA 95008, U.S.A. 675 Campbell Technology Part Phone: +1-408-610-3105

Ricoh Europe (Netherlands) B.V.

Semiconductor Support Centre

Prof. W.H. Keesomlaan 1, 1183 DJ Amstelveen, The Netherlands Phone: +31-20-5474-309

Ricoh International B.V. - German Branch

Semiconductor Sales and Support Centre Oberrather Strasse 6, 40472 Düsseldorf, Germany Phone: +49-211-6546-0

Ricoh Electronic Devices Korea Co., Ltd.

3F, Haesung Bldg, 504, Teheran-ro, Gangnam-gu, Seoul, 135-725, Korea Phone: +82-2-2135-5700 Fax: +82-2-2051-5713

Ricoh Electronic Devices Shanghai Co., Ltd.

Room 403, No.2 Building, No.690 Bibo Road, Pu Dong New District, Shanghai 201203, People's Republic of China

Phone: +86-21-5027-3200 Fax: +86-21-5027-3299

Ricoh Electronic Devices Shanghai Co., Ltd. Shenzhen Branch

1205, Block D(Jinlong Building), Kingkey 100, Hongbao Road, Luohu District,

Shenzhen, China Phone: +86-755-8348-7600 Ext 225

Ricoh Electronic Devices Co., Ltd.

Taipei office
Room 109, 10F-1, No.51, Hengyang Rd., Taipei City, Taiwan (R.O.C.)
Phone: +886-2-2313-1621/1622 Fax: +886-2-2313-1623

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

#### Ricoh Electronics:

```
R3114N281A-TR-FE R3114Q201A-TR-FE R3114K271A-TR R3114K071A-TR R3114Q461C-TR-FE R3114K301A-
TR R3114K241C-TR R3114Q261C-TR-FE R3114Q221C-TR-FE R3114N201A-TR-FE R3114N191A-TR-FE
R3114Q461A-TR-FE R3114K201A-TR R3114K311C-TR R3114Q181C-TR-FE R3114Q381A-TR-FE R3114K291A-
TR R3114Q211A-TR-FE R3114K161A-TR R3114K171A-TR R3114K071C-TR R3114K081A-TR R3114K081C-TR
R3114K091A-TR R3114K091C-TR R3114K101A-TR R3114Q491C-TR-FE R3114Q411C-TR-FE R3114Q421A-TR-
FE R3114Q421C-TR-FE R3114Q431C-TR-FE R3114Q451A-TR-FE R3114Q451C-TR-FE R3114Q331C-TR-FE
R3114Q341A-TR-FE R3114Q381C-TR-FE R3114Q391A-TR-FE R3114Q401A-TR-FE R3114Q401C-TR-FE
R3114Q281C-TR-FE R3114Q301A-TR-FE R3114Q301C-TR-FE R3114Q311A-TR-FE R3114Q311C-TR-FE
R3114Q331A-TR-FE R3114Q241C-TR-FE R3114Q251A-TR-FE R3114Q251C-TR-FE R3114Q271A-TR-FE
R3114Q271C-TR-FE R3114Q281A-TR-FE R3114Q191C-TR-FE R3114Q201C-TR-FE R3114Q221A-TR-FE
R3114Q231A-TR-FE R3114Q231C-TR-FE R3114Q241A-TR-FE R3114Q091C-TR-FE R3114Q101A-TR-FE
R3114Q101C-TR-FE R3114Q121A-TR-FE R3114Q181A-TR-FE R3114Q191A-TR-FE R3114N501C-TR-FE
R3114Q071A-TR-FE R3114Q071C-TR-FE R3114Q081A-TR-FE R3114Q081C-TR-FE R3114Q091A-TR-FE
R3114N421A-TR-FE R3114N421C-TR-FE R3114N451A-TR-FE R3114N451C-TR-FE R3114N491C-TR-FE
R3114N501A-TR-FE R3114N331A-TR-FE R3114N331C-TR-FE R3114N351A-TR-FE R3114N401A-TR-FE
R3114N401C-TR-FE R3114N411C-TR-FE R3114N271C-TR-FE R3114N281C-TR-FE R3114N291A-TR-FE
R3114N301C-TR-FE R3114N311A-TR-FE R3114N311C-TR-FE R3114N241A-TR-FE R3114N241C-TR-FE
R3114N251A-TR-FE R3114N251C-TR-FE R3114N261A-TR-FE R3114N271A-TR-FE R3114N201C-TR-FE
R3114N211A-TR-FE R3114N221A-TR-FE R3114N221C-TR-FE R3114N231A-TR-FE R3114N231C-TR-FE
R3114N101A-TR-FE
```