

Miniature PCB Relay OJ/OJE

3 to 10A rating

Typical applications

- Small size
- 4000V_{rms} coil to contact dielectric strength (OJ type)
- Sensitive coil optional



F0277-C

Appliances, HVAC, industrial control

Approvals

VDE 40007630, TUV R 50139166, UL E82292, CQC03001007764 Technical data of approved types on request

Contact Data		
Contact arrangement	1 form A,	1 NO
Rated voltage	30VDC, 2	50VAC
Max. switching voltage	30VDC, 2	77VAC
Rated current	3 to 1	0A
Contact material	Ag, AgSnO	, AgCdO
Min. recommended contact load	100mA,	5VDC
Frequency of operation	360 op	s./h
Operate time max.	OJ/OJE-L	
	OJ/OJE-D/	H: 10ms
Release time max.	4ms	3
Electrical endurance		
LM 3A, 250VAC, res., -30°C to		100x10 ³ ops.
DM 5A, 250VAC, res, -30°C to) +85°C	60x10 ³ ops.
LMH(2) 8A, 250VAC, res., -30°C to	o +70°C	100x10 ³ ops.
LMH2 8A, 250VAC,res., -30°C to) +85°C	30x10 ³ ops.
HM 10A, 250VAC, res., -30°C	to +70°C	100x10 ³ ops.
HM2 10A, 250VAC, res., -30°C	to +85°C	10x10 ³ ops.
Contact ratings		
LM	3A, 250	
DM	5A 250	VAC
LMH(2)	8A 250	VAC
HM(2)	10A 250)VAC
Mechanical endurance, DC coil	10x10 ⁶ op	erations

Coil Data

een bata	
Coil voltage range	3 to 48VDC
Operative range, IEC 61810	2
Coil insulation system according UL	Class E, F

Coil versions, DC coil, OJ/OJE-L sensitive type


Coil	Rated	Operate	Release	Coil	Rated coil			
code	voltage	voltage	voltage	resistance	power			
	VDC	VDC	VDC	Ω±10%	mW			
003	3	2.25	0.15	45	200			
005	5	3.75	0.25	125	200			
006	6	4.5	0.3	180	200			
009	9	6.75	0.45	405	200			
012	12	9	0.6	720	200			
024	24	18	1.2	2880	200			
048	48	36	2.4	11520	200			

All figures are given for coil without pre-energization, at ambient temperature +23°C


Coil versions, DC coil, OJ/OJE-D and -H type

Coil	Rated	Operate	Release	Coil	Rated coil				
code	voltage	voltage	voltage	resistance	power				
	VDC	VDC	VDC	Ω±10%	mW				
003	3	2.1	0.15	20	450				
005	5	3.5	0.25	55.6	450				
006	6	4.2	0.3	80	450				
009	9	6.3	0.45	180	450				
012	12	8.4	0.6	320	450				
024	24	16.8	1.2	1280	450				
048	48	33.6	2.4	5120	450				
A 11 C									


All figures are given for coil without pre-energization, at ambient temperature +23°C



Operate time



Coil temperature rise



06-2011, Rev. 0611 www.te.com © 2011 Tyco Electronics Corporation, a TE Connectivity Ltd. company Datasheets and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section. Datasheets and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions


Datasheets, product data, 'Definitions' section, application notes and all specifications are subject to change. 1



Miniature PCB Relay OJ/OJE (Continued)

Inculation Date	
Insulation Data	
Initial dielectric strength	7501
between open contacts	750V _{rms}
between contact and coil	OJ: 4000V _{rms}
	OJE: 3000V _{rms}
Clearance/creepage	
between contact and coil	OJ: > 7.7mm / 9.4mm
between contact and coil	OJE: > 3.2mm / 3.6mm
Tracking index of relay base	PTI 250
Other Data	
1	China RoHS, REACH, Halogen content
	Product Compliance Support Center at
	m/customersupport/rohssupportcenter
Ambient temperature	
DM:	-30°C to +85°C
HM:	-30°C to +70°C
HM2:	-30°C to +85°C
LM	-30°C to +90°C
LMH:	-30°C to +70°C
LMH2:	-30°C to +85°C
Category of environmental protection	1
IEC 61810	RTII - dust protected
	RTIII - wash tight
Shock resistance (functional)	10g
Shock resistance (destructive)	100g
Weight	9g
Resistance to soldering heat THT	-3
IEC 60068-2-20	BTII: 270°C/10s
120 00000 2 20	RTIII: 260°C/5s
Packaging unit	tray/100, carton box/1000
	1.a.y, 100, 001011 00/0 1000






PCB layout Bottom view on solder pins 4 - .05 DIA / (1.3) .067 (1.71) → (1.71)

> .500 ± .004 (12.7 ± .1) →

Dimensions



Produ	ict co	de structure	Турі	cal product code	OJ	-SH	-1	12	LMH	F	-WG	,000
Туре	OJ OJE	Miniature PCB Relay OJ, 4kV dielectric betw Miniature PCB Relay OJE, 3kV dielectric betv										
Categ	ory of p	protection										
-	SS SH	Fux proof Wash tight										
Numb	er of po	bles										
	1	1 pole										
Coil vo	oltage											
	Coil co	de: please refer to coil versions table (e.g. 12	= 12V	DC)								
Conta	ct rating	g and coil power										
		450 mWcoil power		200mW coil power								
	DM	5A type, coil power 450mW	LM	3A type, coil power	200mW							
	ТМ	TV-5 type, coil power 450mW	LMH	8A type, coil power	200mW							
	HM	10A type, coil power 450mW	LMH2	8A type, coil power	200mW							
	HM2	10A type, coil power 450mW										
Insula	tion sys	stem designation										
	Blank	Insulation Class E (standard)	F	Insulation Class F								
Specia	al type											
	Blank	Standard	WG	For domestic applia	ances (IEC	60335-1	, 4 Editic	on)				
Suffix												
	,000,	Standard										

2

Datasheets and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section.

Datasheets and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions

Datasheets, product data, 'Definitions' section, application notes and all specifications are subject to change.

-100 ± .004 (2.54 ± .1)



OEG

Miniature PCB Relay OJ/OJE (Continued)

Product code	Rating	Cont. mat.	Coil	Coil power	Туре	Insulation	Enclosure	Part Number
OJ-SH-105LM,000	ЗA	Ag	5VDC	200mW	Standard	Class E	Wash tight	1461404-1
OJE-SH-112LM,000			12VDC					1461401-5
OJE-SS-112LM,000							Flux proof	4-1419128-6
OJ-SH-112LM,000							Wash tight	1461404-6
OJ-SS-112LM,000							Flux proof	2-1419129-1
OJ-SS-124LM,000								3-1419129-1
OJ-SH-124LM,000			24VDC				Wash tight	1461404-4
OJE-SH-105DM,000	5A		5VDC	450mW				1461400-1
OJE-SS-105DM,000							Flux proof	2-1419128-8
OJE-SH-112DM,000			12VDC				Wash tight	1461400-4
OJE-SS-112DM,000							Flux proof	4-1419128-2
OJ-SH-112DM,000							Wash tight	1461406-4
OJ-SS-112DM,000							Flux proof	1-1419129-8
OJE-SH-124DM,000			24VDC				Wash tight	1461400-5
OJE-SS-124DM,000							Flux proof	6-1419128-2
OJ-SS-124DM,000							•	2-1419129-9
OJE-SH-105LMH,000	8A	AgCdO	5VDC	200mW			Wash tight	1461403-3
OJE-SH-105LMH-WG		9			WG type			1721875-2
OJE-SS-105LMH,000					Standard		Flux proof	1461034-2
OJ-SH-105LMH,000							Wash tight	8-1419128-1
OJ-SH-106LMH,000			6VDC				, i i i i i i i i i i i i i i i i i i i	1461247-1
OJE-SH-109LMH,000			9VDC					1461403-2
OJE-SS-109LMH,000			0.20				Flux proof	5-1419144-3
OJ-SH-109LMH,000							Wash tight	1461247-2
OJ-SS-109LMH2-WG		AgSnO			WG type		Flux proof	1721874-4
OJ-SS-109LMHF,000		AqCdO			Standard	Class F		1721083-5
OJE-SH-112LMH.000		, igouo	12VDC	_	Otaridara	Class E	Wash tight	1461403-4
OJE-SH-112LMH-WG			12000		WG type		vvaorreigne	1721875-5
OJE-SS-112LMH,000					Standard	1	Flux proof	5-1419128-0
OJE-SS-112LMH2		AgSnO			otaridara			1721261-5
OJ-SH-112LMH,000		AgCdO					Wash tight	9-1419128-8
OJ-SH-112LMH2		AgSnO					vvaorreigne	1-1721260-1
OJ-SS-112LMH,000		AgCdO					Flux proof	2-1419129-5
OJ-SS-112LMH2		AgSnO						1721260-5
OJ-SS-112LMHF,000		AgCdO				Class F		1721083-1
OJE-SH-124LMH,000		Agodo	24VDC	-		Class E	Wash tight	1461403-5
OJE-SH-124LMH-WG			24000		WG type		vvasii tigiit	1721875-6
OJE-SS-124LMH,000					Standard		Flux proof	7-1419128-1
OJ-SH-124LMH.000					Stanuaru		Wash tight	1461247-3
OJ-SS-124LMH,000							Flux proof	4-1419144-4
OJ-SS-124LMH2		AgSnO					Tiux piooi	1721260-6
OJ-SS-124LMH2-WG		Agono			WG type			1721200-0
OJ-SS-124LMHF,000		AgCdO			Standard	Class F	-	1461014-2
OJ-SH-105HM,000	10A	Agede	5VDC	450mW	Stanuaru	Class E	Wash tight	1461405-3
OJE-SH-105HM,000	IUA	Ag	12VDC	4301110		Class E	vvasn ligni	1461402-6
			12VDC				El nu pro of	
OJE-SS-112HM,000		A @ 0 m 0					Flux proof	4-1419128-3
OJE-SS-112HM2,000		AgSnO						1721539-5
OJ-SH-112HM,000		Ag					Wash tight	1461405-5
OJ-SS-112HM,000							Flux proof	1419135-3
OJ-SS-112HMF,000			0.41/200	-		Class F	-	1461078-5
OJE-SS-124HM,000			24VDC			Class E		6-1419128-4
OJ-SS-124HM,000								1440007-2
OJ-SS-124HM2,000		AgSnO						1721538-7

3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

 OJ-SH-124LM,000
 OJE-SH-105DM,095
 OJE-SH-124DM,000
 OJ-SH-112DM,000
 OJ-SH-112LM,000
 OJ-SH

 105HM,095
 OJE-SH-112DM,095
 OJ-SH-105HM,000
 OJ-SS-109DM,000
 OJE-SH-105DM,000
 OJE-SH-112HM,000

 OJE-SS-112LMH,000
 OJE-SH-105LMH,000
 OJE-SS-105LMH,000
 OJE-SS-124LMHF,000
 OJ-SS-112LMH2
 OJ-SS

 109LMHF,000
 OJ-SS-109LMH2-WG
 OJE-SH-124LMH-WG
 OJ-SS-124LMH2
 OJE-SS-112LMH2