

Micro Commercial Components

Micro Commercial Components 130 W Cochran St, Unit B Simi Valley, CA 93065 Tel:818-701-4933

BC856A THRU BC858C

PNP Small

Signal Transistor 200mW SOT-23

DIMENSIONS					
	INCHES		М		
DIM	MIN	MAX	MIN	MAX	NOTE
Α	.110	.120	2.80	3.04	
В	.083	.104	2.10	2.64	
С	.047	.055	1.20	1.40	
D	.035	.041	.89	1.03	
Е	.070	.081	1.78	2.05	
F	.018	.024	.45	.60	
G	.0005	.0039	.013	.100	
Н	.035	.044	.89	1.12	
J	.003	.007	.085	.180	
K	.015	.020	.37	.51	

Suggested Solder

Pad Layout inches mm

Features

- Lead Free Finish/RoHS Compliant ("P" Suffix designates RoHS Compliant. See ordering information)
- Epoxy meets UL 94 V-0 flammability rating
- Moisure Sensitivity Level 1
- Ideally Suited for Automatic Insertion
- 150°C Junction Temperature
- For Switching and AF Amplifier Applications
- Halogen free available upon request by adding suffix "-HF"

echanical Data

- Case: SOT-23, Molded Plastic
- Terminals: Solderable per MIL-STD-202, Method 208
- Polarity: See Diagram
- Weight: 0.008 grams (approx.)

Marking Code (Note 2)						
Туре	Marking	Туре	Marking			
BC856A	3A	BC857C	3G			
BC856B	3B	BC858A	3J			
BC857A	3E	BC858B	3K			
BC857B	3F	BC858C	3L			

Maximum Ratings @ 25°C Unless Otherwise Specified

Charateristic		Symbol	Value	Unit
Collector-Base Voltage	BC856		-80	
	BC857	V_{CBO}	-50	V
	BC858		-30	
Collector-Emitter Voltage	BC856		-65	
	BC857	$V_{\sf CEO}$	-45	V
	BC858		-30	
Emitter-Base Voltage		V_{EBO}	-5.0	V
Collector Current		I _C	-100	mΑ
Peak Collector Current		I _{CM}	-200	mΑ
Peak Emitter Current		I _{EM}	-200	mΑ
Power Dissipation@T _s =50°C	P_d	200	mW	
Operating & Storage Tempe	T_j , T_{STG}	-55~150	°C	

Note: 1. Package mounted on ceramic substrate 0.7mm X 2.5cm² area.

2. Current gain subgroup "C" is not available for BC856

1 of 5 **Revision: D** 2013/07/03



BC856A thru BC858C

Electrical Characteristics @ TA = 25°C unless otherwise specified


Characteristic			Symbol	Min	Тур	Max	Unit	Test Condition
Collector-Base Breakdown Voltage (Note 3) BC856 BC857 BC858		V _(BR) CBO	-80 -50 -30			V	I _C = 10μA, I _B = 0	
Collector-Emitter Breakdown Voltage (Note 3) BC856 BC857 BC858		V _{(BR)CEO}	-65 -45 -30			V	I _C = 10mA, I _B = 0	
Emitter-Base Breakdown Voltage	(Note 3)		V _{(BR)EBO}	-5	_	_	V	$I_E = 1\mu A, I_C = 0$
H-Parameters Small Signal Current Gain	Current Gain	Group A B C	h _{fe} h _{fe} h _{fe}		200 330 600	_	_	
Input Impedance Output Admittance	Current Gain	Group A B C	h _{ie} h _{ie} h _{ie} h _{oe}		2.7 4.5 8.7 18	_ _ _	kΩ kΩ kΩ μS	V _{CE} = -5.0V, I _C = -2.0mA, f = 1.0kHz
Reverse Voltage Transfer Ratio	Current Gain	B C	h _{oe} h _{oe} h _{re} h _{re} h _{re}	_ _ _ _	30 60 1.5x10-4 2x10-4 3x10-4	_ _ _ _ _	μS μS —	
DC Current Gain (Note 3)	Current Gain	Group A B C	h _{FE}	125 220 420	180 290 520	250 475 800	_	V _{CE} = -5.0V, I _C = -2.0mA
Thermal Resistance, Junction to S	Substrate Backs	ide	R _{0JSB}	_	_	320	°C/W	Note 1
Thermal Resistance, Junction to A	mbient		$R_{\theta JA}$	_	_	625	°C/W	Note 1
Collector-Emitter Saturation Volta	ge (Note 3)		V _{CE(SAT)}	_	-75 -250	-300 -650	mV	I _C = -10mA, I _B = -0.5mA I _C = -100mA, I _B = -5.0mA
Base-Emitter Saturation Voltage (Note 3)			V _{BE(SAT)}	_	-700 -850	_	mV	I _C = -10mA, I _B = -0.5mA I _C = -100mA, I _B = -5.0mA
Base-Emitter Voltage (Note 3)			V _{BE(ON)}	-600 —	-650 —	-750 -820	mV	V _{CE} = -5.0V, I _C = -2.0mA V _{CE} = -5.0V, I _C = -10mA
Collector-Cutoff Current (Note 3)		BC856 BC857 BC858	ICES ICES ICES ICBO ICBO	_ _ _ _	_ _ _ _	-15 -15 -15 -15 -4.0	nA nA nA nA µA	V _{CE} = -80V V _{CE} = -50V V _{CE} = -30V V _{CB} = -30V V _{CB} = -30V, T _A = 150°C
Gain Bandwidth Product			f _T	100	200	_	MHz	V _{CE} = -5.0V, I _C = -10mA, f = 100MHz
Collector-Base Capacitance			Ссво	_	3	_	pF	V _{CB} = -10V, f = 1.0MHz
Noise Figure		NF	_	2	10	dB	V_{CE} = -5.0V, I_{C} = 200 μ A, R_{S} = 2 $k\Omega$, f = 1 k Hz, Δf = 200Hz	

Notes

- 1. Package mounted on ceramic substrate 0.7mm x 2.5cm² area.
- 2. Current gain subgroup "C" is not available for BC856.
- 3. Short duration pulse test to minimize self-heating effect.





BC856A thru BC858C





BC856A thru BC858C







Ordering Information:

Device	Packing
Part Number-TP	Tape&Reel 3Kpcs/Reel

Note: Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Micro Commercial Components (MCC):

BC856A-TP BC856B-TP BC857A-TP BC857B-TP BC857C-TP