



Single pole, multiclamp terminal blocks

Compression clamp


DIN 1 - 3



Colour	Type	Part numbers
<i>Standard blocks</i>		
Grey	M 4/6.3A	0115 468.20
Blue	M 4/6.3A.N	0125 468.22
Beige V0	M 4/6.3A.V0	0195 468.21
<i>M 4/6.3A with partition</i>		
Grey	M 4/6.3A.1	0115 483.00



Standard 6 mm block. **0115 468.20**



Accessories

- | Image | Description | Colour | Type | Part numbers | |
|-------|---|---------------------------|----------|--------------------------------------|--------------------------|
| 1 | End section | grey, blue, yellow, beige | FEM3A | th. 3,0 mm | 0116 576.15 |
| 2 | Circuit separator | grey, blue, yellow, beige | SCM6 | | 0113 003.10 |
| 3 | Test socket | | AL2, AL3 | DIA. 2,0 mm, DIA. 3,0 mm | 0163 043.21, 0163 261.00 |
| 4 | Test device | | DCJ | yellow | 0173 059.03 |
| 5 | Test plug | | FC2 | DIA. 2,0 mm | 0007 865.26 |
| 6 | Assembled jumper bar (without IP 20 protection) | 32 A | BJM6 | (1)(2) 2 poles | 0168 516.25 |
| 7 | Assembled jumper bar (with IP 20 protection) | 32 A | BJMI6 | (1)(2) 2 poles | 0176 663.00 |
| 8 | Jumper bar not assembled Post + screw + washer | 32 A | BJS6 | (1)(2) 20 poles | 0174 784.20 |
| 9 | Connector plate | | EL6 | | 0173 627.21 |
| 10 | Screwless jumper bar orange IP 20 | 32 A | BJE6.2 | (1) 2 poles | 0299 694.04 |
| 11 | Jumper | 32 A | BJB | | 0199 466.23 |
| 12 | Alternated jumper bar | 35 A | BJA6 | (1)(2) | 0116 541.12 |
| 13 | Universal jumper bar | 50 A | BJDP1 | (1)(2) spacing 6 <-> spacing 16 | 0179 623.03 |
| 14 | Pivoting jumper bar | 50 A | BJDP3 | (1)(2) spacing 6 <-> spacing 12 | 0179 625.05 |
| 15 | Comb-type jumper bar | 35 A | PC6 | (1)(2) spacing 6 <-> spacing 8 or 10 | 0174 781.25 |
| 16 | IDC jumper | 35 A | AD2,5 | | 0114 205.20 |

End stop	th. 9 mm	BADL	V0	0399 903.02
End stop	th. 9,1 mm	BAM	V2	0103 002.26
End stop	th. 9,1 mm	BAM V0	V0	0199 306.03
Rail	35 x 7,5 x 1	PR3.Z2		0174 300.17
Rail	35 x 15 x 2,3	PR4		0168 500.12
Rail	35 x 15 x 1,5	PR5		0168 700.22
Rail	32 x 15 x 1,5	PR1.Z2		0163 050.04

Other end stops, rails and accessories : see section on accessories.

Characteristics

Wire size		IEC	UL	CSA
		NFC DIN		
Compression clamp	Solid wire	0,2-4 mm ²	22-10 AWG	12 AWG maxi.
	Stranded wire	0,22-4 mm ²	22-10 AWG	12 AWG maxi.
Voltage				
Rated		800 V	600 V	600 V
Pulse		8 kV		
Pollution degree		3		
Current				
Rated		32 A	20 A	25 A
Wire size				
Rated / Gauge		4 mm ² / A4	10 AWG	12 AWG
Wire strip. length	Recomm. Screwdriver	Recomm. torque	Protection	
9,5 mm	4 mm	0,5-0,8 Nm	IP 20	
.37"	.157"	4.4-7.1 lb.in	NEMA 1	

Notes

The use of some accessories may decrease the block's voltage rating. For more information, consult us.



R See section on marking method

Nota : (1) A circuit separator SC may be required with the use of these accessories.
(2) Use of these accessories requires the user to cut out the partition of the terminal block M 4/6.3A.1.