onsemi

Schottky Rectifier


SS32 - S310

Description


The SS32–S310 series includes a high–efficiency, low power loss, general–propose Schottky rectifiers. The clipbonded leg structure provides high thermal performance and low electrical resistance. These rectifiers are suited for free wheeling, secondary rectification, and reverse polarity protection applications.

Features

- Metal to Silicon Rectifiers, Majority Carrier Conduction
- Low–Forward Voltage Drop
- Easy Pick and Place
- High–Surge Current Capability
- This Device is Pb-Free and Halide Free



MARKING DIAGRAM



ORDERING INFORMATION

Device	Package	Shipping [†]
SS32 SS33 SS34 SS35 SS36 SS38 SS39 S310	SMC (Pb-Free, Halide-Free)	3000 / Tape & Reel

+ For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

		Value								
Symbol	Parameter	SS32	SS33	SS34	SS35	SS36	SS38	SS39	S310	Units
V _{RRM}	Maximum Repetitive Reverse Voltage	20	30	40	50	60	80	90	100	V
I _{F(AV)}	Maximum Average Forward Current at T _A = 75°C	3.0							A	
I _{FSM}	Non-Repetitive Peak Forward Surge Current: 8.3 ms Single Half-Sine Wave	100						А		
dV/dt	Maximum Voltage Rate of Change	10000					V/μS			
T _{STG}	Storage Temperature Range	Temperature Range -55 to +150					°C			
ТJ	Operating Junction Temperature -55 to +150						°C			

ABSOLUTE MAXIMUM RATINGS Values are at $T_A = 25^{\circ}C$ unless otherwise noted.

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS


Symbol	Parameter	Value	Unit
PD	Power Dissipation	2.27	W
R_{\thetaJA}	Thermal Resistance, Junction to Ambient (Note 1)	55	°C/W
$R_{\theta JL}$	Thermal Resistance, Junction to Lead	17	°C/W

1. Device mounted on FE-4 PCB 0.55 x 0.55 inch (14 x 14 mm).

ELECTRICAL CHARACTERISTICS Values are at $T_A = 25^{\circ}C$ unless otherwise noted.

			Value								
Symbol	Parameter	Test Conditions	SS32	SS33	SS34	SS35	SS36	SS38	SS39	S310	Units
V _F	Forwarded Voltage	I _F = 3.0 A	500			750		850			mV
I _R	Reverse Current at Rated V_R	$T_A = 25^{\circ}C$	0.5					mA			
		$T_A = 100^{\circ}C$	20			10					

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.




TYPICAL CHARACTERISTICS



Figure 1. Forward Current Derating Curve





100

Figure 5. Total Capacitance

V_R, Reverse Voltage (V)

1

-S310

10

SS35

100

10

0.1




Figure 6. Thermal Impedance Characteristics

2.45

1.90



SMC CASE 403AG **ISSUE O** DATE 31 AUG 2016 8.15 В 7.75 1.96 3.27 6.25 3.39 /B 2.75 5.55 6.81 \oplus (M) 0.13 С В А LAND PATTERN RECOMMENDATION 7.15 Α 6.60 **TOP VIEW 8** ° R0.15 0 0 **4X** 2.65 MAX GAGE 0.41 PLANE С 0.15 SEATING PLANE 0.203 0.30 /В` 0.050 4.70 0.05 **8** ° 4.40 0.45 ⊕|0.13 (M) **0** ° С В 1.60 Α 0.75 SIDE VIEW **DETAILA** NOTES: SCALE 2:1 EXCEPT WHERE NOTED, CONFORMS TO Α. JEDEC DO-214, VARIATION AB ⁄в` DOES NOT COMPLY TO JEDEC STD. VALUE C. ALL DIMENSIONS ARE IN MILLIMETERS DIMENSIONS ARE EXCLUSIVE OF BURRS, D.

- MOLD FLASH, AND TIE BAR PROTRUSIONS. E. DIMENSIONS AND TOLERANCING AS PER ASME Y14.5–2009
- F. LAND PATTERN STANDARD: DIOM7957X241M

 DOCUMENT NUMBER:
 98AON13442G
 Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.

 DESCRIPTION:
 SMC
 PAGE 1 OF 1

 ON Semiconductor and ()) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and calcular performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

TECHNICAL SUPPORT

onsemi Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

onsemi:

<u>SS32</u> <u>SS33</u> <u>SS34</u> <u>SS35</u> <u>SS36</u> <u>SS38</u> <u>SS39</u> <u>S310</u>