

DATA SHEET

METAL FILM RESISTORS

General Purpose MFR Series


±0.5%, ±1%, ±2%, ±5%

1/6W to 3W

RoHS compliant & Halogen Free



YAGEO





APPLICATIONS

- Y All general purpose applications
- Ÿ Power applications

EATURES

- Ÿ AEC-Q200 qualified
- Ÿ Wide resistance range
- Ϋ́ PPAP ready (MFR-25/MFR50S/MFR-50)
- Ÿ High stability
- Ÿ RoHS compliant & halogen-free

ORDERING INFORMATION

Part number of the general purpose metal film resistor are identified by the series, power rating, tolerance, packing, temperature coefficient, forming and resistance value.

PART NUMBER

<u>MFR</u>	<u> 200</u>	<u>F</u>	<u>T</u>	<u>F</u>	<u>73-</u>	<u>100R</u>
(1)	(2)	(3)	(4)	(5)	(6)	(7)

(1) SERIES

MFR Series

(2) POWER RATING

-12 = 1/6W	-50 = 1/2W	200 = 2W
25S = 1/4W	100 = 1W	3WS = 3W
-25 = 1/4W	2WS = 2W	1WS = 1W

50S = 1/2W

(3) TOLERANCE

$D = \pm 0.5\%$	$F = \pm 1\%$	$G = \pm 2\%$
I - +5%		

(4) PACKAGING

D. Dool Dook	T. Doy Dook	D Dulk
R = Reel Pack	T = Box Pack	B = Bulk

(5) TEMPERATURE COEFFICIENT OF RESISTANCE

E=±50ppm/°C	F=±100ppm/°C	- = Based on spec
	. = 100pp, 0	- Bacca cir opco

(6) FORMING

26- = 26mm	FFK = F-form Kink
52- = 52.4mm	FKK = FKK Type
73- = 73mm	MT = MT Type Forming
M = M-Type Forming	FT = FT Type Forming
MB = M-form W/fla	PN = PANAsert
F = F Type	AV = AVIsert
FK = FK Type	
52A=52.4mm, ψd 0.4±0.02mm	
52B=52.4mm, ψd 0.45±0.02mm	
52C=52.4mm, ψd 0.5±0.02mm	
52G=52.4mm, ψd ≥ 0.6mm	


(7) RESISTANCE VALUE

E24 & E96 & E192 Series Example: $100R = 100\Omega, \, 10K = 10,000\Omega, \, 1M = 1,000,000\Omega$

52H=52.4mm, non-painting on soldering spots


DIMENSIONS

Unit: mm



Normal	Miniature	L	ψD	Н	ψd
MFR-12	MFR25S	3.4 ± 0.3	1.9 ± 0.2	28 ± 2.0	0.45 ± 0.05
MFR-25	MFR50S	6.3 ± 0.5	2.4 ± 0.2	28 ± 2.0	0.55 ± 0.05
MFR-50	MFR1WS	9.0 ± 0.5	3.3 ± 0.3	26 ± 2.0	0.55 ± 0.05
MFR100	MFR2WS	11.5 ± 1.0	4.5 ± 0.5	35 ± 2.0	0.8 ± 0.05
MFR200	MFR3WS	15.5 ± 1.0	5.0 ± 0.5	33 ± 2.0	0.8 ± 0.05

DERATING CURVE



ELECTRICAL CHARACTERISTICS

CHARACTERISTICS	MFR-12	MFR25S	MFR-25	MFR50S	MFR-50	MFR1WS	MFR100	MFR2WS	MFR3WS
Power Rating at 70 °C	1/6W	1/4W	1/4W	1/2W	1/2W	1W	1W	2W	3W
Maximum Working Voltage	200V	200V	250V	300V	350V	400V	500V	500V	500V
Maximum Overload Voltage	400V	400V	500V	600V	700V	800V	1000V	1000V	1000V
Voltage Proof on Insulation	300V	400V	500V	500V	500V	700V	1000V	1000V	1000V
Resistance Range	1Ω ~ 4M7Ω for E24 & E96 series value								
Operating Temp. Range	- 55°C to +155°C								
Temperature Coefficient	±50ppm/°C , ±100ppm/°C								

Note: For resistance value out of above range is by request.

TEST AND REQUIRMENTS

TEST	TEST METHOD	PROCEDURE	APPRAISE
Short Time Overload	IEC 60115-1 4.13	2.5 times RCWV for 5 sec.(Not more than maximum overload voltage)	±0.25%+0.05Ω
Voltage Proof on Insulation	IEC 60115-1 4.7	In V-Block for 60 sec. test voltage as above table	No Breakdown
Temperature Coefficient	IEC 60115-1 4.8	Between -55°C to +155°C	Ву Туре
Insulation Resistance	IEC 60115-1 4.6	In V-Block for 60 sec.	>10,000ΜΩ
Solderability	IEC 60115-1 4.17	245±5°C for 3±0.5 Sec.	95% Min. coverage
Solvent Resistance of Marking	IEC 60115-1 4.30	IPA for 5±0.5 Min. with ultrasonic	No deterioration of coatings and markings
Robustness of Terminations	IEC 60115-1 4.16	Direct load for 10 Sec. in the direction of the terminal leads	≥2.5Kg(24.5N)
Periodic-pulse Overload	IEC 60115-1 4.39	4 times RCWV 10,000 cycles (1 Sec. on, 25 Sec.off)	±1.0%+0.05Ω
Damp Heat Steady State	IEC 60115-1 4.24	40±2°C,90-95% RH for 56 days, loaded with 0.1 times RCWV	±1.5%+0.05Ω
Endurance at 70°C	IEC 60115-1 4.25	70±2°C at RCWV(or Umax., whichever less) for 1,000 Hr.(1.5 Hr.on,0.5 Hr. off)	±1.5%+0.05Ω
Temperature Cycling	IEC 60115-1 4.19	è -55°C è Room Temp. è +155°C Room Temp.(5 cycles)	±0.75%+0.05Ω
Resistance to Soldering Heat	IEC 60115-1 4.18	260±3°C for 10±1 Sec., immersed to a point 3±0.5mm from the body	±0.25%+0.05Ω

Note:

RCWV (Rated Continuous Working Voltage):

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

 $V=\sqrt{(P X R)}$

or max. working voltage whichever is less

Where

V=Continuous rated DC or


AC (rms) working voltage (V)


P=Rated power (W)

R=Resistance value (Ω)




PULSE DIAGRAMS






AXIAL / REEL TAPE SPECIFICATION



Unit: mm

Normal	Miniature	a	A	B1-B2 (Max.)	S (spacing)	T (max. deviation of spacing)
MFR-12	MFR25S	6 ± 0.5	52.4 ± 1.5	1.2	- 5	
IVIFR-12	WFK200	0 ± 0.5	26.0 ± 1.5	1.0	5	
MED OF	MEDEOS	6.105	52.4 ± 1.5	1.2	- 5	-
MFR-25	R-25 MFR50S	6 ± 0.5	26.0 ± 1.5	1.0	5	1 mm per 10 spacing, 0.5 mm per 5 spacing
MFR-50	MFR1WS	6 ± 0.5	52.4 ± 1.5	1.2	5	
MED400	MEDOWIC	0.105	73.0 ± 1.5	1.5		- o.o min por o opaomig
MFR100	MFR2WS	6 ± 0.5	52.4 ± 1.5	1.2	- 5	
MFR200	MEDOOO MEDOWO	6 ± 0.5	73.0 ± 1.5	1.5	40	
IVIFIXZUU	MFR3WS	0 ± 0.5	52.4 ± 1.5	1.2	- 10	


TAPE ON REEL PACKING



TYPE Unit: mm/piece

Normal	Miniature	Across Flange(A)	В	Quantity Per Reel
MFR-12	MFR25S	66.5	75.5	5,000
MFR-25	MFR50S	66.5	75.5	5,000
MFR-50	MFR1WS	66.5	75.5	2,500
MFR100	MFR2WS	87	96	2,000
MFR200	MFR3WS	87	96	1,000

TAPE ON BOX PACKING



TYPE		DIMENSION	S		Unit: mm/piece
Normal	Miniature	Α	В	С	Quantity Per Box
MFR-12	MFR25S	48	102	255	5,000
MFR-12	MFR25S	81	70	260	5,000
MFR-25	MFR50S	48	102	255	5,000
MFR-25	MFR50S	81	104	260	5,000
MFR-50	MFR1WS	73	45	258	1,000
MFR100	MFR2WS	81	91	260	1,000
MFR100	MFR2WS	103	78	260	1,000
MFR200	MFR3WS	81	91	260	1,000
MFR200	MFR3WS	103	94	260	1,000


BULK PACKING

Normal	Miniature	Piece/Per Inner Box	Bag/Per Inner Box	Piece Per Bag
MFR-12	MFR25S	10,000	10	1,000
MFR-25	MFR50S	10,000	10	1,000
MFR-50	MFR1WS	5,000	5	1,000
MFR100	MFR2WS	2,000	4	500
MFR200	MFR3WS	1,000	2	500




FORMING

M TYPE




TYPE		DIMENSIONS	3			Unit: mm
Normal	Miniature	L	ψD	ψd	Р	н
MFR-12	MFR25S	3.4± 0.3	1.9 ± 0.2	0.45 ± 0.05	6.0 ± 1	10.0 ±1
MFR-25	MFR50S	6.3 ± 0.5	2.4 ± 0.2	0.55 ± 0.05	10.0 ± 1	10.0 ± 1
MFR-50	MFR1WS	9.0 ± 0.5	3.3± 0.3	0.55 ± 0.05	12.5 ± 1	10.0 ± 1
MFR100	MFR2WS	11.5 ± 1.0	4.5 ± 0.5	0.8 ± 0.05	15.0 ± 1	12.5 ± 1
MFR200	MFR3WS	15.5 ± 1.0	5.0 ± 0.5	0.8 ± 0.05	20.0 ± 1	15.0 ± 1

MB TYPE




TYPE		DIMENSION	IS		Ur				
Normal	Miniature	L	ψD	ψd	Р	H1	H2	t	
MFR-25	MFR50S	6.3 ± 0.5	2.4 ± 0.2	0.55 ± 0.05	10.0 ± 1	6.0 ± 1	5.0 ± 1	1.2 ± 0.2	
MFR-50	-	9.0 ± 0.5	3.3± 0.3	0.55 ± 0.05	12.5 ± 1	6.0 ± 1	5.0 ± 1	1.2 ± 0.2	
-	MFR1WS	9.0 ± 0.5	3.3± 0.3	0.8 ± 0.05	12.5 ± 1	6.0 ± 1	5.0 ± 1	1.4 ± 0.2	
MFR100	MFR2WS	11.5 ± 1.0	4.5 ± 0.5	0.8 ± 0.05	15.0 ± 1	6.0 ± 1	5.0 ± 1	1.4 ± 0.2	
MFR200	MFR3WS	15.5 ± 1.0	5.0 ± 0.5	0.8 ± 0.05	20.0 ± 1	10.0 ± 1	5.0 ± 1	1.4 ± 0.2	

MHA TYPE




TYPE		DIMENSI	DIMENSIONS				Unit: mm		
Normal	Miniature	L	ψD	ψd	В	Н0	н	Р	P0
		9.0±0.5	3.3±0.3	0.55±0.05	17.5Max	19.0±1.0	4.0±1.0	30.0±1.0	15.0±0.3
MFR-50	MFR1WS	P1	P2	F	W	W0	W1	ΨD0	
		7.5±1.0	3.75±0.5	7.5±0.5	18.0±0.5	5.0Min	9.0±0.5	4.0±0.2	_

MHB TYPE




TYPE		DIMENSIO	ONS							Unit: mm
Normal	Miniature	L	ψD	ψd	В	н	НО	н	H2	Н3
		15.5±1.0	5.0±0.5	0.8±0.05	21.0Max.	30Max.	18.0±1.0	5.5(Ref.)	8.0±1.5	16Max.
MFR200	MFR3WS	Р	P0	PI	P2	F	W	W0	W1	ΨD0
		30.0±1.0	15.0±0.3	7.5±1.0	3.75±0.8	7.5±0.5	18.0±0.5	5.0Min.	9.0±0.5	4.0±0.3

MHC TYPE




TYPE		DIMENSIC	DIMENSIONS						Unit: mm	
Normal	Miniature	L	ψD	ψd	В	Н	н	Р	P0	
		15.5±1.0	5.0±0.5	0.8±0.05	21.0Max.	19.0±1.0	5.25±1.0	30.0±1.0	15.0±0.3	
MFR200	MFR3WS	F	W	W0	W1	ΨD0				
		10.0±0.5	18.0±0.5	5.0Min.	9.0±0.5	4.0±0.2	_			



TYPE		DIMENSI	DIMENSIONS								Unit: mm
Normal	Miniature	L	ψD	ψd	P	h	H Max.	hl	НІ	E Max.	е
MFR-25	MFR50S	6.3 ± 0.5	2.4 ± 0.2	0.55 ± 0.05	6±1	-	-	5.5±0.5	13.5±0.5	3.5	-
MFR-50	MFR1WS	9.0±0.5	3.3±0.3	0.55±0.05	6±1	8±1	22	5±1	18.5 Max.	3.5	3.5±1
MFR100	MFR2WS	11.5±1	4.5±0.5	0.8±0.05	6±1	8±1	24	5±1	20 Max.	3.5	3.5±1
MFR200	MFR3WS	15.5±1	5.0±0.5	0.8±0.05	8±1	8±1	28	5± 1	25 Max.	3.5	3.5±1


FT TYPE (Taping Pack)




TYPE		DIME	Unit: mm	
Normal	Miniature	H1 Max.	H2 Max.	H3 Max.
MFR-25	MFR50S	10	18.5	8.5
MFR-50	MFR1WS	13	21.5	8.5
MFR100	MFR2WS	16	24.5	8.5

MT TYPE (Taping Pack)

Rated Watts: 1/6W,1/4WS




PN TYPE (Taping Pack)




TYPE		DIMEN	SIONS	Unit: mm
Normal	Miniature	H1 Max.	H2 Max.	H3 Max.
MFR-25	MFR50S	13	21.5	8.5
MFR-50	MFR1WS	17	25.5	8.5
MFR100	MFR2WS	19	27.5	8.5

AV TYPE (Taping Pack)



TYPE		DIMEN	DIMENSIONS				
Normal	Miniature	H1 Max.	H2 Max.	H3 Max.			
MFR-25	MFR50S	11.5	20	8.5			
MFR-50	MFR1WS	14.5	23	8.5			
MFR100	MFR2WS	17.5	26	8.5			

MARKING





REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 0	Aug.2, 2021	-	- First issue of this specification
Version 1	Sep.28, 2021		Add F TYPE for -25&50S power

MFR

" Yageo reserves all the rights for revising the content of this datasheet without further notification, as long as the products itse If are unchanged. Any product change will be announced by PCN."

LEGAL DISCLAIMER

Yageo, its distributors and agents (collectively, "Yageo"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. Yageo may make changes, modifications and/or improvements to product related information at any time and without notice.

Yageo makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, Yageo disclaims (i) any and all liability arising out of the application or use of any Yageo product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non-infringement and merchantability.

Yageo statements regarding the suitability of products for certain types of applications are based on Yageo's knowledge of typical operating conditions for such types of applications in a generic nature. Such statements are neither binding statements of Yageo nor intended to constitute any warranty concerning the suitability for a specific customer application or use. They are intended for use only by customers with requisite knowledge and experience for determining whether Yageo products are the correct products for their application or use. In addition, unpredicatable and isolated cases of product failure may still occur, therefore, customer application or use of Yageo products which requires higher degree of reliability or safety, shall employ additional protective safeguard measures to ensure that product failure would not result in personal injury or property damage.

Yageo products are not designed for application or use in medical, life-saving, or life-sustaining devices or for any other application or use in which the failure of Yageo products could result in personal injury or death. Customers using or selling Yageo products not expressly indicated for above-mentioned purposes shall do so at their own risk and agree to fully indemnify Yageo and hold Yageo harmless.

Information provided here is intended to indicate product specifications only. Yageo reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

YAGEO:

MFR-25FTE52-4K7 MFR-25FBF52-698K MFR-25FBF52-90K9 MFR-25FTE52-51R MFR-25FBF52-23R MFR-25FBF52-23R2 MFR-25FBF52-23R5 MFR-25FBF52-23R7 MFR-25FBF52-240K MFR-25FBF52-240R MFR-25FBF52-243K MFR-25FBF52-243R MFR-25FBF52-249K MFR-25FBF52-249R MFR-25FBF52-24K MFR-25FBF52-24K3 MFR-25FBF52-24K9 MFR-25FBF52-24R MFR-25FBF52-24R3 MFR-25FBF52-24R5 MFR-25FBF52-24R9 MFR-25FBF52-255K MFR-25FBF52-25R MFR-25FBF52-25K5 MFR-25FBF52-25R MFR-25FBF52-25R5 MFR-25FBF52-261K MFR-25FBF52-261R MFR-25FBF52-267K MFR-25FBF52-267R MFR-25FBF52-26K1 MFR-25FBF52-26K7 MFR-25FBF52-26R MFR-25FBF52-26R1 MFR-25FBF52-26R5 MFR-25FBF52-26R7 MFR-25FBF52-270K MFR-25FBF52-270R MFR-25FBF52-271R MFR-25FBF52-274K MFR-25FBF52-274R MFR-25FBF52-27K MFR-25FBF52-27K1 MFR-25FBF52-27K4 MFR-25FBF52-27R MFR-25FBF52-27R4 MFR-25FBF52-27R5 MFR-25FBF52-280K MFR-25FBF52-280R MFR-25FBF52-287K MFR-25FBF52-287R MFR-25FBF52-28K MFR-25FBF52-28K7 MFR-25FBF52-28R MFR-25FBF52-28R5 MFR-25FBF52-28R7 MFR-25FBF52-294K MFR-25FBF52-294R MFR-25FBF52-29K1 MFR-25FBF52-29K4 MFR-25FBF52-29R MFR-25FBF52-29R4 MFR-25FBF52-29R5 MFR-25FBF52-2K MFR-25FBF52-2K05 MFR-25FBF52-2K1 MFR-25FBF52-2K15 MFR-25FBF52-2K2 MFR-25FBF52-2K21 MFR-25FBF52-2K26 MFR-25FBF52-2K32 MFR-25FBF52-2K37 MFR-25FBF52-2K4 MFR-25FBF52-2K43 MFR-25FBF52-2K49 MFR-25FBF52-2K55 MFR-25FBF52-2K61 MFR-25FBF52-2K67 MFR-25FBF52-2K7 MFR-25FBF52-2K74 MFR-25FBF52-2K8 MFR-25FBF52-2K87 MFR-25FBF52-2K94 MFR-25FBF52-2M MFR-25FBF52-2M2 MFR-25FBF52-2M26 MFR-25FBF52-2M32 MFR-25FBF52-2M43 MFR-25FBF52-2M49 MFR-25FBF52-2M55 MFR-25FBF52-2M7 MFR-25FBF52-2M74 MFR-25FBF52-2M8 MFR-25FBF52-2M87 MFR-25FBF52-2R MFR-25FBF52-2R1 MFR-25FBF52-2R5 MFR-25FBF52-300K MFR-25FBF52-300R MFR-25FBF52-301K