## **H** Series

Vishay BCcomponents



## FEATURES

- High capacitance in small size
- Kinked (preferred) or straight leads
- Compliant to RoHS Directive 2011/65/EU

## APPLICATIONS

- Bypassing
- Coupling
- Resonant circuit

## DESIGN

The capacitors consist of a ceramic disc both sides of which are silver-plated. Connection leads are made of tinned copper having a diameter of 0.6 mm.

The capacitors have inward kinked leads with a spacing of 5 mm (0.200") or 7.5 mm (0.300") and a lead length from 4 mm to 30 mm. Encapsulation is made of phenolic resin for 500  $V_{DC}$  and epoxy resin for 1 kV<sub>DC</sub>.

### **CAPACITANCE RANGE**

Class 2, at 1 kHz, 1 V<sub>BMS</sub> ± 0.2 V<sub>BMS</sub>; 1000 pF to 4700 pF

### **RATED DC VOLTAGE**

500 V and 1 kV

## **DIELECTRIC STRENGTH**

250 % of rated voltage for 500  $V_{DC}$  200 % of rated voltage for 1  $kV_{DC}$ 

### INSULATION RESISTANCE AT 500 VDC

 $\geq$  10 000 M $\Omega$ 

### **TOLERANCE ON CAPACITANCE**

± 10 %; ± 20 %

### **DISSIPATION FACTOR**

Class 2,  $\leq$  2.5 %



www.vishay.com

QUICK REFERENCE DATA			
DESCRIPTION	CLASS 2 (X7R)		
Voltage (V <sub>DC</sub> )	500, 1000		
Min. Capacitance (pF)	1000		
Max. Capacitance (pF)	4700		
Mounting	Through hole		

#### MARKING

Marking indicates capacitance value and tolerance in accordance with "EIA 198".

The capacitors meet the essential requirements of "EIA 198". Unless stated otherwise all electrical values apply at an ambient temperature of 25 °C  $\pm$  3 °C, at normal atmospheric conditions.

## **OPERATING TEMPERATURE RANGE**

Class 2, - 55 °C to +125 °C

### **TEMPERATURE COEFFICIENTS**

Class 2, X7R

## SECTIONAL SPECIFICATIONS

Class 2, IEC 60 384-9, EIA 198

## CLIMATIC CATEGORY

Class 2, 55/125/21

Revision: 14-Feb-12

Document Number: 28540



1

## **H** Series



## Vishay BCcomponents

## DIMENSIONS





Capacitors with 5 mm (0.20") and 7.5 mm (0.30") lead spacing

ORDERING INFORMATION (PREFERRED TYPES), CLASS 2, 500 V <sub>DC</sub> , KINKED					
<u> </u>		CLEAR TEXT CODE			
(pF)	(%)	(mm)	(mm)	(mm)	13 <sup>TH</sup> DIGIT: T = REEL; U = AMMO; 3 = BULK
CLASS 2 X7R					
1000	-	6.5	5.0		H102K25X7RL6.J5R
1500		7.5		5.0	
2200	± 10	8.5		4.0	H222K33X7RL6.J5R
3300		10			H332K39X7RL6.J5R
4700		12	7.5		H472K47X7RL6.J7R

Notes

<sup>(1)</sup> SH = Seated height

Maximum thickness 4.0 mm

· Lead style codes refer to inward kinked leads. Other styles available on request

ORDERING INFORMATION (PREFERRED TYPES), CLASS 2, 1 kV <sub>DC</sub> , KINKED					
C		CLEAR TEXT CODE			
(pF)	(%)	(mm)	(mm)	(mm)	13 <sup>TH</sup> DIGIT: T = REEL; U = AMMO; 3 = BULK
CLASS 2 X7R					
1000	-	6.5	5.0		H102K25X7RN6.J5R
1500		8			H152K31X7RN6.J5R
2200	± 10	9		4.0	H222K35X7RN6.J5R
3300		10.5			H332K41X7RN6.J5R
4700		12	7.5		H472K47X7RN6.J7R

Notes

<sup>(1)</sup> SH = Seated height

Maximum thickness 4.0 mm

· Lead style codes refer to inward kinked leads. Other styles available on request

PACKAGING					
D <sub>MAX</sub>	SIZE CODE	PACKAGING QUANTITIES			
(mm)		BULK	REEL	AMMO	
5.0 (0.20")	20	1000	2000	2000	
6.5 (0.25")	25				
7.5 (0.29")	29				
8.5 (0.33")	33				
10.0 (0.39")	39				
11.0 (0.43")	43				
12.0 (0.47")	47				
13.5 (0.53")	53	500			
15.0 (0.59")	59		-	-	
17.5 (0.69")	69				

Note

The capacitors are supplied in bulk packaging (cardboard boxes), in tape on reel or in ammopack.

## **H** Series



## Vishay BCcomponents



Kinked capacitors on tape, lead spacing 5.0 mm (0.2")

DIMENSIONS OF TAPE					
SYMBOL	DADAMETED	DIMENSIONS (mm)			
	PARAMETER	NOMINAL	TOLERANCE		
D	Body diameter	11.0 maximum	-		
d	Lead diameter	0.6	± 0.05		
Р	Pitch between capacitors	12.7	± 1.0		
P <sub>0</sub> <sup>(1)</sup>	Feed-hole pitch	12.7	± 0.3		
ΔP	Plane deviation	1.0 maximum	-		
P1 <sup>(2)</sup>	Feed-hole center to lead center	3.85	± 0.7		
P <sub>2</sub> <sup>(2)</sup>	Feed-hole center to component center	6.35	± 1.3		
F	Lead spacing	5.0	0.6 - 0.4		
Δh	Component alignment	0	± 1.0		
W	Tape width	18.0	1.0 - 0.5		
W <sub>0</sub>	Hold-down tape width	5.0 minimum	-		
W <sub>1</sub>	Hole position	9.0	0.75 - 0.5		
W <sub>2</sub>	Hold-down tape margin	3.0 maximum	-		
H <sub>0</sub>	Height to seating plane	16.0	± 0.5		
H <sub>1</sub>	Maximum component height	32.0	-		
е	Lead end protrusion	1.0 maximum	-		
L	Maximum length of snipped lead	11.0	-		
D <sub>0</sub>	Feed-hole diameter	4.0	± 0.2		
t	Total tape thickness	0.9 maximum	-		
t <sub>1</sub>	Maximum thickness of tape and wires	1.5 maximum	-		

#### Notes

<sup>(1)</sup> Cumulative pitch error:  $\pm \le 1$  mm/20 pitches

<sup>(2)</sup> Obliquity maximum 3°



Vishay BCcomponents

## **REEL AND TAPE DATA** in millimeters



Reel with capacitors on tape



Ammopack with capacitors on tape



Vishay

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay: H103K63X7RL63J7R H332K41X7RN63J5R