

M12-Receptacle Connectors In Accordance With IEC 61076-2-101


RSFM.../20/0.5 M | RKFM.../20/0.5 M



Male, 3-, 4-, 5- and 8-Pole

M12 Receptacle connector, combined FIXCON/ M12 male connector for front mounting, assembled stranded wire, solder contacts potted with epoxy, chassis side thread M20 x 1.5 (panel nut RSKFM 20).

RSFM.../20/0.5 M



*a O-ring enclosed separately


*b solder contacts potted with epoxy
 *L*0.5 m



M12 Female, 3-, 4-, and 5-Pole

M12 Receptacle connector, combined FIXCON/ M12 female connector for front mounting, assembled stranded wire, solder contacts potted with epoxy, chassis side thread M20 x 1.5 (panel nut RSKFM 20).


RKFM.../20/0.5 M



Pin Assignments


Face Views / M12, Male / Female

3 pole




1 = brown
 3 = blue
 4 = black

4 pole




1 = brown
 2 = white
 3 = blue
 4 = black

5 pole



1 = brown
 2 = white
 3 = blue
 4 = black
 5 = green/yellow

8 pole



1 = white
 2 = brown
 3 = green
 4 = yellow
 5 = grey
 6 = pink
 7 = blue
 8 = red



M12-Receptacle Connectors In Accordance With IEC 61076-2-101

RSFM.../20/0.5 M | RKFM.../20/0.5 M

Technical Data

Environmental









Degree of protection IP 67 / NEMA 6P
 Operating temperature range -25°C (-13°F) / +80°C (+176°F)

Mechanical

Housing CuZn
 Surface housing Cu/Ni
 Contact bearer PA 6/66
 Contact CuZn
 Contact surface Cu/Au
 O-ring Neoprene

Electrical

Operating voltage 240 V, 3 and 4 poles
 60 V, 5 poles
 30 V, 8 poles
 Rated voltage 250 V, 3 and 4 poles
 63 V, 5 poles
 36 V, 8 poles
 Rated current 4 A, 3 - 5 poles
 1,5 A, 8 poles
 Rated impulse voltage 2,0 kV, 3 and 4 poles
 1,5 kV, 5 and 8 poles
 Pollution degree 3
 Insulation resistance > 10⁹ Ω
 Contact resistance ≤ 5 mΩ

Part Number	Pins	Lead (mm ²)	Characteristics
RSFM 3/20/0.5 M	3	0.34	 
RSFM 4/20/0.5 M	4	0.34	 
RSFM 5/20/0.5 M RKFM 5/20/0.5 M	5	4 x 0.34 / 1 x 0.50	 
RSFM 8/20/0.5 M	3	0.34	 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lumberg Automation:](#)

[RSFM 4/20/0,5 M](#) [RSFM 4/20/1 M](#) [RSFM 8/20/0,5 M](#) [RSFM 5/20/0.5M](#) [RSFM 5/20/2 M](#)