


1 Watt IV Series

xppower.com **XP**

DC-DC



- Single & Dual Output
- SIP or DIP Package
- 3000 VDC Isolation
- Optional 4000 & 6000 VDC Isolation
- -40 °C to +85 °C Operation
- MTBF >1.1 Mhrs
- 3 Year Warranty

Specification

Input

- Input Voltage Range • Nominal $\pm 10\%$ ⁽³⁾
- Input Reflected • 20 mA pk-pk through 12 μ H,
- Ripple Current • 5 Hz to 20 MHz
- Input Reverse Voltage • None
- Protection
- Input Filter • Capacitor

Output

- Output Voltage • See table
- Minimum Load • None⁽⁴⁾
- Line Regulation • 1.2%/1% Δ Vin
- Load Regulation • $\pm 10\%$ 20-100% load change (3.3 V models $\pm 20\%$)
- Setpoint Accuracy • $\pm 3\%$
- Ripple & Noise • 75 mV pk-pk max, 20 MHz bandwidth
- Temperature Coefficient • 0.02%/°C
- Maximum Capacitive Load • Dual: $\pm 100 \mu$ F, Single: 220 μ F

General

- Efficiency • See table
- Isolation Voltage • 3000 VDC⁽⁶⁾
- Isolation Resistance • $10^9 \Omega$
- Isolation Capacitance • 60 pF typical
- Switching Frequency • Variable, 80 KHz typical
- MTBF • >1.1 Mhrs to MIL-HDBK-217F at 25 °C, GB

Environmental

- Operating Temperature • -40 °C to +85 °C
- Storage Temperature • -40 °C to +125 °C
- Case Temperature • 100 °C max
- Cooling • Convection-cooled

Safety


- Safety Approvals • UL60950-1 & CAN/CSA C22.2 No. 60950-1
UL62368-1 & CAN/CSA C22.2 No. 62368-1

Notes

1. For dual output, delete suffix 'A', and split current equally between rails.
2. For DIP package, replace 'S' in part number with 'D'.
3. For 48 V nominal input, a 4.7-47 μ F capacitor is required across the input.
4. Operation at no load will not damage unit but it may not meet all specifications.
5. 48 V model dimension is 0.28 (7.20).
6. For 4000 VDC Isolation, add suffix '-H4'. For 6000 VDC Isolation, add suffix '-H6'.
7. All dimensions in inches (mm).
8. Pin pitch tolerance: ± 0.014 (± 0.35)
9. Case tolerance: ± 0.02 (± 0.5)
10. Weight: SIP 0.006 lbs (2.6 g), DIP 0.005 lbs (2.3 g)

Input Voltage ⁽³⁾	No Load Input Current	Output Voltage	Output Current	Efficiency	Model Number ^(1,2)
5 VDC	30 mA	3.3 V	300 mA	75%	IV0503SA
	30 mA	5.0 V	200 mA	78%	IV0505SA
	30 mA	9.0 V	112 mA	75%	IV0509SA
	30 mA	12.0 V	84 mA	76%	IV0512SA
	30 mA	15.0 V	66 mA	76%	IV0515SA
	30 mA	24.0 V	42 mA	72%	IV0524SA
12 VDC	20 mA	3.3 V	300 mA	74%	IV1203SA
	20 mA	5.0 V	200 mA	74%	IV1205SA
	20 mA	9.0 V	112 mA	75%	IV1209SA
	20 mA	12.0 V	84 mA	77%	IV1212SA
	20 mA	15.0 V	66 mA	78%	IV1215SA
	20 mA	24.0 V	42 mA	75%	IV1224SA
24 VDC	10 mA	3.3 V	300 mA	75%	IV2403SA
	10 mA	5.0 V	200 mA	77%	IV2405SA
	10 mA	9.0 V	112 mA	75%	IV2409SA
	10 mA	12.0 V	84 mA	78%	IV2412SA
	10 mA	15.0 V	66 mA	78%	IV2415SA
	10 mA	24.0 V	42 mA	78%	IV2424SA
48 VDC	6 mA	3.3 V	300 mA	72%	IV4803SA
	6 mA	5.0 V	200 mA	72%	IV4805SA
	6 mA	9.0 V	112 mA	74%	IV4809SA
	6 mA	12.0 V	84 mA	75%	IV4812SA
	6 mA	15.0 V	66 mA	75%	IV4815SA
	6 mA	24.0 V	42 mA	70%	IV4824SA

Mechanical Details



T H E X P E R T S I N P O W E R

30 April 2020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

XP Power:

[IV1212S](#) [IV2409S](#) [IV1215S](#) [IV4803SA](#) [IV0512SA](#) [IV0509S](#) [IV0505SA](#) [IV1209SA](#) [IV0503SA](#) [IV1215SA](#)
[IV0509SA](#) [IV2405S](#) [IV4824S](#) [IV2415S](#) [IV2412S](#) [IV1203SA](#) [IV1205S](#) [IV2403S](#) [IV4815SA](#) [IV4809SA](#) [IV0505S](#)
[IV0515SA](#) [IV2409SA](#) [IV1212SA](#) [IV4824SA](#) [IV4812SA](#) [IV2405SA](#) [IV0515S](#) [IV4809S](#) [IV4805S](#) [IV0503S](#) [IV1205SA](#)
[IV4815S](#) [IV1203S](#) [IV2424SA](#) [IV1224S](#) [IV4812S](#) [IV4805SA](#) [IV1209S](#) [IV0524S](#) [IV2415SA](#) [IV4803S](#) [IV2403SA](#)
[IV0524SA](#) [IV2424S](#) [IV0512S](#) [IV2412SA](#) [IV1224SA](#)