
CLASSIC Splicing Connector; for all conductor types; max. 4 mm<sup>2</sup>; 5-conductor; with levers; gray housing; Surrounding air temperature: max 40° C; 2.50 mm<sup>2</sup>; gray



www.wago.com/222-415





# Data Notes

Safety information 1 in grounded power lines

#### Electrical data

## Ratings per IEC/EN

Ratings per	EN 60664
Nominal voltage (II/2)	400 V
Rated surge voltage (II/2)	4 kV
Rated current	32 A
Legend (ratings)	(II / 2) ≙ Overvoltage category II / Pollution degree 2

#### Connection data

Total number of connection points	5
Total number of potentials	1

 $\label{thm:continuity} \textbf{Subject to changes. Please also observe the further product documentation!}$ 

WAGO GmbH & Co. KG Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/222-415



#### Connection 1

Connection technology	CAGE CLAMP®
Actuation type	Lever
Connectable conductor materials	Copper
Solid conductor	0.08 2.5 mm² / 28 12 AWG
Stranded conductor	0.08 2.5 mm² / 28 12 AWG
Fine-stranded conductor	0.08 4 mm² / 28 12 AWG
Strip length	9 10 mm / 0.35 0.39 inch
Wiring direction	Side-entry wiring

## Physical data

Width	26.6 mm / 1.047 inch
Height	14.5 mm / 0.571 inch
Depth	20.5 mm / 0.807 inch

#### Material data

Note on material data	Information on material data can be found here	
Color	gray	
Flammability class per UL94	V0	
ire load	0.13 MJ	
Color of actuator	orange	
Weight	6.6 g	

## **Environmental requirements**

Surrounding air temperature (operation)	40 °C
Continuous operating temperature	85 ℃

#### Commercial data

Product Group	7 (Push Wire Conn.)
eCl@ss 10.0	27-14-11-04
eCl@ss 9.0	27-14-11-04
ETIM 7.0	EC000446
ETIM 6.0	EC000446
PU (SPU)	400 (40) Stück
Packaging type	box

 $\label{thm:condition} \textbf{Subject to changes. Please also observe the further product documentation!}$ 

WAGO GmbH & Co. KG

Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/222-415



Country of origin	DE	
GTIN	4044918464956	
Customs tariff number	85369010000	

#### Approvals / Certificates

## **Country specific Approvals**

			Certificate
Logo	Approval	Additional Approval Text	name
	ENEC 15	EN 60998	ENEC-
15	UL International Demko A/S		01360

#### Ship Approvals

			Certificate
Logo	Approval	Additional Approval Text	name
ABS.	ABS	-	18-
	American Bureau of Shipping		HG1755093-
TATE ONE OF THE			PDA
	DNV GL	EN 60998	TAE000015T
	Det Norske Veritas, Germanischer Lloyd		
	LR	EN 60998	04/20013
BAP THE AMERICAN	Lloyds Register		(E8)

#### **UL-Approvals**

			Certificate
Logo	Approval	Additional Approval Text	name
c(UL)us	UL	UL 486C	E69654
LISTED	UL International Germany GmbH		

#### Optional accessories

## Mounting adapter

Mounting accessories



Item no.: 222-500

Mounting carrier; 222 Series; for DIN-35 rail mounting/screw mounting; orange

www.wago.com/222-500

 $\label{lem:condition} \textbf{Subject to changes. Please also observe the further product documentation!}$ 

WAGO GmbH & Co. KG Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/222-415



# Downloads Documentation

**Bid Text** 

222-415	19 февр. 2019 г.	xml	Download
X81 - Datei		3.5 kB	
222-415	23 янв. 2019 г.	docx	Download
docx - Datei		15.8 kB	
Additional Information			
Technical Section		pdf	Download
Technical explanations		2.2 MB	

#### CAD/CAE-Data

CAE data

2D/3D Models 222-415	URL	Download
CAD data		
ZUKEN Portal 222-415	URL	Download
WSCAD Universe 222-415	URL	Download
EPLAN Data Portal 222-415	URL	Download

## **Environmental Product Compliance**

**Compliance Search** 

Envir	ronmental Product Compliance 222-415	URL	Download
CLAS	SSIC Splicing Connector; for all conductor types; max. 4 mm²; 5-conductor; with		
lever	rs; gray housing; Surrounding air temperature: max 40°C; 2.50 mm²; gray		

#### **Installation Notes**

Conductor termination

 $\label{thm:condition} \textbf{Subject to changes. Please also observe the further product documentation!}$ 

WAGO GmbH & Co. KG Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.

# Data sheet | Item number: 222-415 www.wago.com/222-415



Strip conductor to 9 10 mm (0.35 0.39 inch).	Termination: Lift the lever to open the clamping unit and insert a stripped conductor.	Then, lower the lever to close the clamp.
Testing		
Testing via Profi-LED+ voltage tester (206-806).		
Application		
Maria Garage and Albanda and A		
Wiring fine-stranded conductors in junction boxes.	Custom low-voltage lighting system	Connecting pre-wired and pre-fabricated components (e.g., in mobile homes).

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.

# www.wago.com/222-415

Data sheet | Item number: 222-415



Lighting fixture connection with finestranded wires and power feed

 $\label{thm:condition} \textbf{Subject to changes. Please also observe the further product documentation!}$ 

WAGO GmbH & Co. KG Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/222-415



# Compact, lever-operated splicing connectors:

They connect up to five stripped, finestranded conductors from 0.08 to 4 mm² (28 ... 12 AWG), as well as solid or stranded conductors from up to 2.5 mm² (12 AWG) – without tools!

#### How they work:

Pull up one of the orange operating levers to open the clamping unit so that the lever engages and keeps the clamp in its opened position. Then insert the conductor and push the lever back down, flush with the connector housing.

#### Safety:

The lever's specially designed rest position reliably prevents accidental unclamping of a connected conductor. Application safety, for any type of conductor (solid, stranded, finestranded), is confirmed by approvals like ENEC or UL.

ENEC is the European mark for electrical products that demonstrates compliance with European safety standards. The ENEC mark is subjected to the same EN standards as the VDE mark.

While the VDE mark is only permitted in Germany, the ENEC mark is accepted in more than 20 European countries.

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.