FCX789A

25V PNP MEDIUM POWER TRANSISTOR IN SOT89

Features

- BV_{CEO} > -25V
- I_C = -3A high Continuous Current
- I_{CM} = -8A Peak Pulse Current
- Low saturation voltage $V_{CE(sat)}$ < -320mV @ -3A
- h_{FE} specified up to -8A for high current gain hold up
- Complementary NPN Type: FCX688B
- **Lead-Free Finish; RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**
- **Qualified to AEC-Q101 Standards for High Reliability**

Mechanical Data

- Case: SOT89
- Case material: molded plastic. "Green" molding compound.
- UL Flammability Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish - Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 (e3)
- Weight: 0.05 grams (Approximate)

SOT89

Top View



Device Symbol



Top View
Pin Out

Ordering Information (Note 4)

Product	Marking	Reel size (inches)	Tape width (mm)	Quantity per reel
FCX789ATA	789	7	12	1,000

Notes:
1. EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant. All applicable RoHS exemptions applied.
2. See http://www.diodes.com for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
4. For packaging details, go to our website at http://www.diodes.com.

Marking Information



789 = Product Type Marking Code

© Diodes Incorporated

Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Limit	Unit
Collector-Base Voltage	V_{CBO}	-25	V
Collector-Emitter Voltage	V_{CEO}	-25	V
Emitter-Base Voltage	V_{EBO}	-7	V
Continuous Collector Current	I_C	-3	A
Peak Pulse Current	I_{CM}	-8	A

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit
Power Dissipation	(Note 5)	P_D	1	W
	(Note 6)		2	
Thermal Resistance, Junction to Ambient Air	(Note 5)	$R_{\theta JA}$	125	°C/W
	(Note 6)		62.5	
Thermal Resistance, Junction to Leads	(Note 7)	$R_{\theta JL}$	5.31	°C/W
Operating and Storage Temperature Range		T_J, T_{STG}	-55 to +150	°C

ESD Ratings (Note 8)

Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge - Human Body Model	ESD HBM	4,000	V	3A
Electrostatic Discharge - Machine Model	ESD MM	≥ 400	V	C

Notes:
5. For a device surface mounted on 15mm X 15mm FR4 PCB with high coverage of single sided 1 oz copper, in still air conditions; the device is measured when operating in steady state condition.
6. Same as note (5), except the device is mounted on 40mm X 40mm FR4 PCB.
7. Thermal resistance from junction to solder-point (at the end of collector lead).
8. Refer to JEDEC specification JESD22-A114 and JESD22-A115.

© Diodes Incorporated

Thermal Characteristics and Derating Information



Derating Curve



Transient Thermal Impedance



Pulse Power Dissipation



Safe Operating Area

© Diodes Incorporated

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Typ.	Max	Unit	Test Condition
Collector-Base Breakdown Voltage	BV_{CBO}	-25	-	-	V	I_C = -100µA
Collector-Emitter Breakdown Voltage (Note 9)	BV_{CEO}	-25	-	-	V	I_C = -10mA
Emitter-Base Breakdown Voltage	BV_{EBO}	-7	-8.1	-	V	I_E = -100µA
Collector Cutoff Current	I_{CBO}	-	<1	-100	nA	V_{CB} = -15V
Emitter Cutoff Current	I_{EBO}	-	<1	-100	nA	V_{EB} = -5.6V
DC current transfer Static ratio (Note 9)	h_{FE}	300 230 180 75	500 320 250 120	800 - - -	-	I_C = -10mA, V_{CE} = -2V I_C = -1A, V_{CE} = -2V I_C = -2A, V_{CE} = -2V I_C = -6A, V_{CE} = -2V
Collector-Emitter Saturation Voltage (Note 9)	$V_{CE(sat)}$	- - -	-130 -290 -250	-190 -400 -320	mV	I_C = -1A, I_B = -10mA I_C = -2A, I_B = -20mA I_C = -3A, I_B = -100mA
Base-Emitter Saturation Voltage (Note 9)	$V_{BE(sat)}$	-	-0.8	-0.9	V	I_C = -1A, I_B = -10mA
Base-Emitter Turn-on Voltage (Note 9)	$V_{BE(on)}$	-	-0.8	-	V	I_C = -1A, V_{CE} = -2V
Transitional Frequency	f_T	100	-	-	MHz	I_C = -50mA, V_{CE} = -5V f = 50MHz
Input capacitance	C_{ibo}	-	225	-	pF	V_{EB} = -0.5V, f = 1MHz,
Output capacitance	C_{obo}	-	25	-	pF	V_{CB} = -10V, f = 1MHz,
Switching times	t_{on}	-	35	-	nS	I_C = -500mA, V_{CC} = -10V I_{B1} = -I_{B2} = -50mA
	t_{off}		400			

Notes: 9. Measured under pulsed conditions. Pulse width ≤ 300µs. Duty cycle ≤ 2%.

© Diodes Incorporated

Typical Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)



VCE(sat) v IC



VCE(sat) v IC



hFE v IC



VBE(sat) v IC



VBE(on) v IC

© Diodes Incorporated

Package Outline Dimensions

Please see AP02002 at http://www.diodes.com/datasheets/ap02002.pdf for latest version.



SOT89		
Dim	**Min**	**Max**
A	1.40	1.60
B	0.44	0.62
B1	0.35	0.54
C	0.35	0.44
D	4.40	4.60
D1	1.62	1.83
E	2.29	2.60
e	1.50 Typ	
H	3.94	4.25
H1	2.63	2.93
L	0.89	1.20
All Dimensions in mm		

Suggested Pad Layout

Please see AP02001 at http://www.diodes.com/datasheets/ap02001.pdf for the latest version.



Dimensions	Value (in mm)
X	0.900
X1	1.733
X2	0.416
Y	1.300
Y1	4.600
Y2	1.475
Y3	0.950
Y4	1.125
C	1.500

© Diodes Incorporated

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or

2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2012, Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

FCX789ATA