

# 8POS,MICRO MNL,RCPT HSG ✓ ACTIVE

MATE-N-LOK | Micro MATE-N-LOK


TE Part # 794617-8

TE Internal #: 794617-8

[View on TE.com >](#)



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Product Type: **Housing**

Housing Type: **Receptacle**

Connector System: **Wire-to-Board, Wire-to-Wire**

Number of Positions: **8**

Centerline (Pitch): **3 mm [ .118 in ]**

## Features

### Product Type Features

Product Type	Housing
Housing Type	Receptacle
Connector System	Wire-to-Board, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Contact Type	Socket

### Configuration Features

Number of Positions	8
Number of Rows	2
Row-to-Row Spacing	3 mm [.118 in]

### Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

### Contact Features

Contact Retention	Without
-------------------	---------

### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

### Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

### Housing Features

Centerline (Pitch)	3 mm [.118 in]
--------------------	----------------

UL Flammability Rating	UL 94V-0
------------------------	----------

Housing Color	Black
---------------	-------

Housing Material	Nylon 66/6
------------------	------------

### Usage Conditions

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

### Industry Standards

CSA Rating	Certified
------------	-----------

Glow Wire Rating	GWT 750°C (Without Flame), GWT 850°C (Flame ≤ 30 sec)
------------------	---

UL Rating	Recognized
-----------	------------

Agency/Standard Number	E28476
------------------------	--------

CSA File Number	LR7189
-----------------	--------

VDE Tested	Yes
------------	-----

Agency/Standard	CSA, UL
-----------------	---------

### Packaging Features

Packaging Method	Package
------------------	---------

Packaging Quantity	1
--------------------	---

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	ECHAによる現在の候補リスト: 2019年1月 (197) 候補リストの表記: 2019年1月(197)
--	--



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

### Compatible Parts




Rectangular Power Connectors(29)

### Also in the Series | Micro MATE-N-LOK



Connector Contacts(1)



Power Contacts(26)



Rectangular Power Connectors(711)

### Customers Also Bought



TE Part #91501-1  
CERTICRIMP 24-20 MICRO  
MNL



TE Part #843996-6  
TOOL, EXTRACTION  
RESET



TE Part #1-794617-0  
10POS,MICRO MNL,RCPT  
HSG



TE Part #1-794610-2  
MICRO MNL RPT CNT,LS  
PC 30AU L



TE Part #794610-1  
MICRO MNL RPT CNT,LS  
PC,TIN



TE Part #794617-6  
6POS,MICRO MNL,RCPT  
HSG



TE Part #104257-2  
03 MTE RCPT HSG SR  
LATCH .100



TE Part #104257-5  
06 MTE RCPT HSG SR  
LATCH .100



TE Part #794617-4  
4POS,MICRO MNL,RCPT  
HSG



TE Part #794606-1  
MICRO MNL RPT CNT  
STRIP 20-24

## Documents

### Product Drawings

8POS,MICRO MNL,RCPT HSG

English

### CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_794617-8\_J.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_794617-8\_J.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_794617-8\_J.3d\_stp.zip

English

### Datasheets & Catalog Pages

SOFT\_SHELL\_PIN\_AND\_SOCKET\_CONNECTORS\_CATALOG



English

[1773458-4\\_MICRO\\_MATE\\_N\\_LOK\\_CONNECTOR\\_SYSTEM\\_ORG](#)

English

---

**Product Specifications**

[Application Specification](#)

English

---

**Product Environmental Compliance**

[MD\\_794617-8\\_06112018924\\_dmtec](#)

English

[MD\\_794617-8\\_06112018924\\_dmtec](#)

English

---

**Agency Approvals**

[VDE Certificate](#)

English

[VDE Certificate](#)

English