


MSC030SDA120S Zero Recovery Silicon Carbide Schottky Diode

1 Product Overview



1.1 Features

The following are key features of the MSC030SDA120S device:

- No reverse recovery current/no forward recovery
- Low forward voltage
- Low leakage current
- Avalanche energy rated
- RoHS compliant

1.2 Benefits

The following are benefits of the MSC030SDA120S device:

- High switching frequency
- Low switching losses
- Low noise (EMI) switching
- Higher reliability systems
- Increased system power density

1.3 Applications

The MSC030SDA120S device is designed for the following applications:

- Power factor correction (PFC)
- Anti-parallel diode
 - Switch-mode power supply
 - Inverters/converters
 - Motor controllers
- Freewheeling diode
 - Switch-mode power supply
 - Inverters/converters
- Snubber/clamp diode

2 Device Specifications

This section details the specifications for the MSC030SDA120S device.

2.1 Absolute Maximum Ratings

The following table shows the absolute maximum ratings for the MSC030SDA120S device.

All ratings at $T_c = 25\text{ }^\circ\text{C}$ unless otherwise specified.

Table 1 • Absolute Maximum Ratings

Symbol	Parameter	Ratings	Unit	
V_R	Maximum DC reverse voltage	1200	V	
V_{RRM}	Maximum peak repetitive reverse voltage			
V_{RWM}	Maximum working peak reverse voltage			
I_F	Maximum DC forward current	$T_c = 25\text{ }^\circ\text{C}$	65	A
		$T_c = 135\text{ }^\circ\text{C}$	29	
		$T_c = 145\text{ }^\circ\text{C}$	24	
I_{FRM}	Repetitive peak forward surge current ($T_c = 25\text{ }^\circ\text{C}$, $t_p = 8.3\text{ ms}$, half sine wave)	92		
I_{FSM}	Non-repetitive forward surge current ($T_c = 25\text{ }^\circ\text{C}$, $t_p = 8.3\text{ ms}$, half sine wave)	165		
P_{tot}	Power dissipation	$T_c = 25\text{ }^\circ\text{C}$	259	W
		$T_c = 110\text{ }^\circ\text{C}$	112	
T_J, T_{STG}	Operating junction and storage temperature range	-55 to 175	$^\circ\text{C}$	
T_L	Lead temperature for 10 seconds	300		
E_{AS}	Single pulse avalanche energy (starting $T_J = 25\text{ }^\circ\text{C}$, $L = 0.22\text{ mH}$, peak $I_L = 30\text{ A}$)	100	mJ	

The following table shows the thermal and mechanical characteristics of the MSC030SDA120S device.

Table 2 • Thermal and Mechanical Characteristics

Symbol	Characteristic	Min	Typ	Max	Unit
$R_{\theta JC}$	Junction-to-case thermal resistance		0.4	0.58	$^\circ\text{C/W}$
Wt	Package weight		0.14		oz
			3.9		g

2.2 Electrical Performance

The following table shows the static characteristics of the MSC030SDA120S device.

Table 3 • Static Characteristics

Symbol	Characteristic	Test Conditions	Min	Typ	Max	Unit
V_F	Forward Voltage	$I_F = 30\text{ A}, T_J = 25\text{ }^\circ\text{C}$	1.5	1.8		V
		$I_F = 30\text{ A}, T_J = 175\text{ }^\circ\text{C}$		2.1		
I_{RM}	Reverse leakage current	$V_R = 1200\text{ V}, T_J = 25\text{ }^\circ\text{C}$	9	200		μA
		$V_R = 1200\text{ V}, T_J = 175\text{ }^\circ\text{C}$		150		
Q_C	Total capacitive charge	$V_R = 600\text{ V}, T_J = 25\text{ }^\circ\text{C}$		130		nC
C_J	Junction capacitance	$V_R = 400\text{ V}, T_J = 25\text{ }^\circ\text{C}, f = 1\text{ MHz}$		141		pF
	Junction capacitance	$V_R = 800\text{ V}, T_J = 25\text{ }^\circ\text{C}, f = 1\text{ MHz}$		105		

2.3 Performance Curves

This section shows the typical performance curves for the MSC030SDA120S device.

Figure 1 • Maximum Transient Thermal Impedance




Figure 2 • Forward Current vs. Forward Voltage




Figure 3 • Max Forward Current vs. Case Temp




Figure 4 • Max Power Dissipation vs. Case Temp




Figure 5 • Reverse Current vs. Reverse Voltage




Figure 6 • Total Capacitive Charge vs. Reverse Voltage





Figure 7 • Junction Capacitance vs. Reverse Voltage




3 Package Specification

This section shows the package specification for the MSC030SDA120S device.

3.1 Package Outline Drawing

This section shows the TO-268 package drawing of the MSC030SDA120S device.

Figure 8 • Package Outline Drawing



The following table lists the TO-268 dimensions and should be used in conjunction with the Package Outline Drawing.

Table 4 • TO-268 Dimensions

Symbol	Min (mm)	Max (mm)	Min (in.)	Max (in.)
A	4.90	5.10	0.193	0.201
B	15.85	16.20	0.624	0.638
C	18.70	19.10	0.736	0.752
D	1.00	1.25	0.039	0.049
E	13.80	14.00	0.543	0.551
F	13.30	13.60	0.524	0.535
G	2.70	2.90	0.106	0.114
H	1.15	1.45	0.045	0.057
I	1.95	2.21	0.077	0.087

Symbol	Min (mm)	Max (mm)	Min (in.)	Max (in.)
J	0.94	1.38	0.037	0.054
K	2.40	2.70	0.094	0.106
L	0.40	0.60	0.016	0.024
M	1.45	1.60	0.057	0.063
N	0.00	0.18	0.000	0.007
O	12.40	12.70	0.488	0.500
P	5.45 BSC (nom.)		0.215 BSC (nom.)	
Terminal 1	Cathode			
Terminal 2	Cathode			
Terminal 3	Anode			
Terminal 4	Cathode			



Microsemi Headquarters

One Enterprise, Aliso Viejo,
CA 92656 USA
Within the USA: +1 (800) 713-4113
Outside the USA: +1 (949) 380-6100
Sales: +1 (949) 380-6136
Fax: +1 (949) 215-4996
Email: sales.support@microsemi.com
www.microsemi.com

© 2019 Microsemi. All rights reserved. Microsemi and the Microsemi logo are trademarks of Microsemi Corporation. All other trademarks and service marks are the property of their respective owners.

Microsemi makes no warranty, representation, or guarantee regarding the information contained herein or the suitability of its products and services for any particular purpose, nor does Microsemi assume any liability whatsoever arising out of the application or use of any product or circuit. The products sold hereunder and any other products sold by Microsemi have been subject to limited testing and should not be used in conjunction with mission-critical equipment or applications. Any performance specifications are believed to be reliable but are not verified, and Buyer must conduct and complete all performance and other testing of the products, alone and together with, or installed in, any end-products. Buyer shall not rely on any data and performance specifications or parameters provided by Microsemi. It is the Buyer's responsibility to independently determine suitability of any products and to test and verify the same. The information provided by Microsemi hereunder is provided "as is, where is" and with all faults, and the entire risk associated with such information is entirely with the Buyer. Microsemi does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other IP rights, whether with regard to such information itself or anything described by such information. Information provided in this document is proprietary to Microsemi, and Microsemi reserves the right to make any changes to the information in this document or to any products and services at any time without notice.

Microsemi, a wholly owned subsidiary of Microchip Technology Inc. (Nasdaq: MCHP), offers a comprehensive portfolio of semiconductor and system solutions for aerospace & defense, communications, data center and industrial markets. Products include high-performance and radiation-hardened analog mixed-signal integrated circuits, FPGAs, SoCs and ASICs; power management products; timing and synchronization devices and precise time solutions, setting the world's standard for time; voice processing devices; RF solutions; discrete components; enterprise storage and communication solutions; security technologies and scalable anti-tamper products; Ethernet solutions; Power-over-Ethernet ICs and midspans; as well as custom design capabilities and services. Microsemi is headquartered in Aliso Viejo, California, and has approximately 4,800 employees globally. Learn more at www.microsemi.com.

053-4092 | January 2019 | Preliminary

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microchip:](#)

[MSC030SDA120S](#)