

# Switching Power Supply Type SPD 240W 3 phases DIN rail mounting



- Universal AC 3 phases input full range
- Installation on DIN rail 7.5 or 15mm
- PFC as standard
- High efficiency up to 90%
- Power ready output
- Parallel connection feature
- Compact dimensions
- UL, cUL listed and TUV/CE

## Product Description

The Switching power application where the supplies SPD series are specially designed to be used in all automation and performance are a must.

## Ordering Key

**SP D 24 240 3**

Model \_\_\_\_\_  
 Mounting (D= Din rail) \_\_\_\_\_  
 Output voltage \_\_\_\_\_  
 Output power \_\_\_\_\_  
 Input Type \_\_\_\_\_

Input type: 3 = three phase

## Approvals



## Output Performances

MODEL NO.	INPUT VOLTAGE	OUTPUT WATTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT	EFF. (min.)	EFF. (typ.)
<b>Single Output Models</b>						
<b>SPD24</b>	3ø 340~575 VAC	240 WATTS	+24 VDC	10 A	85%	90%
<b>SPD48</b>	3ø 340~575 VAC	240 WATTS	+48 VDC	5 A	89%	91%

## Output Data

<b>Line regulation</b>	± 1%	<b>Voltage fall time (I<sub>o,nom</sub>)</b>	150ms max
<b>Load regulation</b>		<b>Rated continuous loading</b>	
<b>Single mode</b>	±1%	<b>24V Model</b>	10A @ 24VDC/8.2A @ 28.5VDC
<b>Parallel mode</b>	±5%	<b>48V Model</b>	5A @ 48VDC/4.2A @ 56VDC
<small>When S/P switch is set to parallel, it is not possible to trim output voltage.</small>		<b>Reverse voltage</b>	
<b>Minimum load</b>	0A	<b>12V Model</b>	35VDC
<b>Turn on time (full resistive load)</b>		<b>24V Model</b>	63VDC
<b>VI nom, Io nom</b>	1000ms	<b>Capacitor load</b>	
<b>VI nom, Io nom 12V model with 7000 µF CAP</b>	1500ms	<b>VI nom Io nom 24V model</b>	7000µF
<b>Transient recovery time</b>	2ms	<b>Voltage rise time</b>	
<b>Ripple and noise</b>	100mVpp	<b>VI nom Io nom</b>	150ms
<b>Output voltage accuracy</b>	±1%	<b>VI nom, Io nom</b>	
<b>Temperature coefficient</b>	±0.03%/°C	<b>12V model with 7000µF CAP</b>	500ms
<b>Hold up time Vi</b>	20ms		

## Input Data

<b>Rated input voltage</b>	400 - 500VAC	<b>Inrush current</b>	
<b>Voltage range</b>		<i>Vi nom, Io nom</i>	<b>Typ.</b> 20A
<b>AC</b>	3PH AC IN 340 - 575Vac 47-63Hz 2PH AC IN 340 - 575Vac 47-63Hz (with 2P the output is derated to 75%)	<b>Max.</b>	25A
<b>DC</b>	480 - 820VDC	<b>Inrush current time</b>	
<b>Input current</b> ( <i>Vi: 400VAC / 500VAC, Io nom</i> )		<i>Vi nom, Io nom</i>	4 ~ 6 ms
<b>Typ.</b>	0.65A / 0.55A	<b>Power dissipation</b>	
<b>Rated input current</b> ( <i>Vi: 340VAC, Io nom</i> )		<b>24V Model</b>	30W
<b>Max.</b>	0.85A	<b>48V Model</b>	24W
		<b>Frequency range</b>	47-63Hz
		<b>Leakage current</b>	
		<b>Input-Output</b>	0.25mA
		<b>Input-FG</b>	3.5mA

## Controls and Protections

<b>Input fuse</b> <sup>1)</sup>	2A/600VAC internal/Phase	<b>Over voltage protection</b>	<b>VDC</b>	
<b>Output short circuit</b>	Hiccup mode		<b>Min.</b>	<b>Max.</b>
<b>Power ready output</b> (only 24V model) <b>on threshold</b>	≥17.6-19.4VDC	<b>24V Model</b>	30	33
<b>Electrical isolation</b>	500VDC	<b>48V Model</b>	60	68
<b>Contact rating at 60VDC</b>	0.3A	<b>Internal surge voltage protection</b> (IEC 61000-4-5)	Varistor	

1) Fuse not replaceable by user


## General Data (@ nominal line, full load, 25°C)

<b>Ambient temperature</b>	-40°C to +71°C	<b>MTB</b> (Bellcore issue 6 @ 40°C, GB)	
<b>Derating</b> (>61°C to +71°C)	2.5%/C	<b>24V Model</b>	488000 Hours
<b>Ambient humidity</b>	20 ~ 90% RH	<b>48V Model</b>	519000 Hours
<b>Storage</b>	-25°C to +85°C	<b>Case material</b>	Metal
<b>Protection degree</b>	IP20	<b>Dimensions LxWxD mm(inch)</b>	124 (4.88) x 89 (3.5) x 118.8 (4.68)
<b>Cooling</b>	Free air convection	<b>Weight</b>	1100 g
<b>Pollution degree</b>	2		

## Norms and Standards

<b>Vibration resistance</b>	meet IEC 60068-2-6 (Mounting by rail: 10-500Hz, 2G, along X, Y, Z each Axis, 60 min for each Axis)	<b>CQC</b>	GB4943.1-2011, GB9254-2008, GB17625.1-2012
<b>Shock resistance</b>	meet IEC 60068-2-27 (15G,11ms, 3 Axis, 6 faces, 3 times for each face)	<b>CE</b>	EN 61000-6-3, EN 55022 Class B, EN 61000-3-2, EN 61000-3-3, EN 61000-6-2, EN 55024, EN 61000-4-2 Level 4, EN 61000-4-3 Level 3, EN 61000-4-4 Level 4, EN 61000-4-5 Level 3, L/N-FG Level 4, EN 61000-4-6 Level 3, EN 61000-4-8 Level 4, EN 61000-4-11, ENV 50204 Level 2, EN 61204-3
<b>UL/cUL</b>	UL508 listed, UL60950-1, Recognized, ISA 12.12.01 (Class 1, Division 2, Groups A, B, C and D)		
<b>TUV</b>	EN 60950-1, CB scheme EN 61558-1, EN 61558-2- 17 (meet EN 60204)		


## Block Diagram




## Pin Assignment and Front Controls

Pin No.	Designation	Description
1, 2	V-	Negative output terminal
3, 4	V+	Positive output terminal
5	L3	Input terminals
6	L2	Input terminals
7	L1	Input terminals
8	$\oplus$	Ground this terminal to minimize high-frequency emissions
9	RDY	A normal open relay contact for DC ON level control
10	RDY	(Never connect except 24V model)
	DC ON	Operation indicator LED
	DC LO	DC LOW voltage indicator LED
	Vout ADJ	Trimmer-potentiometer for Vout adjustment
	S/P	Single / Parallel select switch



## Derating Diagram




## Typ. Efficiency Curve



## Typ. Current Limited Curve



## Mechanical Drawings mm (inches)



## Installation

### Ventilation and cooling

Normal convection All sides  
 25mm free space for  
 cooling is recommended.

### Screw connections

10-24AWG flexible or solid  
 cable 8mm stripping  
 recommend.

### Max. torque for screws terminals Input terminal Output terminal

1.008Nm (9.0lb-in)  
 0.616Nm (5.5lb-in)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Carlo Gavazzi:](#)

[SPD242403](#)