



Specification For Approval

承認書

客 戶 (Customer)			
品 名 (Product Name)	ECM		
機 種 (Model No.)			
客戶料號 (Customer Parts No.)			
供應商料號 (Supplier Model No.)	PVM9745-C40CS		
客戶承認簽章 Customer Approval Signature	In Charge	Checked	Approval

Revision History			
Version	Date	Description	Author
V 00	2018.08.23	Creation	VIVIAN

紘立企業有限公司 E-mail: vecot@veco.com.tw

Vanson Enterprise Co., Ltd. Tel: +886-2-2267 2389 Fax: +886-2-2267 2588

佛山鋅利電子有限公司 E-mail: vecof@vanson.net Office: fs_sales@veco.com.cn

Vanson Electronics(Nanhai)Co., Ltd. Tel: +86-757-8853 6828 Fax: +86-757-8853 6826

鴻立電子上海有限公司 E-mail: vesf@shtel.net.cn Office: vesi@shtel.net.cn

Vanson Electronics Shanghai Inc. Tel: +86-21-5958 5999 Fax: +86-21-5958 5678

重慶弘立電子有限公司 E-mail: cq_sales@veco.com.cn

Vanson Electronics (ChongQing)Co.,Ltd. Tel: +86-023-49521999 Fax: +86-023-49655990

合肥宏立電子有限公司 E-mail: reception@veco-hf.com

HeFei Vanson Electronics Inc. Tel: +86-551-568 9589 Fax: +86-551-568 9593



Design : VIVIAN Checked : VIVIAN Approval : VIVIAN

VECO VANSONIC ENTERPRISE CO.,LTD.

3F., No. 123, Zhongcheng Rd., Tucheng Dist., New Taipei City, Taiwan.

E-mail: vecot@veco.com.tw <http://www.veco.com.tw>
 TEL: +886-2-2267 2389 FAX: +886-2-2267 2588

1.	Name :	Omni directional FILM Electret Condenser Microphone																																
2.	Model No.	PVM9745-C40CS																																
3.	Scope :	Electrical Characteristics (Temperature =20±2°C Humidity=65±5%)																																
	Parameter	Symbol	Condition	Limits			Unit																											
				Min.	Center	Max.																												
3.1	Sensitivity	S	0dB=1V/Pa , at 1kHz	-42.5	-40	-37.5	dB																											
3.2	Output impedance	Z out	f=1kHz			2.2	KΩ																											
3.3	Current Consumption	I _{DSS}	V _{CC} =3.0 V,R _L =2.2KΩ			500	μA																											
3.4	Signal to Noise Ratio	S/N	at 1kHz S.P.L=1Pa (A-Weighted Curve)	58			dB																											
3.5	Decreasing Voltage	ΔS	V _{CC} =3.0V to2.0V			-3	dB																											
3.6	Operating Voltage			1.0		10	V																											
3.7	Maximum input S.P.L					110	dB																											
3.8	Typical Frequency Response Curve																																	
	Frequency Response			Microphone Response Tolerance Window																														
				<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: center;">Frequency(Hz)</th> <th style="text-align: center;">Lower Limit(dB)</th> <th style="text-align: center;">Upper Limit(dB)</th> </tr> </thead> <tbody> <tr><td style="text-align: center;">50</td><td style="text-align: center;">-6</td><td style="text-align: center;">+3</td></tr> <tr><td style="text-align: center;">100</td><td style="text-align: center;">-3</td><td style="text-align: center;">+3</td></tr> <tr><td style="text-align: center;">800</td><td style="text-align: center;">-3</td><td style="text-align: center;">+3</td></tr> <tr><td style="text-align: center;">1000</td><td style="text-align: center;">0</td><td style="text-align: center;">0</td></tr> <tr><td style="text-align: center;">1200</td><td style="text-align: center;">-3</td><td style="text-align: center;">+3</td></tr> <tr><td style="text-align: center;">3000</td><td style="text-align: center;">-3</td><td style="text-align: center;">+8</td></tr> <tr><td style="text-align: center;">5000</td><td style="text-align: center;">-3</td><td style="text-align: center;">+8</td></tr> <tr><td style="text-align: center;">10000</td><td style="text-align: center;">-8</td><td style="text-align: center;">+8</td></tr> </tbody> </table>				Frequency(Hz)	Lower Limit(dB)	Upper Limit(dB)	50	-6	+3	100	-3	+3	800	-3	+3	1000	0	0	1200	-3	+3	3000	-3	+8	5000	-3	+8	10000	-8	+8
Frequency(Hz)	Lower Limit(dB)	Upper Limit(dB)																																
50	-6	+3																																
100	-3	+3																																
800	-3	+3																																
1000	0	0																																
1200	-3	+3																																
3000	-3	+8																																
5000	-3	+8																																
10000	-8	+8																																
3.9	Measurement Circuit																																	
							R _L =2.2KΩ																											
							V _s =3.0V																											
							C=1μF																											



6. Drawing

9	FET		1	
8	P.C.B		1	
7	Copper ring		1	
6	Housing Chamber		1	
5	Electret Back		1	
4	Spacer		1	
3	Polarized Diaphragm		1	
2	Case	AL-Mg Alloy	1	
1	Felt	Non-weave cloth	1	
No.	Name	material	QTY	Remark





7. Temperature Conditions

Storage Temperature Range	Operation Temperature Range
$-40^{\circ}\text{C} \sim +75^{\circ}\text{C}$	$-40^{\circ}\text{C} \sim +75^{\circ}\text{C}$

8. Terminal Mechanical Strength

Terminal mechanical strength to be no interference in operation after pulled the terminal with 1kg strength for 1 minute.

<p>9.</p>	<p>Reliability Test</p> <p>After each of following test, the sensitivity of the microphone should be within $\pm 3\text{dB}$ of initial sensitivity after 3hours of conditioning at 20°C.</p> <p>1. Vibration Test</p> <p>Frequency : 10Hz~55Hz Amplitude : 1.52mm Change of Frequency : 1 octave/min 2 hours in each of axes</p> <p>2. High Temperature Test $+75^{\circ}\text{C}$ for 240 hours.</p> <p>3. Low Temperature Test -40°C for 240 hours.</p> <p>4. Humidity Test 90%~95%RH, $+60^{\circ}\text{C}$ for 240 hours.</p> <p>5. Thermal shocking test -40°C, 30 minutes \leftrightarrow $+75^{\circ}\text{C}$, 30 minutes, repeated 32 cycles \rightarrow room temperature, 3 hours.</p> <p>6. Temperature Cycles $-40^{\circ}\text{C} \leftrightarrow +20^{\circ}\text{C} \leftrightarrow +75^{\circ}\text{C} \leftrightarrow +20^{\circ}\text{C} \leftrightarrow -40^{\circ}\text{C}$ (2h) (0.5h) (2h) (0.1h) (2h) (0.5h) (2h) (0.5h) (2h) for 5 cycles.</p> <p>7. Packing Drop Test Height : 1.5m Procedure: 5 times from each of axes</p> <p>8. Electrostatic discharge Tested to IEC61000-4-2 level 3 :</p> <p>a) Contact discharge The microphone shall operate normally after 10 discharges to is 6KV DC and the discharge network is 150pF and 330Ω.</p> <p>b) Air discharge The microphone shall operate normally after 10 discharges to is 8KV DC and the discharge network is 150pF and 330Ω</p>
<p>10.</p>	<p>Soldering Condition</p> <p>1. We suggest using anti-static welding machine which can control soldering temperature automatically.</p> <p>2. Soldering temperature should be controlled under 320°C and soldering time for each terminal should be 1~2 sec..</p> <p>3. Microphone should be fixed on the metal block (heat sink), which has high radiation effects, and heat sink shall contact with MIC tightly.</p> <p>4. Microphone may easily be destroyed by the static electricity and the countermeasure for eliminating the static electricity shall be executed (worktable and human body shall be ground connection).</p>

<p>10.</p>	<p>Shape of heat sink</p> 				
	<p>Shape of hole at fixed part</p> 				
<p>11.</p>	<table border="1"> <thead> <tr> <th data-bbox="204 974 782 1019">Packing Introduction</th> <th data-bbox="782 974 1465 1019">Packing chart</th> </tr> </thead> <tbody> <tr> <td data-bbox="204 1019 782 2027"> <p>DIMENSION:(LENGTH*WIDTH *HEIGHT)</p> <ul style="list-style-type: none"> a) SMAIL PACKET 100mm*100mm*10mm b) MID PACKET: 205mm*105mm*50mm c) PAPER CASE: 550mm*230mm*235mm <p>EQUIPMENT</p> <ul style="list-style-type: none"> a) ADHENSIVE TAPE MACHINE b) AUTO PACKER <p>PACKING INTRODUCTION</p> <ul style="list-style-type: none"> c) 100PCS/ SMAIL PACKET d) 1000PCS/MID PACKET e) 20000PCS/PAPER CASE <p>QUANTITY INTRODUCTION</p> <ul style="list-style-type: none"> f) 1PC=0.7g g) NET WEIGHT : 14.0kg GROSS WEIGHT : 17.0kg <p>LABEL STIPULATION</p> <p>LABEL EVERY BOXES(SEE THE CHART) DIMENSIONSSHOULDBESEENEASILY.</p> </td> <td data-bbox="782 1019 1465 2027">  </td> </tr> </tbody> </table>	Packing Introduction	Packing chart	<p>DIMENSION:(LENGTH*WIDTH *HEIGHT)</p> <ul style="list-style-type: none"> a) SMAIL PACKET 100mm*100mm*10mm b) MID PACKET: 205mm*105mm*50mm c) PAPER CASE: 550mm*230mm*235mm <p>EQUIPMENT</p> <ul style="list-style-type: none"> a) ADHENSIVE TAPE MACHINE b) AUTO PACKER <p>PACKING INTRODUCTION</p> <ul style="list-style-type: none"> c) 100PCS/ SMAIL PACKET d) 1000PCS/MID PACKET e) 20000PCS/PAPER CASE <p>QUANTITY INTRODUCTION</p> <ul style="list-style-type: none"> f) 1PC=0.7g g) NET WEIGHT : 14.0kg GROSS WEIGHT : 17.0kg <p>LABEL STIPULATION</p> <p>LABEL EVERY BOXES(SEE THE CHART) DIMENSIONSSHOULDBESEENEASILY.</p>	
Packing Introduction	Packing chart				
<p>DIMENSION:(LENGTH*WIDTH *HEIGHT)</p> <ul style="list-style-type: none"> a) SMAIL PACKET 100mm*100mm*10mm b) MID PACKET: 205mm*105mm*50mm c) PAPER CASE: 550mm*230mm*235mm <p>EQUIPMENT</p> <ul style="list-style-type: none"> a) ADHENSIVE TAPE MACHINE b) AUTO PACKER <p>PACKING INTRODUCTION</p> <ul style="list-style-type: none"> c) 100PCS/ SMAIL PACKET d) 1000PCS/MID PACKET e) 20000PCS/PAPER CASE <p>QUANTITY INTRODUCTION</p> <ul style="list-style-type: none"> f) 1PC=0.7g g) NET WEIGHT : 14.0kg GROSS WEIGHT : 17.0kg <p>LABEL STIPULATION</p> <p>LABEL EVERY BOXES(SEE THE CHART) DIMENSIONSSHOULDBESEENEASILY.</p>	