

INTERCONNECTS

SERIES 800, 801, 802, 803 • .100" GRID (.030" DIA. PINS), LOW PROFILE HEADERS & VERSATILE SOCKETS • SINGLE & DOUBLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3




FIG. 4





FIG. 5

- Series 800 and 802 single and double row pin headers use MM #5016 pins. See page 215 for details
- Series 801 and 803 single and double row sockets use MM #1303 receptacles. See page 180 for details
- Series 801 and 803 receptacles use Hi-Rel, 6-finger BeCu #47 contact rated at 4.5 amps. Receptacles accept .030" diameter and .025" square pins. See page 256 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 800...002 Single Row Low Profile Pin Header																					
	800-XX-0__-10-002000 Specify number of pins ↑ 01-64																					
FIG. 2	Series 802...002 Double Row Low Profile Pin Header																					
	802-XX-0__-10-002000 Specify number of pins ↑ 04-64																					
<div style="display: flex; justify-content: space-around; align-items: center;"> <div style="border: 1px solid black; padding: 5px; background-color: #d4edda; color: #28a745; font-weight: bold;">RoHS-2 2011/65/EU</div> <div style="border: 1px solid black; border-radius: 50%; padding: 10px; text-align: center;">XX=Plating Code See Below</div> <div style="border: 1px solid black; border-radius: 50%; padding: 10px; text-align: center; font-size: small;">For Electrical, Mechanical & Environmental Data, See page 264</div> </div>																						
<table border="1" style="width: 100%; text-align: center;"> <thead> <tr> <th style="width: 15%;">SPECIFY PLATING CODE XX=</th> <th style="width: 15%;">10 ◆</th> <th style="width: 15%;">90</th> <th style="width: 15%;">40 ◆</th> <th style="width: 15%;"></th> </tr> </thead> <tbody> <tr> <td>Pin Plating </td> <td>10 μ" Au</td> <td>200 μ" Sn/Pb</td> <td>200 μ" Sn</td> <td></td> </tr> </tbody> </table>		SPECIFY PLATING CODE XX=	10 ◆	90	40 ◆		Pin Plating	10 μ" Au	200 μ" Sn/Pb	200 μ" Sn												
SPECIFY PLATING CODE XX=	10 ◆	90	40 ◆																			
Pin Plating	10 μ" Au	200 μ" Sn/Pb	200 μ" Sn																			
FIG. 3	Series 801...002 Low Profile Socket (short insulator)																					
	801-XX-0__-10-002000 Specify number of pins ↑ 01-64																					
FIG. 4	Series 801...012 Low Profile Socket (long insulator)																					
	801-XX-0__-10-012000 Specify number of pins ↑ 01-36																					
FIG. 5	Series 803...002 Double Row Low Profile Socket																					
	803-XX-0__-10-002000 Specify number of pins ↑ 04-72																					
<div style="display: flex; justify-content: space-around; align-items: center;"> <div style="border: 1px solid black; padding: 5px; background-color: #d4edda; color: #28a745; font-weight: bold;">RoHS-2 2011/65/EU</div> <div style="border: 1px solid black; border-radius: 50%; padding: 10px; text-align: center;">XX=Plating Code See Below</div> <div style="border: 1px solid black; border-radius: 50%; padding: 10px; text-align: center; font-size: small;">For Electrical, Mechanical & Environmental Data, See page 264</div> </div>																						
<table border="1" style="width: 100%; text-align: center;"> <thead> <tr> <th style="width: 15%;">SPECIFY PLATING CODE XX=</th> <th style="width: 15%;">91</th> <th style="width: 15%;">93</th> <th style="width: 15%;">99</th> <th style="width: 15%;">41 ◆</th> <th style="width: 15%;">43 ◆</th> <th style="width: 15%;">47 ◆</th> </tr> </thead> <tbody> <tr> <td>Sleeve (Pin) </td> <td>200 μ" Sn/Pb</td> <td>200 μ" Sn/Pb</td> <td>200 μ" Sn/Pb</td> <td>200 μ" Sn</td> <td>200 μ" Sn</td> <td>200 μ" Sn</td> </tr> <tr> <td>Contact (Clip) </td> <td>10 μ" Au</td> <td>30 μ" Au</td> <td>100 μ" Sn/Pb</td> <td>10 μ" Au</td> <td>30 μ" Au</td> <td>Au Flash</td> </tr> </tbody> </table>		SPECIFY PLATING CODE XX=	91	93	99	41 ◆	43 ◆	47 ◆	Sleeve (Pin)	200 μ" Sn/Pb	200 μ" Sn/Pb	200 μ" Sn/Pb	200 μ" Sn	200 μ" Sn	200 μ" Sn	Contact (Clip)	10 μ" Au	30 μ" Au	100 μ" Sn/Pb	10 μ" Au	30 μ" Au	Au Flash
SPECIFY PLATING CODE XX=	91	93	99	41 ◆	43 ◆	47 ◆																
Sleeve (Pin)	200 μ" Sn/Pb	200 μ" Sn/Pb	200 μ" Sn/Pb	200 μ" Sn	200 μ" Sn	200 μ" Sn																
Contact (Clip)	10 μ" Au	30 μ" Au	100 μ" Sn/Pb	10 μ" Au	30 μ" Au	Au Flash																

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[801-93-011-10-012000](#) [801-43-030-10-002000](#) [800-10-014-10-002000](#) [800-10-024-10-002000](#) [800-10-037-10-002000](#) [800-40-001-10-002000](#) [800-40-016-10-002000](#) [800-90-002-10-002000](#) [800-90-004-10-002000](#) [800-90-010-10-002000](#) [800-90-008-10-002000](#) [800-90-006-10-002000](#) [800-90-012-10-002000](#) [800-90-059-10-002000](#) [801-43-007-10-002000](#) [801-43-022-10-012000](#) [801-43-027-10-012000](#) [801-43-050-10-002000](#) [801-93-004-10-002000](#) [801-93-002-10-012000](#) [801-93-006-10-002000](#) [801-93-024-10-002000](#) [801-93-003-10-012000](#) [801-93-008-10-002000](#) [802-10-004-10-002000](#) [802-10-008-10-002000](#) [802-10-026-10-002000](#) [802-40-012-10-002000](#) [802-90-016-10-002000](#) [803-47-024-20-001000](#) [803-47-006-10-002000](#) [803-47-008-10-001000](#) [803-47-014-10-002000](#) [803-47-072-10-002000](#) [803-47-010-10-001000](#) [803-47-100-20-001000](#) [803-47-014-20-001000](#) [803-47-072-10-001000](#) [803-47-010-20-001000](#)