



Long Side Termination Thick Film Chip Resistors



LINKS TO ADDITIONAL RESOURCES



RCL e3 resistors series are the perfect choice for most fields of power measurement electronics where reliability, stability, power dissipation, and robust design is of major concern.

Typical applications include power electronics in automotive and industrial appliances.

FEATURES

- Enhanced power rating
- Long side terminations
- Enhanced thermal cycling performance
- AEC-Q200 qualified
- Material categorization: for definitions of compliance please see www.vishav.com/doc?99912



APPLICATIONS

- Automotive
- Industrial
- Commercial

TECHNICAL SPECIFICATION	S					
DESCRIPTION	RCL0406 e3	RCLO	612 e3	RCL1020 e3	RCL1218 e3	RCL1225 e3
Imperial size	0406	06	612	1020	1218	1225
Metric size code	RR1016M	RR1	632M	RR2550M	RR3246M	RR3263M
Resistance range	1 Ω to 1 M Ω ; jumper (0 Ω)	1 Ω to 39.2 k Ω ; jumper (0 Ω)	40.2 kΩ to 1 MΩ	1 Ω to 1 M Ω ; jumper (0 Ω)	1 Ω to 2.2 M Ω ; jumper (0 Ω)	1 Ω to 1 M Ω ; jumper (0 Ω)
Resistance tolerance			± 5 %;	±1%		
Temperature coefficient			± 200 ppm/K;	± 100 ppm/K		
Rated dissipation, P_{70} ⁽¹⁾	0.25 W	1.0 W ⁽²⁾	1.0 W ⁽²⁾	1.0 W	1.0 W	2.0 W ⁽²⁾
Operating voltage, U _{max.} AC _{RMS} /DC	50 V	200 V	75 V	200 V	200 V	200 V
Permissible film temperature, $\vartheta_{\text{F max.}}^{(1)}$			155	°C		
Operating temperature range			-55 °C to	+155 °C		
Max. resistance change at P_{70} for resistance range, $ \Delta R/R $ after:						
1000 h			≤ 1.0 %			
8000 h	≤ 2.0 %					
Permissible voltage against ambient (insulation):						
1 min, <i>U</i> _{ins}	100 V	100 V	100 V	300 V	300 V	300 V
Failure rate: FIT _{observed}	≤ 0.1 x 10 ⁻⁹ /h					


Notes

- (1) Please refer to APPLICATION INFORMATION below
- (2) Specified power rating requires dedicated mounting conditions to achieve the required thermal resistance

APPLICATION INFORMATION

When the resistor dissipates power, a temperature rise above the ambient temperature occurs, dependent on the thermal resistance of the assembled resistor together with the printed circuit board. The rated dissipation applies only if the permitted film temperature is not exceeded.

These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime.






TEMPERATURE COEFFICIENT AND RESISTANCE RANGE							
TYPE / SIZE	TCR	TOLERANCE	RESISTANCE	E-SERIES			
	± 200 ppm/K	± 5 %	1 Ω to 1 MΩ	E24			
RCL0406 e3	± 100 ppm/K	± 1 %	1 Ω to 1 MΩ	E24; E96			
	Jumper, I _{max.} = 4 A	≤ 10 mΩ	0 Ω	-			
	± 200 ppm/K	± 5 %	1 Ω to 1 MΩ	E24			
RCL0612 e3	± 100 ppm/K	± 1 %	1 Ω to 1 MΩ	E24; E96			
	Jumper, I _{max.} = 6 A	≤ 10 mΩ	0 Ω	-			
	± 200 ppm/K	± 5 %	1 Ω to 1 MΩ	E24			
RCL1020 e3	± 100 ppm/K	± 1 %	1 Ω to 1 MΩ	E24; E96			
	Jumper, I _{max.} = 10 A	≤ 10 mΩ	0 Ω	-			
	± 200 ppm/K	± 5 %	1 Ω to 2.2 MΩ	E24			
RCL1218 e3	± 100 ppm/K	± 1 %	1 Ω to 2.2 MΩ	E24; E96			
	Jumper, I _{max.} = 7 A	≤ 20 mΩ	0 Ω	-			
	± 200 ppm/K	± 5 %	1 Ω to 1 MΩ	E24			
RCL1225 e3	± 100 ppm/K	± 1 %	1 Ω to 1 MΩ	E24; E96			
	Jumper, $I_{\text{max.}} = 12 \text{ A}$	≤ 10 mΩ	0 Ω	-			

Note

• The temperature coefficient of resistance (TCR) is not specified for 0 Ω jumpers

PACKAGING										
TYPE / SIZE	CODE	QUANTITY	PACKAGING STYLE	WIDTH	PITCH	PACKAGING DIMENSIONS				
	EA = ET1	5000				Ø 180 mm/7"				
RCL0406 e3	EB = ET5	10 000			4 mm	Ø 285 mm/11.25"				
	EC = ET6	20 000	Paper tape acc. to IEC 60286-3, Type 1a	8 mm		Ø 330 mm/13"				
	EA = ET1	5000			4 mm	Ø 180 mm/7"				
RCL0612 e3	EB = ET5	10 000				Ø 285 mm/11.25"				
	EC = ET6	20 000				Ø 330 mm/13"				
RCL1020 e3	EF = E02	4000			4 mm					
RCL1218 e3	EK = ET9	4000	Blister tape acc. to	12 mm	4 mm	Ø 180 mm/7"				
RCL1225 e3	EG = E67	2000	IEC 60286-3, Type 2a		8 mm	ווווווויסו ש ו				
NOL 1220 63	EH = E82	4000]		4 mm					





Vishay Draloric

DESCRIPTION

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. A cermet film layer and a glass-over are deposited on a high grade (Al_2O_3) ceramic substrate with its prepared inner contacts on both sides. A special laser is used to achieve the target value by smoothly fine trimming the resistive layer without damaging the ceramics. The resistor elements are covered by a protective coating designed for electrical, mechanical and climatic protection. The terminations receive a final pure tin on nickel plating.

The result of the determined production is verified by an extensive testing procedure on 100 % of the individual chip resistors. Only accepted products are laid directly into the tape in accordance with **IEC 60286-3 Type 1a and Type 2a** ⁽¹⁾.

ASSEMBLY

The resistors are suitable for processing on automatic SMD assembly systems. They are suitable for automatic soldering using wave, reflow or vapor phase as shown in **IEC 61760-1** ⁽¹⁾. The encapsulation is resistant to all cleaning solvents commonly used in the electronics industry, including alcohols, esters and aqueous solutions. The suitability of conformal coatings, potting compounds and their processes, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system.

The resistors are RoHS-compliant, the pure tin plating provides compatibility with lead (Pb)-free and lead-containing soldering processes. Solderability is specified for 2 years after production or requalification. The permitted storage time is 20 years. The immunity of the plating against tin whisker growth has been proven under extensive testing.

MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances:

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein (2)
- The Global Automotive Declarable Substance List (GADSL) (3)
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) (4) for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see www.vishay.com/how/leadfree.

Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at www.vishay.com/doc?49037.

APPROVALS

The resistors are qualified according to AEC-Q200. Where applicable, the resistors are tested in accordance with **EN 140401-802** which refers to **EN 60115-1**, **EN 60115-8** and the variety of environmental test procedures of the **IEC 60068** (1) series.

RELATED PRODUCTS

The RCA-LS e3, Sulfur Resistant, Long Side Termination Thick Film Chip Resistors series is designed for harsh environment applications. For ordering RCA-LS e3 products please refer to latest edition of datasheet, www.vishav.com/doc?20060.


Notes

- (1) The quoted IEC standards are also released as EN standards with the same number and identical contents
- (2) The IEC 62474 list of declarable substances is maintained in a dedicated database, which is available at http://std.iec.ch/iec62474
- (3) The Global Automotive Declarable Substance List (GADSL) is maintained by the American Chemistry Council and available at www.gadsl.org
- (4) The SVHC list is maintained by the European Chemical Agency (ECHA) and available at http://echa.europa.eu/candidate-list-table




FUNCTIONAL PERFORMANCE

Single Pulse (1)




Maximum pulse load, single pulse; applicable if $\bar{P} \to 0$ and n < 1000 and $\hat{U} \le \hat{U}_{max}$; for permissible resistance change equivalent to 8000 h operation

Continuous Pulse (1)



Maximum pulse load, continuous pulses; applicable if $\bar{P} \leq P\left(\vartheta_{\text{amb}}\right)$ and $\hat{U} \leq \hat{U}_{\text{max}}$; for permissible resistance change equivalent to 8000 h operation

Pulse Voltage (1)




Maximum pulse voltage, single and continuous pulses; applicable if $\hat{P} \leq \hat{P}_{max}$; for permissible resistance change equivalent to 8000 h operation

Note

(1) Pulse diagram under review to match upgraded rated dissipation and operating voltage

www.vishay.com

Derating





Vishay Draloric

TESTS AND REQUIREMENTS

All executed tests are carried out in accordance with the following specifications:

EN 60115-1, generic specification

EN 60115-8 (successor of EN 140400), sectional specification

EN 140401-802, detail specification

IEC 60068-2-xx, test methods

The parameters stated in the Test Procedures and Requirements table are based on the required tests and permitted limits of EN 140401-802. The table presents only the most important tests, for the full test schedule refer to the documents listed above. However, some additional tests and a number of improvements against those minimum requirements have been included.

The testing also covers most of the requirements specified by EIA/IS-703 and JIS-C-5201-1.

The tests are carried out under standard atmospheric conditions in accordance with IEC 60068-1, 4.3, whereupon the following values are applied:

Temperature: 15 °C to 35 °C Relative humidity: 25 % to 75 %

Air pressure: 86 kPa to 106 kPa (860 mbar to 1060 mbar).

EN 60115-1 CLAUSE	TEST		PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (△ <i>R</i>)		
	l		Stability for product types:	STABILITY CLASS 1 OR BETTER	STABILITY CLASS 2 OR BETTER	
			RCL e3	1 Ω to	2.2 MΩ	
4.5	-	Resistance	-	±1%	± 5 %	
4.8	-	Temperature coefficient	(20 / -55 / 20) °C and (20 / 155 / 20) °C	± 100 ppm/K	± 200 ppm/K	
4.25.1	_	Endurance at 70 °C	$U = \sqrt{P_{70} \times R}$ or $U = U_{\text{max.}}$; whichever is the less severe; 1.5 h on; 0.5 h off			
4.20.1	- Elidurance at 70		70 °C; 1000 h	± (1 % R + 0.05 Ω)	± (2 % R + 0.1 Ω)	
			70 °C; 8000 h	± (2 % R + 0.1 Ω)	± (4 % R + 0.1 Ω)	
4.25.3	-	Endurance at upper category temperature	155 °C, 1000 h	± (1 % R + 0.05 Ω)	± (2 % R + 0.1 Ω)	
4.24	78 (Cab)	Damp heat, steady state	(40 ± 2) °C; 56 days; (93 ± 3) % RH;	± (1 % R + 0.05 Ω)		
4.37	67 (Cy)	Damp heat, steady state, accelerated	(85 ± 2) °C; (85 ± 5) % RH; $U = \sqrt{0.1 \times P_{85} \times R} \le 100 \text{ V};$ 1000 h	± (1 % R + 0.05 Ω)	± (2 % R + 0.1 Ω)	
4.23	-	Climatic sequence:	-			
4.23.2	2 (Bb)	dry heat	125 °C; 16 h			
4.23.3	30 (Db)	damp heat, cyclic	55 °C; 24 h; ≥ 90 % RH; 1 cycle			
4.23.4	1 (Ab)	cold	-55 °C; 2 h	± (1 % R + 0.05 Ω)	± (2 % R + 0.1 Ω)	
4.23.5	13 (M)	low air pressure	8.5 kPa; 2 h; (25 ± 10) °C	_ (1 /071 1 0.00 22)	_ (= /0// 1 0.1 22)	
4.23.6	30 (Db)	damp heat, cyclic	55 °C; 24 h; ≥ 90 % RH; 5 cycles			
4.23.7	-	DC load	$U = \sqrt{P_{70} \times R} \le U_{\text{max.}}$ 1 min			
-	1 (Aa)	Cold	-55 °C; 2 h	± (0.25 % R + 0.05 Ω)	± (0.5 % R + 0.05 Ω)	
4.19	14 (Na)	Rapid change of temperature	30 min at -55 °C and 30 min at 125 °C; 1000 cycles	± (1 % R + 0.05 Ω)		



Vishay Draloric


EN 60115-1 CLAUSE	IEC 60068-2 ⁽¹⁾ TEST METHOD	TEST	PROCEDURE		EMENTS CHANGE (∆ <i>R</i>)
			Stability for product types:	STABILITY CLASS 1 OR BETTER	STABILITY CLASS 2 OR BETTER
			RCL e3	1 Ω to	2.2 MΩ
4.13	-	Short time overload	$U = 2.5 \times \sqrt{P_{70} \times R} \le 2 \times U_{\text{max.}};$ whichever is the less severe; 5 s	± (2 % R	+ 0.05 Ω)
4.27	-	Single pulse high voltage overload	Severity no. 4: $U=10 \times \sqrt{P_{70} \times R}$ or $U=2 \times U_{\text{max.}}$; whichever is the less severe; 10 pulses 10 µs/700 µs		+ 0.05 Ω) e damage
4.39	-	Periodic electric overload	$U = \sqrt{15 \times P_{70} \times R}$ or $U = 2 \times U_{\text{max.}}$; whichever is the less severe; 0.1 s on; 2.5 s off; 1000 cycles	\pm (1 % R + 0.05 Ω) no visible damage	
4.38	-	Electrostatic discharge (human body model)	IEC 61340-3-1 ⁽¹⁾ ; 3 pos. + 3 neg. discharges; ESD voltage acc. to the size	± (1 % R + 0.05 Ω)	
4.22	6 (Fc)	Vibration	Endurance by sweeping; 10 Hz to 2000 Hz; no resonance; amplitude \leq 1.5 mm or \leq 200 m/s ² ; 7.5 h	± (0.25 % <i>R</i> + 0.05 Ω) no visible damage	\pm (0.5 % R + 0.05 Ω) no visible damage
4.17	58 (Td)	Solderability	Solder bath method; Sn60Pb40 non-activated flux; (235 ± 5) °C; (2 ± 0.2) s Solder bath method; Sn96.5Ag3Cu0.5 non-activated flux; (245 ± 5) °C; (3 ± 0.3) s	Good tinning (≥ 95 % covered) no visible damage	
4.18	58 (Td)	Resistance to soldering heat	Solder bath method (260 ± 5) °C; (10 ± 1) s	± (0.25 % R + 0.05 Ω)	± (0.5 % R + 0.05 Ω)
4.29	45 (XA)	Component solvent resistance	Isopropyl alcohol; +50 °C; method 2	No visible damage	
4.32	21 (Uu ₃)	Shear (adhesion)	17.7 N	No visible damage	
4.33	21 (Uu ₁)	Substrate bending	Depth 2 mm; 3 times	\pm (0.25 % R + 0.05 Ω) no visible damage, no open circuit in bent positio	
4.7	-	Voltage proof	$U = 1.4 \times U_{ins}$; 60 s		or breakdown
4.35	-	Flammability, needle flame test	IEC 60695-11-5 ⁽¹⁾ ; 10 s	No burning after 30 s	

Note

⁽¹⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents




DIMENSIONS



DIMENSIONS AND MASS										
TYPE / SIZE	L (mm)	W (mm)	H (mm)	T1 (mm)	T2 (mm)	MASS (mg)				
RCL0406 e3	1.0 ± 0.10	1.6 ± 0.10	0.35 ± 0.10	0.2 +0.10 / -0.15	0.2 ± 0.10	2				
RCL0612 e3	1.6 ± 0.20	3.2 ± 0.20	0.55 ± 0.10	0.35 ± 0.15	0.25 ± 0.15	11				
RCL1020 e3	2.5 ± 0.20	5.0 ± 0.20	0.55 ± 0.10	0.38 ± 0.15	0.25 ± 0.15	25.5				
RCL1218 e3	3.2 +0.10 / -0.20	4.6 ± 0.15	0.55 ± 0.05	0.45 ± 0.20	0.4 ± 0.20	29.5				
RCL1225 e3	3.2 ± 0.20	6.3 ± 0.20	0.70 ± 0.10	0.8 ± 0.20	0.4 ± 0.20	55				

SOLDER PAD DIMENSIONS



RECOMMENDED SOLDER PAD DIMENSIONS									
	WAVE SOLDERING				REFLOW SOLDERING				
TYPE / SIZE	G (mm)	Y (mm)	X (mm)	Z (mm)	G (mm)	Y (mm)	X (mm)	Z (mm)	
RCL0406 e3	0.30	0.80	1.95	1.90	0.35	0.60	1.75	1.55	
RCL0612 e3	0.50	1.20	3.70	2.90	0.60	1.00	3.50	2.60	
RCL1020 e3	1.30	1.25	5.50	3.80	1.30	1.10	5.25	3.50	
RCL1218 e3	1.80	1.30	5.10	4.40	1.90	1.10	4.90	4.10	
RCL1225 e3	1.10	1.80	6.80	4.70	1.20	1.60	6.60	4.40	

Notes

- The given solder pad dimensions reflect the considerations for board design and assembly as outlined e.g in standards IEC 61188-5-x (1) or in publication IPC-7351.
- Still, the given solder pad dimensions will be found adequate for most general applications
- (1) The quoted IEC standards are also released as EN standards with the same number and identical contents



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

RCL0612178KFKEA	RCL061217K4FKEA	RCL061217K8FKEA	RCL061217R4FKEA	RCL061217R8FKEA
RCL0612180RFKEA	RCL0612182KFKEA	RCL0612182RFKEA	RCL0612187KFKEA	RCL0612187RFKEA
RCL061218K0FKEA	RCL061218K7FKEA	RCL061218R0FKEA	RCL061218R2FKEA	RCL061218R7FKEA
RCL0612191KFKEA	RCL0612191RFKEA	RCL0612196KFKEA	RCL0612196RFKEA	RCL061219K6FKEA
RCL061219R1FKEA	RCL061219R6FKEA	RCL06121K00FKEA	RCL06121K02FKEA	RCL06121K05FKEA
RCL06121K07FKEA	RCL06121K10FKEA	RCL06121K15FKEA	RCL06121K20FKEA	RCL06121K21FKEA
RCL06121K30FKEA	RCL06121K33FKEA	RCL06121K37FKEA	RCL06121K40FKEA	RCL06121K43FKEA
RCL06121K50FKEA	RCL06121K58FKEA	RCL06121K60FKEA	RCL06121K62FKEA	RCL06121K74FKEA
RCL06121K80FKEA	RCL06121K82FKEA	RCL06121K96FKEA	RCL06121M00FKEA	RCL06121R00FKEA
RCL06121R02FKEA	RCL06121R05FKEA	RCL06121R10FKEA	RCL06121R18FKEA	RCL06121R20FKEA
RCL06121R24FKEA	RCL06121R27FKEA	RCL06121R37FKEA	RCL06121R40FKEA	RCL06121R43FKEA
RCL06121R47FKEA	RCL06121R50FKEA	RCL06121R54FKEA	RCL06121R60FKEA	RCL06121R62FKEA
RCL06121R69FKEA	RCL06121R74FKEA	RCL06121R78FKEA	RCL06121R80FKEA	RCL06121R82FKEA
RCL0612200RFKEA	RCL0612205KFKEA	RCL0612205RFKEA	RCL061220K0FKEA	RCL061220K5FKEA
RCL061220R0FKEA	RCL0612210KFKEA	RCL0612210RFKEA	RCL0612215KFKEA	RCL061221K0FKEA
RCL061221R5FKEA	RCL0612220KFKEA	RCL0612220RFKEA	RCL0612221KFKEA	RCL0612221RFKEA
RCL0612226RFKEA	RCL061222K0FKEA	RCL061222K1FKEA	RCL061222K6FKEA	RCL061222R0FKEA
RCL061222R1FKEA	RCL061222R6FKEA	RCL0612232RFKEA	RCL061223K2FKEA	RCL061223R7FKEA
RCL0612240RFKEA	RCL0612243KFKEA	RCL0612243RFKEA	RCL0612249RFKEA	RCL061224K0FKEA
RCL061224K3FKEA	RCL061224R0FKEA	RCL061224R3FKEA	RCL0612255KFKEA	RCL0612255RFKEA