

Sn96%,		Yes	Yes
CUSTOMER	TERMINAL	RoHS	LEAD(Pb)-FREE







## ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER		TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2	@20°C	1.32 ohms max.
D.C. RESISTANCE	2-3	@20°C	1.32 ohms max.
D.C. RESISTANCE	7-6	@20°C	0.03 ohms max.
INDUCTANCE	7-6	10kHz, 100mVAC, Ls	20.00uH min.
LEAKAGE INDUCTANCE	7-6	tie(1+2+3), 100kHz, 100mVAC, Ls	150.0nH max.
DIELECTRIC	1-7	3000VAC, 1 second	-
TURNS RATIO		(1-2):(7-6)	4.2:1, ±2%
TURNS RATIO		(2-3):(7-6)	4.2:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	4 -
		Method: Tape & Reel	<del>(A)</del> - <del>(-)</del> -
		PKG-0409	$\Psi$
6B	10/18	www.we-online.com/midcom	CONVENTION PLACEMENT
6A	8/18	SEE REVISION SHEET FOR	REVISION LEVEL



Tolerances unless otherwise specified: Decimals: ±.005 [.13] Footprint: ±.005 [.13] Angles: ±1° Fractions: ±1/64

This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE

## **TRANSFORMER**

eiSos p/n: **750343804** 

PART NO.

750343804

ROHS SPECIFICATION SHEET 1 OF 1

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Wurth Elektronik: 750343804