

Metal Film Resistors

High Power & Flame-Proof Type

Ultra Miniature Style [FMP Series]



INTRODUCTION

The FMP Series Metal Film High Power Resistors are manufactured using a vacuum sputtering system to deposit multiple layers of mixed metal alloys and passivative materials onto a carefully treated high grade ceramic substrate. After a helical groove has been cut in the resistive layer; tinned connecting leads of electrolytic copper are welded to the end-caps. The resistors are coated with layers of pink color lacquer.

FEATURES

Power Rating	1/2W, 1W, 2W, 3W, 4W
Resistance Tolerance	±1%, ±5%
T.C.R.	±100ppm/°C
Flameproof Multi-layer Coating Meets	UL-94V-0
Flameproof Feature Meets Overload Test	UL-1412

DERATING CURVE

For resistors operated in ambient temperatures above 70°C, power rating must be derated in accordance with the curve below.



DIMENSIONS

Unit: mm



STYLE	DIMENSION			
	L	øD	H	ød
Ultra Miniature				
FMP-50	3.4±0.3	1.9±0.2	28±2.0	0.45±0.05
FMP100	6.3±0.5	2.4±0.2	28±2.0	0.55±0.05
FMP200	9.0±0.5	3.9±0.3	26±2.0	0.55±0.05
FMP3WS	11.5±1.0	4.5±0.5	35±2.0	0.8±0.05
FMP300	15.5±1.0	5.0±0.5	33±2.0	0.8±0.05
FMP4WV	17.0±1.0	7.5±0.5	32±2.0	0.8±0.05

Note:

ELECTRICAL CHARACTERISTICS

STYLE	FMP-50	FMP100	FMP200	FMP3WS	FMP300	FMP4WV
Power Rating at 70°C	1/2W	1W	2W	3W		4W
Maximum Working Voltage	200V	350V	500V		750V	
Maximum Overload Voltage	400V	600V	700V		1,000V	
Voltage Proof on Insulation	300V	500V				
Resistance Range	1Ω - 10MΩ & 0Ω for E24 & E96 series value					
Operating Temp. Range	-55°C to +155°C					
Temperature Coefficient	±100ppm/°C					

Note: Special value is available on request

ENVIRONMENTAL CHARACTERISTICS

PERFORMANCE TEST	TEST METHOD	APPRAISE
Short Time Overload	IEC 60115-1 4.13 2.5 times RCWV for 5 Sec.	±0.5%+0.05Ω
Voltage Proof on Insulation	IEC 60115-1 4.7 in V-block for 60 Sec., test voltage by type	By type
Temperature Coefficient	IEC 60115-1 4.8 -55°C to +155°C	By type
Insulation Resistance	IEC 60115-1 4.6 in V-block for 60 Sec.	>1,000MΩ
Solderability	IEC 60115-1 4.17 235±5°C for 3±0.5 Sec.	95% Min. coverage
Solvent Resistance of Marking	IEC 60115-1 4.30 IPA for 5±0.5 Min. with ultrasonic	No deterioration of coatings and markings
Robustness of Terminations	IEC 60115-1 4.16 Direct load for 10 Sec. in the direction of the terminal leads	≥2.5kg (24.5N)
Periodic-pulse Overload	IEC 60115-1 4.39 4 times RCWV 10,000 cycles (1 Sec. on, 25 Sec. off)	±1.0%+0.05Ω
Damp Heat Steady State	IEC 60115-1 4.24 40±2°C, 90-95% RH for 56 days, loaded with 0.1 times RCWV	±2.0%+0.05Ω
Endurance at 70°C	IEC 60115-1 4.25 70±2°C at RCWV for 1,000 Hr. (1.5 Hr. on, 0.5 Hr. off)	±2.0%+0.05Ω
Temperature Cycling	IEC 60115-1 4.19 -55°C ⇌ Room Temp. ⇌ +155°C ⇌ Room Temp. (5 cycles)	±1.0%+0.05Ω
Resistance to Soldering Heat	IEC 60115-1 4.18 260±3°C for 10±1 Sec., immersed to a point 3±0.5mm from the body	±0.25%+0.05Ω
Accidental Overload Test	IEC 60115-1 4.26 4 times RCWV for 1 Min.	No evidence of flaming or arcing

Note: RCWV(Rated Continuous Working Voltage) = $\sqrt{\text{Power Rating} \times \text{Resistance Value}}$ or Max. working voltage listed above, whichever less.

Revision: 201304



EXPLANATIONS OF ORDERING CODE

MFR	-12	F	T	F	52-	100R
Code 1 - 3 Series Name See Index	Code 4 - 6 Power Rating -05 = \varnothing d0.5mm -06 = \varnothing d0.6mm -07 = \varnothing d0.7mm -08 = \varnothing d0.8mm -10 = \varnothing d1.0mm -14 = \varnothing d1.4mm -12 = 1/6W -25 = 1/4W 25S = 1/4WS -50 = 1/2W 50S = 1/2WS 100 = 1W 1WS = 1WS 200 = 2W 2WS = 2WS 204 = 0.4W 207 = 0.6W 300 = 3W 3WS = 3WS 3WM = 3WM 400 = 4W 500 = 5W 5WS = 5WS 5SS = 5WSS 700 = 7W 7WS = 7WS 10A = 10W 20A = 20W 30A = 30W 40A = 40W 50A = 50W 10S = 10WS 15A = 15W 25A = 25W 10B = 100W 25B = 250W	Code 7 Tolerance P = ± 0.02 % A = ± 0.05 % B = ± 0.1 % C = ± 0.25 % D = ± 0.5 % F = ± 1 % G = ± 2 % J = ± 5 % K = ± 10 % - = Base on Spec.	Code 8 Packing Style T = Tape/Box R = Tape/Reel B = Bulk	Code 9 Temperature Coefficient of Resistance - = Base on Spec. A = ± 5 ppm/ $^{\circ}$ C B = ± 10 ppm/ $^{\circ}$ C C = ± 15 ppm/ $^{\circ}$ C S = ± 20 ppm/ $^{\circ}$ C D = ± 25 ppm/ $^{\circ}$ C E = ± 50 ppm/ $^{\circ}$ C F = ± 100 ppm/ $^{\circ}$ C G = ± 200 ppm/ $^{\circ}$ C H = ± 250 ppm/ $^{\circ}$ C I = ± 300 ppm/ $^{\circ}$ C J = ± 350 ppm/ $^{\circ}$ C	Code 10 - 12 Forming Type 26- = 26mm 52- = 52.4mm 73- = 73mm 81- = 81mm 91- = 91mm F = F Type FK = FK Type FKK = FKK Type FFK = F-form Kink M = M-Type Forming MB = M-form W/flat MT = MT Type Forming MR = MR Type AV = AVIsert PN = PANAsert	Code 13 - 17 Resistance Value 0R1 = 0.1 100R = 100 10K = 10,000 10M = 10,000,000

EXCEPTION:

• Cement series:

<Code 8>: Special packing style code

B: Bulk with wirewound or metal oxide sub-assembly for resistance value

W: Bulk with ceramic based wirewound sub-assembly for resistance value

M: Bulk with metal oxide sub-assembly for resistance value

F: Bulk with Fiberglass based wirewound sub-assembly for resistance value

<Code 10-12>: Without forming code

Example: **SQP500JB-10R**

• JPW series:

<Code 13-17>: without resistance value code

Example: **JPW-06-T-52-**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Yageo:

[FMP100JR-52-12K](#) [FMP100JR-52-220R](#) [FMP100JR-52-3K3](#) [FMP200FRF52-130K](#) [FMP200FRF52-154K](#)
[FMP200FRF52-220R](#) [FMP200FRF52-249R](#) [FMP200FRF52-274K](#) [FMP200FRF52-332K](#) [FMP200FRF52-390K](#)
[FMP200FRF52-715K](#) [FMP200FRF52-75K](#) [FMP200JR-52-180K](#) [FMP200JR-52-1M](#) [FMP200JR-52-200K](#) [FMP200JR-](#)
[52-220K](#) [FMP200JR-52-2K7](#) [FMP200JR-52-390R](#) [FMP200JR-52-470R](#) [FMP300FTF73-100K](#) [FMP300FTF73-100R](#)
[FMP300FTF73-47K](#) [FMP300JR-73-22R](#) [FMP100JR-52-470K](#) [FMP200JR-52-1K2](#) [FMP100JR-52-27K](#)
[FMP300FRF73-1K5](#) [FMP300FRF73-49K9](#) [FMP300FRF73-48K7](#) [FMP300FRF73-100K](#) [FMP300FRF73-6K65](#)
[FMP100JR-52-1K](#) [FMP100JR-52-4R7](#) [FMP100JR-52-22K](#) [FMP100JR-52-22R](#) [FMP100JR-52-47R](#) [FMP200JR-52-](#)
[7K5](#) [FMP200JR-52-820K](#) [FMP100JR-52-270R](#) [FMP100JR-52-2K2](#) [FMP100JR-52-47K](#) [FMP100JR-52-4K7](#)
[FMP200JR-52-39K](#) [FMP100JR-52-100K](#) [FMP200JR-52-22R](#) [FMP200JR-52-4R7](#) [FMP200JR-52-100K](#) [FMP200JR-](#)
[52-4K7](#) [FMP200JR-52-33R](#) [FMP100JR-52-390R](#) [FMP100JR-52-56K](#) [FMP200JR-52-120K](#) [FMP200JR-52-15K](#)
[FMP200JR-52-330R](#) [FMP200JR-52-430R](#) [FMP200JR-52-560R](#) [FMP100JR-52-68R](#) [FMP200JR-52-10K](#) [FMP200JR-](#)
[52-1K5](#) [FMP200JR-52-270R](#) [FMP100JR-52-1M](#) [FMP100JR-52-560R](#) [FMP200JR-52-47K](#) [FMP200JR-52-8K2](#)
[FMP100JR-52-10R](#) [FMP200JR-52-47R](#) [FMP200JR-52-12K](#) [FMP100JR-52-1K5](#) [FMP200JR-52-18K](#) [FMP200JR-52-](#)
[68K](#) [FMP200FRF52-100R](#) [FMP100JR-52-1K2](#) [FMP200JR-52-43R](#) [FMP100JR-52-18K](#) [FMP200JR-52-150K](#)
[FMP100JR-52-180R](#) [FMP100JR-52-82K](#) [FMP200JR-52-120R](#) [FMP100JR-52-16K](#) [FMP200JR-52-22K](#) [FMP200JR-](#)
[52-27R](#) [FMP200JR-52-30K](#) [FMP100JR-52-100R](#) [FMP200JR-52-1K8](#) [FMP100JR-52-150K](#) [FMP100JR-52-270K](#)
[FMP100JR-52-33K](#) [FMP100JR-52-820K](#) [FMP200JR-52-27K](#) [FMP200JR-52-56R](#) [FMP200JR-52-820R](#) [FMP200JR-](#)
[52-18R](#) [FMP200JR-52-150R](#) [FMP200JR-52-180R](#) [FMP200JR-52-2K2](#) [FMP200JR-52-5K1](#) [FMP100JR-52-68K](#)
[FMP200JR-52-220R](#) [FMP200JR-52-270K](#) [FMP100JR-52-180K](#)