

**Magnetically Operated Switches  
Reed Switches**

- Very neat, compact, cylindrical units
- LED indicator on QM/34 models
- Suitable for use with our ranges of magnet piston cylinders

**Technical Data**
**Operation:**

QM/33 Normally open  
 QM/34 Normally open with LED (yellow)

**Switching Voltage:**

10 to 240 V a.c./d.c. QM/33  
 10 to 30 V d.c. QM/34

**Switching Current (see graph overleaf):**

1,5 A maximum QM/33  
 1 A maximum QM/34

**Switching Power:**

50 W/50 VA maximum QM/33  
 25 W maximum QM/34

**Note:** Switch life may be greatly reduced when switching reactive loads, e.g. solenoid, relay, and long cable runs. In such cases the fitment of appropriate voltage/current limiting devices should be considered.

**Contact Resistance:**

100 mΩ

**Response Time:**

2 ms QM/33  
 0,5 ms QM/34

**Operating Temperature:**

-20°C to +80°C

**Protection Rating:**

IP 66 (DIN 40050)

**Shock Resistance:**

50 g (during 11 ms)

**Vibration Resistance:**

35 g (50 to 2000 Hz) QM/33  
 10 g (10 to 2000 Hz) QM/34

**Cable Type:**

PVC 2 x 0,34 QM/33  
 PVC 3 x 0,34 QM/34

**Cable Length:**


2, 5 or 10 m

**Materials:**

Plastic body

**Alternative Switches:**

See page N 4.3.051.02


**Ordering Information**

To order a reed switch with LED and 5 m cable length quote: QM/34/5

To order a reed switch with 2 m cable length quote: QM/33/2


Order mounting brackets separately.


**Accessories**


Plug-in connector

See page

N 4.3.051.02






QM/33  brown blue

QM/34  + brown  
- blue  
black  
(Output)





Switching current and switching voltage





Alternative Switches

Symbol	Switches (without LED)	Symbol	Switches (with LED)	Description
	QM/33/* brown blue			High temperature (+150 °C), silicone cable 2 x 0,34 (5 m length), switching voltage 10 to 30 V a.c. / 10 to 30 V d.c.
			QM/34/P brown blue black (Output)	Plug in connector, cable see below
	QM/33/C/* black blue brown			Changeover, PVC cable 3 x 0,34 (5 m length), switching voltage 10 to 110 V a.c./175 V d.c., switching current 250 mA, switching power 5 W/ 5 VA, response time 0,7 ms, contact resistance 100 mΩ, vibration resistance 20 g (during 11 ms)
			QM/34/N/* blue brown black (Output)	Negative output, PVC cable 3 x 0,34 (2 or 5 m length)
			QM/34/N*/PU	Very flexible polyurethane cable 3 x 0,34 (2 m length)
			QM/34/S/* brown blue (Output)	PVC cable 2 x 0,34 (2, 5 or 10 m length), switching voltage 10 to 240 V a.c./d.c., switching current 500 mA, switching power 50 W/ 50 VA, response time 2 ms
			QM/34/S*/PU	Very flexible polyurethane cable 2 x 0,5 (2 m length)

\* insert cable length

Weights for Switches and Plug-In Connector Cables

Plug-in Connector Cables		Plug-in Connector Cables	
Model	Weight (kg)	Model	Weight (kg)
QM/33/2	0,053	M/P34614/*	0,150
QM/34/2	0,086	M/P34595/*	0,130
QM/34/P	0,004		

\* insert 5 m cable length




Basic Dimensions

QM/33

QM/34

QM/34/P

View A



Warning

These products are intended for use in industrial control systems only. Do not use these products where voltage, current and temperatures can exceed those listed under "Technical Data".

Before using these products for non-industrial applications, life-support systems, or other applications not within published specifications, consult NORGREN.

Through misuse, age, or malfunction, components used in control systems can fail in various modes.

The system designer is warned to consider the failure modes of all component parts used in control systems and to provide adequate safeguards to prevent personal injury or damage to equipment in the event of such failure.

**System designers must provide a warning to end users in the system instructional manual if protection against a failure mode cannot be adequately provided.**

System designers and end users are cautioned to review specific warnings found in instruction sheets packed and shipped with these products.