



SNAP-IN INSULATED SHAFT ROTARY POTENTIOMETER

Q-4699




F-09KV

Standard Type, Single Unit



F-09KH

Standard Type, Single Unit



SPECIFICATIONS

Electrical Characteristics

- Total Resistance..... 500Ω~1MΩ
- Total Resistance Tolerance..... ±20%
- Resistance Taper..... A,B,C,D, See P81
- Max.Operation Voltage AC 50V, DC 12 V
- Rated Power..... 0.05W
- Sliding Noise Less than 100 mV
- Insulation Resistance..... More than 100 MQ at DC 100V
- Withstand Voltage 1 minute at AC 250 V
- Residual Resistance Term.1~2:Less than 100 Ω
Term.2~3:Less than 100 Ω

Mechanical Characteristics

- Total Rotational Angle..... 280°±10°
- Rotational Torque 10gf. cm~ 100gf. cm
- Rotational Stopper Strength 3.0 Kgf. cm Min
- Push-Pull Strength 5Kgf Min
- Rotational Life..... 10,000 Cycles

Durability