


WiFi + GPS Combinational External Antenna



AEACBK046014-C2WG



ESD Sensitive



Ø46.6 x 14.5 mm
RoHS/RoHS II Compliant

MSL = N/A: NOT APPLICABLE

FEATURES

- IP67 Dust and Waterproof
- 1574.42MHz/2450MHz/5500MHz frequencies
- LNA Gain up to 20dBi+/-2dB
- VSWR \leq 1.5/2.5 for GPS/WiFi
- RHCP/Linear polarization for GPS/WiFi

APPLICATIONS

- GPS/GLONASS
- WiFi/Bluetooth/Zigbee,
- ISM devices
- Use on outdoor and indoor assets
- M2M
- Telematics
- Commercial vehicles/ Fleet management
- Remote Technology/Monitoring

ELECTRICAL SPECIFICATIONS

Parameters	Min.	Typ.	Max.	Units	Note
Frequency		1575.42 \pm 3MHz		MHz	
Bandwidth		CF \pm 4MHz		MHz	
VSWR			1.5		
Polarization		RHCP			(Right Hand Circular Polarization)
Impedance		50		Ω	
Gain		0		dBi	(Zenith)
Operating Temperature	-40		+85	$^{\circ}$ C	
Input Power			10	W	


LOW NOISE AMPLIFIER (LNA)

Parameters	Min.	Typ.	Max.	Units	Note
DC Voltage		3.3		V	
Gain		20 \pm 2dB		dB	
Output VSWR			2.0		
Noise Figure			1.5	dB	
DC current			10	mA	

Wifi ANTENNA

Parameters	Min.	Typ.	Max.	Units	Note
Frequency Range		2400~2483.5/4800~5825		MHz	
VSWR			2.5		
Polarization Model		Linear			
Impedance		50		Ω	
Gain		2		dBi	(Zenith)
Operating Temperature	-40		+85	$^{\circ}$ C	
Input Power			10	W	

WiFi + GPS Combinational External Antenna



AEACBK046014-C2WG



ESD Sensitive



Ø46.6 x 14.5 mm
RoHS/RoHS II Compliant



MSL = N/A: NOT APPLICABLE

RETURN - LOSS CHARACTERISTICS

RETURN - LOSS CHARACTERISTICS

GPS S11 Return Loss

WiFi S11 Return Loss






RADIATION PATTERNS

GPS Antenna 2D Patterns


XY Plane

XZ Plane

YZ Plane



WiFi + GPS Combinational External Antenna



AEACBK046014-C2WG



ESD Sensitive




Ø46.6 x 14.5 mm
RoHS/RoHS II Compliant

MSL = N/A: NOT APPLICABLE


RADIATION PATTERNS

WiFi Antenna 2D Patterns


XY Plane




XZ Plane



YZ Plane




WiFi Antenna 3D Pattern



Frequency (MHz)	2400	2450	2483
Peak Gain (dBi)	-4.2	-4.50	-4.53
Efficiency (%)	61	61	63

WiFi + GPS Combinational External Antenna



AEACBK046014-C2WG




ESD Sensitive



Ø46.6 x 14.5 mm
RoHS/RoHS II Compliant

MSL = N/A: NOT APPLICABLE

DIMENSIONS



Unit: mm


Parameters	Description
Cable Length	3.00 m
RF Cable	RG178
RF Connector	SMA and others
Radome Material	ABS
Mounting Type	Screw



PACKAGING

Each 700 x 320 x 155 mm size carton includes 100 pcs antenna, 8kgs/carton.

Unit: mm



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[AEACBK046014-C2WG](#)