



MMSTA55/MMSTA56

PNP SMALL SIGNAL SURFACE MOUNT TRANSISTOR

Features

- Epitaxial Planar Die Construction
- Complementary NPN Type Available (MMSTA05/MMSTA06)
- Ideal for Low Power Amplification and Switching
- Ultra-Small Surface Mount Package
- Lead Free/RoHS Compliant (Note 2)
- "Green" Device (Note 3 and 4)

Mechanical Data

Case: SOT-323

Case Material: Molded Plastic, "Green" Molding Compound, Note 4. UL Flammability Classification Rating 94V-0

Moisture Sensitivity: Level 1 per J-STD-020C

Terminal Connections: See Diagram

Terminals: Solderable per MIL-STD-202, Method 208


Lead Free Plating (Matte Tin Finish annealed over Alloy 42 leadframe).

MMSTA55 Marking K2H, K2G (See Page 3)

MMSTA56 Marking K2G (See Page 3)

Ordering & Date Code Information: See Page 3

Weight: 0.006 grams (approximate)



SOT-323									
Dim	Min	Max							
Α	0.25	0.40							
В	1.15	1.35							
С	2.00 2.20								
D	0.65 Nominal								
E	0.30	0.40							
G	1.20	1.40							
Н	1.80	2.20							
٦	0.0	0.10							
K	0.90	1.00							
L	0.25	0.40							
М	0.10	0.18							
α	0°	8°							
All Din	All Dimensions in mm								

Maximum Ratings @T_A = 25°C unless otherwise specified

Characteristic	Symbol	MMSTA55	MMSTA56	Unit	
Collector-Base Voltage	V _{CBO}	-60	-80	V	
Collector-Emitter Voltage	V _{CEO}	-60	-80	V	
Emitter-Base Voltage	V _{EBO}	-4	V		
Collector Current - Continuous (Note 1)	Ic	-5	mA		
Power Dissipation (Note 1)	P _d	20	mW		
Thermal Resistance, Junction to Ambient (Note 1)	$R_{ hetaJA}$	62	°C/W		
Operating and Storage Temperature Range	T _i , T _{STG}	-55 to	°C		

Notes:

- Device mounted on FR-4 PCB, 1 inch x 0.85 inch x 0.062 inch; pad layout as shown on Diodes Inc. suggested pad layout document AP02001, which can be found on our website at http://www.diodes.com/datasheets/ap02001.pdf.
- No purposefully added lead.
- Diodes Inc.'s "Green" policy can be found on our website at http://www.diodes.com/products/lead_free/index.php.
- Product manufactured with Date Code 0627 (week 27, 2006) and newer are built with Green Molding Compound. Product manufactured prior to Date Code 0627 are built with Non-Green Molding Compound and may contain Halogens or Sb2O3 Fire Retardants.



Electrical Characteristics @T_A = 25°C unless otherwise specified

Characteristic		Symbol	Min	Max	Unit	Test Condition		
OFF CHARACTERISTICS (Note 5)								
Collector-Base Breakdown Voltage	MMSTA55 MMSTA56	V _{(BR)CBO}	-60 -80	_	V	$I_C = -100 \mu A, I_E = 0$		
Collector-Emitter Breakdown Voltage	MMSTA55 MMSTA56	V _{(BR)CEO}	-60 -80	_	V	$I_C = -1.0 \text{mA}, I_B = 0$		
Emitter-Base Breakdown Voltage		$V_{(BR)EBO}$	-4.0	_	V	$I_E = -100 \mu A, I_C = 0$		
Collector Cutoff Current	MMSTA55 MMSTA56	I _{CBO}	_	-100	nA	$V_{CB} = -60V, I_{E} = 0$ $V_{CB} = -80V, I_{E} = 0$		
Collector Cutoff Current	MMSTA55 MMSTA56	I _{CEX}	_	-100	nA	$V_{CE} = -60V, I_{BO} = 0V$ $V_{CE} = -80V, I_{BO} = 0V$		
ON CHARACTERISTICS (Note 5)								
DC Current Gain		h _{FE}	100	_	_	$I_C = -10 \text{mA}, V_{CE} = -1.0 \text{V}$ $I_C = -100 \text{mA}, V_{CE} = -1.0 \text{V}$		
Collector-Emitter Saturation Voltage		V _{CE(SAT)}	_	-0.25	V	$I_C = -100 \text{mA}, I_B = -10 \text{mA}$		
Base-Emitter Saturation Voltage		V _{BE(SAT)}	_	-1.2	V	I _C = -100mA, V _{CE} = -1.0V		
SMALL SIGNAL CHARACTERISTICS				•	•			
Current Gain-Bandwidth Product		f _T	50	_	MHz	$V_{CE} = -1.0V, I_{C} = -100mA,$ f = 100MHz		

Notes: 5. Short duration pulse test used to minimize self-heating effect.




Fig. 1, Max Power Dissipation vs. Ambient Temperature




Fig. 3, DC Current Gain vs. Collector Current




Fig. 2, Collector Emitter Saturation Voltage vs. Collector Current




Fig. 4 Base Emitter Voltage vs. Collector Current







Fig. 5 Gain Bandwidth Product vs. Collector Current

Ordering Information (Notes 4 and 6)

Device	Packaging	Shipping				
MMSTA55-7-F	SOT-323	3000/Tape & Reel				
MMSTA56-7-F	SOT-323	3000/Tape & Reel				

6. For packaging details, go to our website at http://www.diodes.com/datasheets/ap02007.pdf. Notes:

Marking Information



K2x = Product Type Marking Code, e.g. K2H = MMSTA55

YM = Date Code Marking Y = Year ex: N = 2002 M = Month ex: 9 = September

Date Code Key

Year	1998	1999	2000	2001	2002	2003	2004	2005	2006	2007	2008	2009	2010	2011	2012
Code	J	K	L	М	N	Р	R	S	Т	U	V	W	Х	Υ	Z
Month	Jan	Fel	b	Mar	Apr	May	Ju	n	Jul	Aug	Sep	Oc	t	Nov	Dec
Code	1	2		2	1	5	6		7	8	9	0		N	D

IMPORTANT NOTICE

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. Diodes Incorporated does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

Diodes Incorporated products are not authorized for use as critical components in life support devices or systems without the expressed written approval of the President of Diodes Incorporated.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

MMSTA55-7-F MMSTA56-7-F