PERICOM® SaRonix-ecera®

PSE Technology Corporation

SPECIFICATION FOR APPROVAL

CUSTOMER NOMINAL FREQUENCY 32.768 KHz **TYPE G4 SMD X'TAL** PRODUCT TYPE SPEC. NO. (P/N) G43270019 **CUSTOMER P/N ISSUE DATE** Nov.9,2012 **VERSION** В

APPROVED	APPROVED PREPARED	
Brenda	Viklai Lu	Bedryeri
APPROVED BY	AVL Status	
Please return one copy with approval to PSE-TW		

PSE Technology Corporation

No.2, Tzu-Chiang 5th Rd, Chung Li Industrial Park, Chung Li City, Taoyuan County, Taiwan (R.O.C.)

TEL: 886-3-451-8888 FAX: 886-3-461-3865

http://www.saronix-ecera.com.tw

*RoHS Exception

*HF-Halogen Free

*REACH Compliant



*** A company of PERICOM Semiconductor Corporation ***

Page i

G43270019

VER. B 9-Nov-12

VERSION HISTORY

Version No.	Version Date	Customer Receipt Date	Supplier Receipt Date	Description	Notes
Α	Jan.21,2011			Initial Release	
В	Nov.9,2012			Changed mechanical drawing	

G43270019

VER. B 9-Nov-12

ELECTRICAL SPECIFICATIONS

SRe Part Number: G43270019

Parameters	Symbol	Specifications	Units	Notes
Nominal Frequency	Fn	32.768	KHz	
Frequency Tolerance	FT	± 20	ppm	at 25°C ± 5°C
Load Capacitance	CL	12.5	pF	Тур.
Drive Level	DL	1	μ W	Max.
Equivalent Series Resistance	ESR	35	ΚΩ	Max.
Temperature Coefficient	K	-0.035	ppm/°C	Тур.
Shunt Capacitance	C0	1.35	pF	Тур.
Operating Temperature Range	TR	-40~85	°C	
Storage Temperature Range		-55~85	°C	
Aging		± 3	ppm	Max 1st year
Insulation Resistance		500	ΜΩ	Min.

^{**}RoHS Complaint Product

Reliability (Mechanical and Environmental Endurance)


No.	Test Items	Test Method and Condition	Requirements
1	Vibration	(1) Vibration Frequency: 10 to 55Hz	Frequency Change: ±10ppm Max.
		(2) Vibration Amplitude: 1.5mm	Resistance Change: ±15% or 5kΩ Max.
		(3) Cycle Time: 1-2min(10-55-10Hz)	
		(4) Direction: X.Y.Z	
		(5) Duration: 2h/each direction	
2	Shock	3 Times free drop from 75cm height to hard wooden	Frequency Change: ±10ppm Max.
		board of thickness more than 30mm	Resistance Change: ±15% or 5kΩ Max.
3	Leakage	Put crystal units into a hermetic container and	Leakage: 1x10 ⁻ 8Pa·m3/s Max.
		Helium for 0.5-0.6Mpa, and keep it for 1h;	
		Check the leakage by a Helium leak detector	



E0-R-4-014 Rev.E Page 1

G43270019

VER. B 9-Nov-12




G43270019

VER. B 9-Nov-12

Marking

eBEmv

Dimensions (Units: mm)



E0-R-4-014 Rev.E Page 3


G43270019

VER. B 9-Nov-12


TAPE AND REEL SPECIFICATION

- 1. Tape and Reel form conform to EIA-481-B
- 2. The quantity of crystal units per reel shall be 3000PCS.
- 3. A "LABEL" on which necessary information is clearly written is on the surface of packing box and the reel.

CARRIER TAPE DIMENSIONS



REEL DIMENSIONS



規格	A±0.5	C±0.2	D±0.3	W1±0.2	W2 ^{+0,4}
330*100*16	330	25	100	20	16

E0-R-4-014 Rev.E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated: G43270019