

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
	G	Contact pin base material change from CuSn (Phosphor bronze) to CuZn (Brass). Plating change from min. 0.8microns gold plating to min. 0.7µm Pd Ni + 0.1µm gold flash at contact area (Area F).		24JUN2014	TJ	JK	

NUMBER		825440	
VERWENDET FÜR		E 92-9802	
WAR NR.		—	


POLZ. PRO REIHE	L±0.5	BESTELL-NR.	
—	—	—	
2	5.08	825 440	-2
3	7.62		-3
4	10.16		-4
5	12.70		-5
6	15.24		-6
7	17.78		-7
8	20.32		-8
9	22.86		-9
10	25.40	1-	-0
11	27.94	1-	-1
12	30.48	1-	-2
13	33.02	1-	-3
14	35.56	1-	-4
15	38.10	1-	-5
16	40.64	1-	-6
17	43.18	1-	-7
18	45.72	1-	-8
19	48.26	1-	-9
20	50.80	2-	-0
21	53.34	2-	-1
22	55.88	2-	-2
23	58.42	2-	-3
24	60.96	2-	-4
25	63.50	2-	-5
26	66.04	2-	-6
27	68.58	2-	-7
28	71.12	2-	-8
29	73.66	2-	-9
30	76.20	3-	-0
31	78.74	3-	-1
32	81.28	3-	-2
33	83.82	3-	-3
34	86.36	3-	-4
35	88.90	3-	-5
36	91.44	3-	-6
37	93.98	3-	-7
38	96.52	3-	-8
39	99.06	3-	-9
40	101.60	4-	-0
41	104.14	4-	-1
42	106.68	4-	-2
43	109.22	4-	-3
44	111.76	4-	-4
45	114.30	4-	-5
46	116.84	4-	-6
47	119.38	4-	-7
48	121.92	4-	-8
49	124.46	4-	-9
50	127.00	5- 825 440	-0

CAD-ORIGINAL
ZEICHNUNG NICHT ÄNDERN

STECKSEITE: IM BEREICH "F" MIN 0.7µmPdNi+0.1µm GOLD FLASH ÜBER 1.27 µm NICKEL.
LÖTSEITE: MIN. 2.5 µm ZINN ÜBER 1.27 µm NICKEL

KONTAKTSTIFT	Cu Zn	⚠
STIFTGEHÄUSE	PBT GV	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE FARBE
ZEICHNUNG GÜLTIG AB		KW 39./96

DIMENSIONS:		DWN	22.06.84	MATERIAL	FINISH					
mm		M.SCHAARSCHMIDT		—	—					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	—	TE Connectivity						
±0.2 mm		APVD	—							
0 PLC ± —		PRODUCT SPEC	108-18012							
1 PLC ± —		APPLICATION SPEC	—							
2 PLC ± —		WEIGHT	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
3 PLC ± —				A4	00779	C-825440	—			
4 PLC ± —				CUSTOMER DRAWING						
ANGLES ± —				SCALE		4:1	SHEET	1 OF 2	REV	G

LOC —	DIST —	REVISIONS																																																																																																																																																							
		P	LTR	DESCRIPTION	DATE	DWN	APVD																																																																																																																																																		
			—	SEE SHEET 1	—	—	—																																																																																																																																																		
VERWENDET FÜR E 92-9802		CAD-ORIGINAL ZEICHNUNG NICHT ÄNDERN																																																																																																																																																							
WAR NR. —																																																																																																																																																									
<table><tr><td>Polz. pro Reihe</td><td>L±0.5</td><td colspan="2">Bestell-Nr.</td><td colspan="3">Bemerkung</td></tr><tr><td>1</td><td>2.54</td><td>5-</td><td>-1</td><td colspan="3"></td></tr><tr><td>2</td><td>5.08</td><td>5-</td><td>-2</td><td colspan="3"></td></tr><tr><td>3</td><td>7.62</td><td>5-</td><td>-3</td><td colspan="3"></td></tr><tr><td>4</td><td>10.16</td><td>5-</td><td>-4</td><td colspan="3"></td></tr><tr><td>5</td><td>12.70</td><td>5-</td><td>-5</td><td colspan="3"></td></tr><tr><td>6</td><td>15.24</td><td>5-</td><td>-6</td><td colspan="3"></td></tr><tr><td>7</td><td>17.78</td><td>5-</td><td>-7</td><td colspan="3"></td></tr><tr><td>8</td><td>20.32</td><td>5-</td><td>-8</td><td colspan="3"></td></tr><tr><td>9</td><td>22.86</td><td>5-</td><td>-9</td><td colspan="3"></td></tr><tr><td>10</td><td>25.40</td><td>6-</td><td>0</td><td colspan="3"></td></tr><tr><td>11</td><td>27.94</td><td>6-</td><td>-1</td><td colspan="3"></td></tr><tr><td>12</td><td>30.48</td><td>6-</td><td>-2</td><td colspan="3"></td></tr><tr><td>13</td><td>33.02</td><td>6-</td><td>-3</td><td colspan="3"></td></tr><tr><td>14</td><td>35.56</td><td>6-</td><td>-4</td><td colspan="3"></td></tr><tr><td>15</td><td>38.10</td><td>6-</td><td>-5</td><td colspan="3"></td></tr><tr><td>16</td><td>40.64</td><td>6-</td><td>-6</td><td colspan="3"></td></tr><tr><td>17</td><td>43.18</td><td>6-</td><td>825 440 -7</td><td colspan="3">△</td></tr><tr><td>18</td><td>45.72</td><td>6-</td><td>-8</td><td colspan="3"></td></tr><tr><td>19</td><td>48.26</td><td>6-</td><td>-9</td><td colspan="3"></td></tr><tr><td>20</td><td>50.80</td><td>7-</td><td>0</td><td colspan="3"></td></tr></table>							Polz. pro Reihe	L±0.5	Bestell-Nr.		Bemerkung			1	2.54	5-	-1				2	5.08	5-	-2				3	7.62	5-	-3				4	10.16	5-	-4				5	12.70	5-	-5				6	15.24	5-	-6				7	17.78	5-	-7				8	20.32	5-	-8				9	22.86	5-	-9				10	25.40	6-	0				11	27.94	6-	-1				12	30.48	6-	-2				13	33.02	6-	-3				14	35.56	6-	-4				15	38.10	6-	-5				16	40.64	6-	-6				17	43.18	6-	825 440 -7	△			18	45.72	6-	-8				19	48.26	6-	-9				20	50.80	7-	0			
Polz. pro Reihe	L±0.5	Bestell-Nr.		Bemerkung																																																																																																																																																					
1	2.54	5-	-1																																																																																																																																																						
2	5.08	5-	-2																																																																																																																																																						
3	7.62	5-	-3																																																																																																																																																						
4	10.16	5-	-4																																																																																																																																																						
5	12.70	5-	-5																																																																																																																																																						
6	15.24	5-	-6																																																																																																																																																						
7	17.78	5-	-7																																																																																																																																																						
8	20.32	5-	-8																																																																																																																																																						
9	22.86	5-	-9																																																																																																																																																						
10	25.40	6-	0																																																																																																																																																						
11	27.94	6-	-1																																																																																																																																																						
12	30.48	6-	-2																																																																																																																																																						
13	33.02	6-	-3																																																																																																																																																						
14	35.56	6-	-4																																																																																																																																																						
15	38.10	6-	-5																																																																																																																																																						
16	40.64	6-	-6																																																																																																																																																						
17	43.18	6-	825 440 -7	△																																																																																																																																																					
18	45.72	6-	-8																																																																																																																																																						
19	48.26	6-	-9																																																																																																																																																						
20	50.80	7-	0																																																																																																																																																						
△ VERPACKUNG:25 STÜCK IN PLASTIK-DOSE PN 165 439-1 MIT PLASTIK-DECKEL PN 165 440-1																																																																																																																																																									
△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI																																																																																																																																																									
△ OBSOLETE																																																																																																																																																									
		BENENNUNG		WERKSTOFF		OBERFLÄCHE FARBE																																																																																																																																																			
ZEICHNUNG GÜLTIG AB KW 39./96																																																																																																																																																									
DIMENSIONS: mm		DWN A.HO	07.06.84	MATERIAL —		FINISH —																																																																																																																																																			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		CHK M.SCHAARSCHMIDT	13.06.84	 TE Connectivity																																																																																																																																																					
		APVD —	—																																																																																																																																																						
		PRODUCT SPEC —		NAME AMPMODU II STIFTLEISTE ZWEIREIHIG																																																																																																																																																					
		APPLICATION SPEC —																																																																																																																																																							
		WEIGHT —	A4	00779	C-825440	RESTRICTED TO —																																																																																																																																																			
CUSTOMER DRAWING				SCALE 4:1	SHEET 2 OF 2	REV G																																																																																																																																																			

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

By -
COPYRIGHT -

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-825440-0](#)