■¬ Colors Available:

Black (BK)



- **Cut-Through Resistance**
- Self Closing Wrap
- Heavy Abrasion Guard
- Resists To Chemicals **And Automotive Fluids**
- **■** Great Spot-Protection
- No Tool Install
- Lightweight And Very **Flexible**

			Put-ops —				
Nominal Size	Part #	Wall Thickness	Bulk	Box A	Box B	Available Colors	Lbs/ 100'
3/8"	F6H0.38BK	.06"	1,200′	150′	75′	Black (BK)	3.2
1/2"	F6H0.50BK	.06"	800′	100′	50′	Black (BK)	3.9
5/8"	F6H0.63BK	.06"	500′	100′	50′	Black (BK)	4.7
3/4"	F6H0.75BK	.06"	500′	100′	50′	Black (BK)	5.0
1"	F6H1.00BK	.06"	400′	75′	25′	Black (BK)	6.2
1 3/8"	F6H1.38BK	.06"	250′	75′	25′	Black (BK)	7.5



Chafe Protection Wrap

F6 HEAVY (F6H) is a unique composite wrap-around chafe guard made from resistant synthetic polymers.

Techflex F6 Heavy is reimagined from the ground up to protect hoses and cables from chafing and abrasion. The easy wrap installation technology is a first for the hydraulic and fluid transfer industry. By combining the extreme cut and abrasion defense of a traditional woven nylon protection sleeve and the self-wrapping properties of our best-selling F6 line of products we have created a new standard for fast in field hose and wire protection.

We have eliminated the need to disconnect fittings, connectors and hoses in order to properly protect your systems from damage. Simply apply F6 Heavy and get back work.

Material

Polyethylene Terephthalate

Grade

F6H

Wall Thickness

.06"

Drawing Number

TF001F6H-WD

This is a non-expandable product. Be sure to



104 Demarest Road • Sparta, NJ 07871





match your application diameter accurately.



ABRASION

Abrasion Resistance Extreme

Abrasion Test Machine Taber 5150

Abrasion Test Wheel Calibrase H-18

Abrasion Test Load 500g

Room Temperature 71°F

First Signs Of Slight Fibers Chafed 1,000.....Test Cycles

Wearing Of Yarns Is Deeper & Uniform 6,000.....Test Cycles

No Noticable Change 10,000.....Test Cycles

Fail/Hole 15,000..... Test Cycles


Pre-Test Weight 6.7123 a Post-Test Weight 6.1526 g

Test End Loss Of Mass Point Of Destruction 0.5597 g



1=No Effect 4=More Affected 2=Little Effect 5=Severely Affected 3=Affected

Aromatic Solvents	2
Aliphatic Solvents	1
Chlorinated Solvents	
Weak Bases	1
Salts	1
Strong Bases	2
Salt Water <i>0-S-1926</i>	1
Hydraulic Fluid MIL-H-5606	1
Lube Oil <i>MIL-L-7808</i>	1
De-Icing Fluid <i>MIL-A-8243</i>	1
Strong Acids	3
Strong Oxidants	2
Esters/Ketones	1
UV Light	1
Petroleum	1
Fungus ASTM G-21	1
Halogen Free	Yes
RoHS	
SVHC	



PHYSICAL PROPERTIES

Monofilament Diameter	.02"
Flammability Rating	
Recommended Cutting	
Colors	
Wall Thickness	
Specific Gravity ASTM D-792 _	1.38
Moisture Absorption % ASTM D-570	2.7
TML	1.10
CVCM	.01
WVR	
Outgassing	High
Oxygen Index	22