

DN350T05

350V NPN SMALL SIGNAL SURFACE MOUNT TRANSISTOR

Features


- BV_{CEO} > 250V
- I_C = 0.5A Continuous Collector Current
- Epitaxial Planar Die Construction
- Complementary PNP Type Available (DP350T05)
- Ideal for Medium Power Amplification and Switching
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability

Mechanical Data


- Case: SOT23
- Case Material: Molded Plastic, "Green" Molding Compound;
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads; Solderable per MIL-STD-202, Method 208 (§3)
- Weight: 0.008 grams (Approximate)







Device Symbol



Top View Pin-Out


Ordering Information (Note 4)

Product	Compliance	Marking	Reel size (inches)	Tape width (mm)	Quantity per reel
DN350T05-7	AEC-Q101	K3S	7	8	3,000

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

Marking Information



K3S = Product Type Marking Code YM = Date Code Marking Y = Year ex: E = 2017 M = Month ex: 9 = September

Date Code Key

Year	2017	'	2018	2019		2020	2021		2022	2023		2024
Code	Е		F	G		Н			J	K		L
Month	Jan	Feb	Mar	Apr	Мау	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	2	4	_	9	7	Ω	a	0	N	D



Absolute Maximum Ratings (@TA = 25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V _{CBO}	350	V
Collector-Emitter Voltage	V _{CEO}	350	V
Emitter-Base Voltage	V _{EBO}	5.0	V
Continuous Base Current	I _B	25	mA
Continuous Collector Current	Ic	500	mA

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 5)	P_{D}	300	mW
Thermal Resistance, Junction to Ambient (Note 5)	$R_{\theta JA}$	417	°C/W
Operating and Storage Temperature Range	T_{J}, T_{STG}	-65 to +150	°C

Electrical Characteristics (@T_A = ±25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 6)						
Collector-Base Breakdown Voltage	V _{(BR)CBO}	350	_	V	$I_C = 100\mu A, I_E = 0$	
Collector-Emitter Breakdown Voltage	V _{(BR)CEO}	350	_	V	$I_C = 1.0 \text{mA}, I_B = 0$	
Emitter-Base Breakdown Voltage	V _{(BR)EBO}	5.0	_	V	$I_E = 10\mu A, I_C = 0$	
Collector Cutoff Current	I _{CBO}	_	50	nA	$V_{CB} = 250V, I_{E} = 0$	
Collector Cutoff Current	I _{EBO}	_	50	nA	$V_{CE} = 5V, I_{C} = 0$	
ON CHARACTERISTICS (Note 6)						
DC Current Gain	h _{FE}	20 30 30 20 15			$\begin{split} I_C &= 1.0 \text{mA}, \ V_{CE} = 10 \text{V} \\ I_C &= 10 \text{mA}, \ V_{CE} = 10 \text{V} \\ I_C &= 30 \text{mA}, \ V_{CE} = 10 \text{V} \\ I_C &= 50 \text{mA}, \ V_{CE} = 10 \text{V} \\ I_C &= 100 \text{mA}, \ V_{CE} = 10 \text{V} \end{split}$	
Collector-Emitter Saturation Voltage	V _{CE} (SAT)	_ _ _	0.30 0.35 0.50 1.0	V	$I_C = 10\text{mA}, I_B = 1.0\text{mA}$ $I_C = 20\text{mA}, I_B = 2.0\text{mA}$ $I_C = 30\text{mA}, I_B = 3.0\text{mA}$ $I_C = 50\text{mA}, I_B = 5.0\text{mA}$	
Base-Emitter Saturation Voltage	V _{BE(SAT)}	 	0.75 0.80 0.90	V	I _C = 10mA, I _B = 1.0mA I _C = 20mA, I _B = 2.0mA I _C = 30mA, I _B = 3.0mA	
Base-Emitter On Voltage	V _{BE(ON)}		2.0	V	I _C = 100mA, V _{CE} = 10V	
SMALL SIGNAL CHARACTERISTICS						
Output Capacitance	$C_{ m obo}$		7.0	pF	$V_{CB} = 20V, f = 1.0MHz, I_E = 0$	
Transition Frequency	f⊤	50	_	MHz	V _{CE} = 10V, I _C = 20mA	

Notes: 5. For a device mounted on minimum recommended pad layout FR4 PCB with high coverage of single sided 1oz copper; device is measured under still air conditions whilst operating in a steady-state.

^{6.} Short duration pulse test used to minimize self-heating effect.



Typical Electrical Characteristics (@TA = +25°C, unless otherwise specified.)




Fig. 1, Max Power Dissipation vs. Ambient Temperature




Fig. 3, Collector-Emitter Saturation Voltage vs. Collector Current




Fig. 5, Base-Emitter On Voltage vs. Collector Current




Fig. 2, DC Current Gain vs. Collector Current




Fig. 4, Base Emitter Saturation Voltage vs. Collector Current





Fig. 6, Capacitance vs. Reverse Voltage



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23




SOT23						
Dim	Min	Max	Тур			
Α	0.37	0.51	0.40			
В	1.20	1.40	1.30			
С	2.30	2.50	2.40			
D	0.89	1.03	0.915			
F	0.45	0.60	0.535			
G	1.78	2.05	1.83			
Н	2.80	3.00	2.90			
J	0.013	0.10	0.05			
K	0.890	1.00	0.975			
K1	0.903	1.10	1.025			
L	0.45	0.61	0.55			
L1	0.25	0.55	0.40			
М	0.085	0.150	0.110			
а	0°	8°				
All	All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23



Dimensions	Value (in mm)		
C	2.0		
Х	0.8		
X1	1.35		
Y	0.9		
Y1	2.9		



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

DN350T05-7