




Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Connector Boots



Boot Angle: **Straight**

Adhesive Pre-Coating: **With**

Adhesive Description: **High Performance Pre-Coat Adhesive**

Number of Positions: **0**

Centerline (Pitch): **0 mm [ 0 in ]**

## Features

### Product Type Features

Product Type	Molded Boot
Molded Part Type	D Subminiature Boot
Adhesive Description	High Performance Pre-Coat Adhesive

### Configuration Features

Number of Positions	0
---------------------	---

### Body Features

Material Systems Code	10
Material	Semi rigid Modified Polyolefin
Material Code	3
Boot Angle	Straight
Adhesive Pre-Coating	With

### Contact Features

Contact Current Rating (Max)	0 A
------------------------------	-----

### Housing Features

Centerline (Pitch)	0 mm[0 in]
--------------------	------------

### Dimensions

Connector Width	10.7 mm[.421 in]
-----------------	------------------



### Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
-----------------------------	----------------------------

### Other

Adhesive Code	86
Adhesive Options	/86 Precoat

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # CJ2087-000  
HL2010E-KIT-120V

## Customers Also Bought




TE Part #928947-000  
SO63-2-55-24-9




TE Part #839717-000  
SO63-3-55-24-9



TE Part #1757624-1  
SZ 8 COAX PIN, RG142, HEX CRIMP



TE Part #733447-000  
214A321-3/86-0



TE Part #313123-000  
214A332-3/86-0



TE Part #330355-000  
234A121-3/86-0



TE Part #ZPF00000000017898  
FAST-E 08 M-X-A 00 A



TE Part #ZPF000000000146308  
DMC-MD 26 F-K-T



TE Part #ZPF000000000146309  
DMC-MD 26 G-K-T



TE Part #625415-000  
SO63-4-55-24-9

## Documents

### Product Drawings

[214A311-3/86-0](#)

English

### Datasheets & Catalog Pages

[1654025\\_Sec4\\_-3](#)

English

### Raychem Molded Parts Visual Guide

English



---

**Product Specifications**

**Product Specification**

English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[214A311-3/86-0](#)