

Main applications

Where transient overvoltage protection in ESD sensitive equipment is required, such as:

- Computers
- Servers
- Printers
- Communication systems and cellular phones
- Video equipment

These devices are particularly adapted to the protection of symmetrical signals.

Features

- 4 / 5 Unidirectional (ESDA6V1P6 and ESDA6V1-5P6) and Bidirectional (ESDA14V2BP6 and ESDA25-4BP6) Transil functions
- Breakdown voltage: $V_{BR} = 6.1 \text{ V min.}, 14.2 \text{ V min. and } 25 \text{ V min.}$
- Low leakage current:
 - < 500 nA (ESDA6V1P6 / ESDA6V1-5P6)
 - < 1 μA (ESDA14V2BP6 and ESDA25-4BP6)
- Very small PCB area < 2.6 mm²

Description

The ESDAxxxP6 are monolithic arrays designed to protect up to 5 lines against ESD transients.

These devices are ideal where board space saving and reduced line capacitance are required.


Benefits

- High ESD protection level
- High integration
- Suitable for high density boards

Complies with the following standards:

IEC61000-4-2 level 4: 15 kV (air discharge)
8 kV (contact discharge)

MIL STD 883E-Method 3015-7: class3
25 kV (Human Body Model)



Order codes

Part Number	Marking
ESDA6V1P6	B
ESDA6V1-5P6	C
ESDA14V2BP6	A
ESDA25-4BP6	V

Figure 1. ESDA6V1P6 functional diagram




Figure 2. ESDA6V1-5P6 functional diagram





Figure 3. ESDA14V2BP6 and ESDA25-4BP6 functional diagram



TM: Transil is a trademark of STMicroelectronics

1 Characteristics

Table 1. Absolute Maximum Ratings ($T_{amb} = 25^{\circ}C$)

Symbol	Parameter		Value	Unit
V_{PP}	IEC 61000-4-2 level 4 standard	air discharge contact discharge	± 15 ± 8	kV
P_{PP}	Peak pulse power (8/20 μs) ⁽¹⁾ T_j initial = T_{amb}	ESDA6V1P6 / ESDA6V1-5P6	150	W
		ESDA14V2BP6 / ESDA25-4BP6	50	
T_j	Junction temperature		150	$^{\circ}C$
T_{stg}	Storage temperature range		-55 to +150	$^{\circ}C$
T_L	Maximum lead temperature for soldering during 10 s at 5 mm for case		260	$^{\circ}C$
T_{op}	Operating temperature range		-40 to +150	$^{\circ}C$

1. for a surge greater than the maximum values, the diode will fail in short-circuit.

Table 2. Electrical Characteristics ($T_{amb} = 25^{\circ}C$)

Symbol	Parameter	
V_{RM}	Stand-off voltage	
V_{BR}	Breakdown voltage	
V_{CL}	Clamping voltage	
I_{RM}	Leakage current	
I_{PP}	Peak pulse current	
αT	Voltage temperature coefficient	
V_F	Forward voltage drop	
C	Capacitance	
R_d	Dynamic resistance	

Part Numbers	V_{BR}			I_{RM} @ V_{RM}	R_d	αT	C	
	min.	max.	@ I_R					
	V	V	mA	max. μA	V	max. Ω	typ. $10^{-4}/^{\circ}C$	typ. @ 0V pF
ESDA6V1P6	6.1	7.2	1	0.5	3	1.5	4	70
ESDA6V1-5P6								
ESDA14V2BP6	14.2	18	1	1	12	1.5	5.8	25
				0.1	3			
ESDA25-4BP6	25	30	1	1	24	1.7	7.3	22

Figure 4. Peak power dissipation versus initial junction temperature




Figure 5. Peak pulse power versus exponential pulse duration ($T_j \text{ initial} = 25^\circ\text{C}$)




Figure 6. Clamping voltage versus peak pulse current ($T_j \text{ initial} = 25^\circ\text{C}$, rectangular waveform, $t_p = 2.5 \mu\text{s}$)




Figure 7. Junction capacitance versus reverse applied voltage (typical values)




Figure 8. Relative variation of leakage current versus junction temperature (typical values)




Figure 9. Peak forward voltage drop versus peak forward current (typical values)




Figure 10. ESD response @ $V_{pp} = 15$ kV air discharge (ESDA6V1-5P6)






Figure 11. ESD response @ $V_{pp} = 15$ kV air discharge (ESDA25-4BP6)



2 Ordering information scheme




3 Package information

- Epoxy meets UL94, V0

Table 3. SOT-666 Dimensions

Ref.	Dimensions					
	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	0.45		0.60	0.018		0.024
A3	0.08		0.18	0.003		0.007
b	0.17		0.34	0.007		0.013
b1	0.19	0.27	0.34	0.007	0.011	0.013
D	1.50		1.70	0.059		0.067
E	1.50		1.70	0.059		0.067
E1	1.10		1.30	0.043		0.051
e		0.50			0.020	
L1		0.19			0.007	
L2	0.10		0.30	0.004		0.012
L3		0.10			0.004	

Figure 12. SOT-666 Footprint (dimensions in mm)



4 Ordering information

Part Number	Marking	Package	Weight	Base qty	Delivery mode
ESDA6V1P6	B	SOT-666IP	2.9 mg	3000	Tape and reel
ESDA6V1-5P6	C				
ESDA14V2BP6	A	SOT-666			
ESDA25-4BP6	V				

5 Revision history

Date	Revision	Changes
07-Feb-2006	1	ESDA6V1P6, ESDA6V1-5P6 and ESDA14V2BP6: datasheets merged. ECOPACK statement added. Some curves combined.
26-Jun-2006	2	Reformatted to current standards. Modified package information to show both SOT-666 and SOT-666IP.
22-May-2007	3	Added product ESDA25-4BP6

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2007 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com