


TOPJOB® Rail-Mounted Terminal Blocks 1.0 (1.5) mm²/AWG 16 Series 2000

0.14–1.0(1.5) mm² ① AWG 24 – 16 800 V/6 kV/3 600 V, 10 A I _N 13.5 A (18 A) 600 V, 10 A Terminal block width 3.5 mm / 0.137 in 9 – 11 mm / 0.39 in	0.14 – 1.0(1.5) mm² ① AWG 24 – 16 800 V/6 kV/3 600 V, 10 A I _N 13.5 A (18 A) 600 V, 10 A Terminal block width 3.5 mm / 0.137 in 9 – 11 mm / 0.39 in	0.14 – 1.0(1.5) mm² ① AWG 24 – 16 800 V/6 kV/3 600 V, 10 A I _N 13.5 A (18 A) 600 V, 10 A Terminal block width 3.5 mm / 0.137 in 9 – 11 mm / 0.39 in
---	--	--

① can be connected: 0.14 mm² – 1.5 mm² "s+f-st"; can be pushed in directly: 0.5 mm² – 1.5 mm² "s" and 0.5 mm² – 1 mm² "insulated ferrule, 10 mm/0.393 in"



Item no.	Pack-unit pcs	Item no.	Pack-unit pcs	Item no.	Pack-unit pcs
2-conductor through terminal blocks		3-conductor through terminal blocks,		4-conductor through terminal blocks,	
gray 2000-1201	100	gray 2000-1301	100	gray 2000-1401	100
blue 2000-1204	100	blue 2000-1304	100	blue 2000-1404	100
orange 2000-1202	100	orange 2000-1302	100	orange 2000-1402	100
more colors are available		more colors are available		more colors are available	
2-conductor ground (earth) terminal block,		3-conductor ground (earth) terminal block,		4-conductor ground (earth) terminal block,	
green-yellow 2000-1207	100	green-yellow 2000-1307	100	green-yellow 2000-1407	100
② Suitable for Ex i applications		② Suitable for Ex i applications		② Suitable for Ex i applications	

Accessories Appropriate marking systems: **WMB/Marker Strips** (see Full Line Catalog W4, Vol. 1, Sec. 14)

End and intermediate plate, 0.7 mm /0.028 in thick orange 2000-1292 100 (4 x 25) gray 2000-1291 100 (4 x 25)	End and intermediate plate, 0.7 mm /0.028 in thick orange 2000-1392 100 (4 x 25) gray 2000-1391 100 (4 x 25)	End and intermediate plate, 0.7 mm /0.028 in thick orange 2000-1492 100 (4 x 25) gray 2000-1491 100 (4 x 25)
Push-in type jumper bars, light gray, insulated, I_N 14 A 2-way 2000-402 200 (8 x 25) 3-way 2000-403 200 (8 x 25) 4-way 2000-404 200 (8 x 25) 5-way 2000-405 100 (4 x 25) : : 10-way 2000-410 100 (4 x 25)	Push-in type jumper bars, light gray, insulated, I_N 14 A 2-way 2000-402 200 (8 x 25) 3-way 2000-403 200 (8 x 25) 4-way 2000-404 200 (8 x 25) 5-way 2000-405 100 (4 x 25) : : 10-way 2000-410 100 (4 x 25)	Push-in type jumper bars, light gray, insulated, I_N 14 A 2-way 2000-402 200 (8 x 25) 3-way 2000-403 200 (8 x 25) 4-way 2000-404 200 (8 x 25) 5-way 2000-405 100 (4 x 25) : : 10-way 2000-410 100 (4 x 25)
Push-in type jumper bars, light gray, insulated, I_N 14 A 1 - 3 2000-433 200 (8 x 25) 1 - 4 2000-434 200 (8 x 25) 1 - 5 2000-435 100 (4 x 25) : : 1 - 10 2000-440 100 (4 x 25)	Push-in type jumper bars, light gray, insulated, I_N 14 A 1 - 3 2000-433 200 (8 x 25) 1 - 4 2000-434 200 (8 x 25) 1 - 5 2000-435 100 (4 x 25) : : 1 - 10 2000-440 100 (4 x 25)	Push-in type jumper bars, light gray, insulated, I_N 14 A 1 - 3 2000-433 200 (8 x 25) 1 - 4 2000-434 200 (8 x 25) 1 - 5 2000-435 100 (4 x 25) : : 1 - 10 2000-440 100 (4 x 25)
Marker strips, white, plain, on roll for center marking 11 mm/0.039 in wide 50 m 2009-110 1 300 m 2009-130 1	Marker strips, white, plain, on roll for center marking 11 mm/0.039 in wide 50 m 2009-110 1 300 m 2009-130 1	Marker strips, white, plain, on roll for center marking 11 mm/0.039 in wide 50 m 2009-110 1 300 m 2009-130 1

