

PRODUCT SPECIFICATION SHEET

A070/... *Mild Steel Plated Base and Stud Levelling Foot Range*




Materials... *Base and Stud: - Mild Steel, Electroless Nickel Plated*

Part number	Thread Size D1(mm)	Thread Length L(mm)	Base Diameter D2(mm)	Overall Height H(mm)	Max Load (Kg)
A070/001	M12	75	55	105	450
A070/002	M12	125	55	155	450
A070/003	M12	150	55	180	600
A070/095	M14	200	70	239	1000
A070/011	M16	75	70	114	1500
A070/018	M16	125	70	164	1500
A070/006	M16	150	70	189	1500
A070/008	M16	200	70	239	1500
A070/024	M16	200	100	245	2000
A070/020	M20	125	100	177	2000
A070/007	M20	150	100	202	2000
A070/009	M20	200	100	250	2000
A070/028	M24	125	100	181	3000
A070/012	M24	150	100	206	3000
A070/013	M24	200	100	256	3000
A070/029	M24	250	100	306	3000

Dimensions are approximate

Bolt Down Base also Available - See A210...



Registered Design

Options Available

The following options are available on all popular sizes :-

Non-Slip Pad:

Nitrile rubber pad (3mm thick) bonded to the Base.

Vibetech Pad:

Vibration dampening Vibetech pad (6/13mm thick) bonded to the base

Specials:

Stud sizes not listed above can be manufactured as Specials.

For further information Please Contact the office or Email :- sales@nutech-eng.com