

DIN30W24

24V/30W Din Rail Power Supply



■ Features:

- Constant voltage design
- European AC input range
- Protections: Short circuit / Overload / Over voltage / Over temperature
- Cooling by free air convection
 - Isolation class II
- Can be installed on DIN Rail TS-35/7 or 15
 - MTBF 200.000 h

ELECTRICAL SPECIFICATION

SELV

MODEL	DIN30W24					
OUTPUT						
Rated Voltage	24V					
Rated Current	1.25A					
Current Range	0 ÷ 1.25A					
Rated Power	30W					
No Output Voltage (max)	25.2V					
Voltage Adjustment Range [6]	22-28V					
Line Regulation	± 1%					
Load Regulation	± 2%					
Tolerance [3]	± 5%					
Ripple & Noise (max.) [2]	200mVp-p					
Setup,Rise Time [4]	500ms, 65ms / 230VAC at full load					
Hold up Time (typ.)	30ms / 230VAC at full load					
INPUT						
Voltage Range	180 ÷ 264VAC					
Frequency Range	47 ÷ 63Hz					
Inrush current (max.)	40A at 230VAC cold start at 25°C					
Efficiency (typ.)	85.28% - Average (25%+50%+75%+100%)/4					
AC Current (typ.)	0.45A / 230VAC					
Leakage current	<1.5mA at 50/60Hz 240VAC INPUT					
Max. No. Of PSU on Circuit Breaker	B10	B16	C10	C16	D10	D16
	10	16	10	16	21	34
No load Power Consumption (max.)	<0.5W					

DIN30W24

24V/30W Din Rail Power Supply



PROTECTIONS

Over Current	Range 120 ÷ 210% Type: hiccup mode. Recovers automatically after fault condition is removed.
Short Circuit	Type: hiccup mode. Recovers automatically after fault condition is removed.
Over Voltage	36-45V Type: hiccup mode. Recovers automatically after fault condition is removed.
Over Temperature	Range: NTC detect Type: shut down output voltage. Re-power on to recovery.

WORKING ENVIRONMENT

Working Temperature	-20°C ÷ +50°C, ambient derate each output at 4.0% per degree from 50°C to 60°C
Operating humidity	5% to 95% (non-condensing)
Storage Temperature and Humidity	-30°C ÷ +70°C, 5 ÷ 95% RH (non-condensing)

SAFETY and EMC REGULATIONS

Safety Standards	Compliance to EN 62368-1
Withstand Voltage	IN/OUT: 3.75kVAC
EMC Emission	Compliance to EN55032
EMC Immunity	Compliance to EN55035
Harmonic Current	Compliance to EN61000-3-2; EN61000-3-3

OTHERS

Dimensions	62.5 x 93 x 56mm (L x W x H)
Weight and Packing	206g; 50pcs./box; weight box and dimensions: 11kg; 37.05 x 23.6 x 33.5 cm

MECHANICAL SPECIFICATION

PIN ASSIGNMENT

NO.	Assignment
1	Input: AC/N
2	Input: AC/L
3,4	Output: U _{OUT} +
5,6	Output: U _{OUT} -
7	LED indication for power on
8	U _{OUT} adjustment




DIN30W24

24V/30W Din Rail Power Supply



MECHANICAL SPECIFICATION:



1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature.
2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1μF i 47μF parallel capacitor.
3. Tolerance includes set up tolerance, line regulation and load regulation.
4. Setup and rise time is measured from 0 to 90% rated output voltage.
5. Power supply is considered as component not indented to apply by end-user. Power supply meets safety and EMC standards however the final equipment with power supply must be re-quality to comply with EMC Directives.
6. By built-in potentiometer.