International

- Logic-Level Gate Drive
- Advanced Process Technology
- Surface Mount (IRL3803S)
- Low-profile through-hole (IRL3803L)
- 175°C Operating Temperature
- Fast Switching
- Fully Avalanche Rated
- Lead-Free

Description

Fifth Generation HEXFETs from International Rectifier utilize advanced processing techniques to achieve extremely low on-resistance per silicon area. This benefit, combined with the fast switching speed and ruggedized device design that HEXFET Power MOSFETs are well known for, provides the designer with an extremely efficient and reliable device for use in a wide variety of applications.


The D²Pak is a surface mount power package capable of accommodating die sizes up to HEX-4. It provides the highest power capability and the lowest possible on-resistance in any existing surface mount package. The D²Pak is suitable for high current applications because of its low internal connection resistance and can dissipate up to 2.0W in a typical surface mount application.


The through-hole version (IRL3803L) is available for low-profile applications.

Absolute Maximum Ratings

IRL3803SPbF IRL3803LPbF

HEXFET® Power MOSFET





	Parameter	Max.	Units
I _D @ T _C = 25°C	Continuous Drain Current, V _{GS} @ 10V③	140©	
I _D @ T _C = 100°C	Continuous Drain Current, V _{GS} @ 10V®	98©	A
I _{DM}	Pulsed Drain Current 🛈 🕲	470	
P _D @T _A =25°C	Power Dissipation	3.8	W
P _D @T _C = 25°C	Power Dissipation	200	W
	Linear Derating Factor	1.3	W/°C
V _{GS}	Gate-to-Source Voltage	±16	V
E _{AS}	Single Pulse Avalanche Energy@⑤	610	mJ
I _{AR}	Avalanche Current①	71	A
E _{AR}	Repetitive Avalanche Energy®	20	mJ
dv/dt	Peak Diode Recovery dv/dt 30	5.0	V/ns
TJ	Operating Junction and	-55 to + 175	
T _{STG}	Storage Temperature Range		°C
	Soldering Temperature, for 10 seconds	300 (1.6mm from case)	

Thermal Resistance

	Parameter	Тур.	Max.	Units
R _{0JC}	Junction-to-Case		0.75	00044
R _{0JA}	Junction-to-Ambient (PCB Mounted, steady-state)**		40	°C/W

www.irf.com

1

PD-95101A

	Parameter	Min.	Тур.	Max.	Units	Conditions
V _{(BR)DSS}	Drain-to-Source Breakdown Voltage	30			V	V_{GS} = 0V, I_{D} = 250 μ A
$\Delta V_{(BR)DSS}/\Delta T_J$	Breakdown Voltage Temp. Coefficient		0.052		V/°C	Reference to 25°C, I _D = 1mA③
R _{DS(on)}	Static Drain-to-Source On-Resistance			0.006	Ω	V _{GS} = 10V, I _D = 71A ⊕
				0.009		V _{GS} = 4.5V, I _D = 59A ④
V _{GS(th)}	Gate Threshold Voltage	1.0			V	V_{DS} = V_{GS} , I_D = 250 μ A
9fs	Forward Transconductance	55			S	V _{DS} = 25V, I _D = 71A③
1	Drain to Source Leokage Current			25	μA	V_{DS} = 30V, V_{GS} = 0V
DSS	Drain-to-Source Leakage Current			250	μΛ	V_{DS} = 24V, V_{GS} = 0V, T_{J} = 150°C
Icss	Gate-to-Source Forward Leakage Gate-to-Source Reverse Leakage			100	nA	V _{GS} = 16V
				100		V _{GS} = -16V
Qg	Total Gate Charge			140		I _D = 71A
Q _{gs}	Gate-to-Source Charge			41	nC	V _{DS} = 24V
Q _{gd}	Gate-to-Drain ("Miller") Charge			78		V_{GS} = 4.5V, See Fig. 6 and 13 $\circledast \circledast$
t _{d(on)}	Turn-On Delay Time		14			V _{DD} = 15V
t _r	RiseTime		230	——		I _D = 71A
t _{d(off)}	Turn-Off Delay Time		29			R _G = 1.3Ω
t _f	Fall Time		35			R _D = 0.20Ω, See Fig. 10 ⊕ ⑤
Ls	Internal Source Inductance		7.5		nH	Between lead,
-5						and center of die contact
Ciss	Input Capacitance		5000			V _{GS} = 0V
Coss	Output Capacitance		1800		рF	V _{DS} = 25V
Ciss	Reverse Transfer Capacitance		880			f = 1.0MHz, See Fig. 5⊚

Electrical Characteristics @ T_J = 25°C (unless otherwise specified)

Source-Drain Ratings and Characteristics

	Parameter	Min.	Тур.	Max.	Units	Conditions	
s	Continuous Source Current					MOSFET symbol	
	(Body Diode)		140@	140©	А	showing the	
IsM	Pulsed Source Current			470		integral reverse 🖳 🚺 🕇	
	(Body Diode) ①					p-n junction diode.	
V _{SD}	Diode Forward Voltage			1.3	V	T _J = 25°C, I _S = 71A, V _{GS} = 0V ⊕	
t _{rr}	Reverse Recovery Time		120	180	ns	T _J = 25°C, I _F = 71A	
Qrr	Reverse Recovery Charge		450	680	nC	di/dt = 100A/µs ⊕֍	
ton	Forward Turn-On Time	Inti	Intrinsic turn-on time is negligible (turn-on is dominated by ${\sf L}_S{\rm +}{\sf L}_D)$				

Notes:

- ① Repetitive rating; pulse width limited by max. junction temperature. (See fig. 11)
- O V_{DD} = 15V, starting T_J = 25°C, L = 180 μ H R_G = 25 Ω , I_{AS} = 71A. (See Figure 12)
- $\textcircled{3}\ I_{SD} \leq 71 \text{A}, \ di/dt \leq 130 \text{A}/\mu \text{s}, \ V_{DD} \leq V_{(BR)DSS}, \ T_{J} \leq 175^{\circ}\text{C}$
- ③ Uses IRL3803 data and test conditions.
- © Calculated continuous current based on maximum allowable junction temperature;for recommended current-handling of the package refer to Design Tip # 93-4
- ** When mounted on 1" square PCB (FR-4 or G-10 Material).

For recommended footprint and soldering techniques refer to application note #AN-994.






Fig 1. Typical Output Characteristics

Fig 2. Typical Output Characteristics




Fig 3. Typical Transfer Characteristics

Fig 4. Normalized On-Resistance Vs. Temperature

www.irf.com

100

International




Fig 5. Typical Capacitance Vs. Drain-to-Source Voltage




Fig 6. Typical Gate Charge Vs. Gate-to-Source Voltage




Fig 7. Typical Source-Drain Diode Forward Voltage




Fig 8. Maximum Safe Operating Area

International

IRL3803S/LPbF




Fig 11. Maximum Effective Transient Thermal Impedance, Junction-to-Case

International




Fig 12a. Unclamped Inductive Test Circuit




Fig 12b. Unclamped Inductive Waveforms






Fig 13a. Basic Gate Charge Waveform









Fig 13b. Gate Charge Test Circuit

Peak Diode Recovery dv/dt Test Circuit




* V_{GS} = 5V for Logic Level Devices

Fig 14. For N-Channel HEXFETS


International **TOR** Rectifier

D²Pak Package Outline


Dimensions are shown in millimeters (inches)








NOTES:





	FLK JDL	. 111232	DIVILINGIO	NO MIL	WILAGO	INLD /	<u>, i i</u>	1
4.	DIMENSIC	N 61 ANE) c1 APP	LY TO B	ASE M	etal (ONLY	
5.	CONTROL	ling dime	ENSION: I	NCH.				
S Y		DIMEN	SIONS	N				
М В	MILLIM	ETERS	INC	O T				
0 L	MIN.	MAX.	MIN.	MAX.	O T E S			
A	4.06	4,83	.160	.190	Ŭ			
A1	0.00	0.254	.000	.010				
b	0.51	0.99	.020	.039				
ь1	0.51	0.89	.020	.035	4			
b2	1,14	1,78	.045	.070				
с	0.38	0.74	.015	.029				
c1	0.38	0.58	.015	.023	4			
c2	1,14	1.65	.045	.065				
D	8.51	9.65	.335	.380	3			
D1	6.86		.270					
Е	9.65	10.67	.380	.420	3			
E1	6.22		.245					
е	2.54 BSC		.100	BSC				
Н	14.61	15.88	.575	.625				
L	1,78	2.79	.070	.110				
L1		1.65		.065				
L2	1.27	1.78	.050 .070					
L3	0.25 BSC		.010 BSC					
L4	4.78	5.28	.188	.208				
m	17.78		.700					
m1	8.89		.350					
n	11,43		.450					
0	2.08		.082					
р	3,81		.150					
R	0.51	0,71	.020	.028				
Θ	90*	93*	90*	93'				
		II				I		

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994

3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.127 [.005"] PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY.

2. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].

LEAD ASSIGNMENTS

<u>HEXFET</u>

1.- GATE 2, 4.- DRAIN 3.- SOURCE

IGBTs, CoPACK

1.- GATE 2, 4.- COLLECTOR 3.- EMITTER

DIODES

1.- ANODE * 2, 4.- CATHODE 3.- ANODE


* PART DEPENDENT.


International **TOR** Rectifier

IRL3803S/LPbF

TO-262 Package Outline

Dimensions are shown in millimeters (inches)





S Y M		N				
B O	MILLIM	ETERS	INC	N O T E S		
L	MIN.	MAX.	MIN.	MAX.	S	
А	4.06	4.83	.160	.190		
A1	2.03	2.92	.080	.115		
b	0.51	0.99	.020	.039		
b1	0.51	0.89	.020	.035	4	
b2	1.14	1.40	.045	.055		
С	0.38	0.63	.015	.025	4	
c1	1.14	1.40	.045	.055		
c2	0.43	.063	.017	.029		
D	8.51	9.65	.335	.380	3	
D1	5.33		.210			
Е	9.65	10.67	.380	.420	3	
E1	6.22		.245			
е	2.54	BSC	.100	.100 BSC		
L	13.46	14.09	.530	.555		
L1	3.56	3.71	.140	.146		
L2		1.65		.065		

LEAD ASSIGNMENTS <u>HEXFET</u>

2.- DRAIN 3.- SOURCE 4.- DRAIN

S

1.- GATE

I<u>GBT</u> 1 - GATE 2 - COLLECTOR 3 - EMITTER

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994

2. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].


۸.,

3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.127 [.005"] PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY.

A. DIMENSION 61 AND c1 APPLY TO BASE METAL ONLY.

5. CONTROLLING DIMENSION: INCH.


TO-262 Part Marking Information



International **IOR** Rectifier

D²Pak Tape & Reel Information

Dimensions are shown in millimeters (inches)



Data and specifications subject to change without notice.

International

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105 TAC Fax: (310) 252-7903 Visit us at www.irf.com for sales contact information.12/04 10 www.irf.com Note: For the most current drawings please refer to the IR website at: <u>http://www.irf.com/package/</u>

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application. For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.