




CABLE RANGE PG7  
 Ø2,5 - Ø6,5mm



ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	PA	BLACK
2	HOUSING	PA	BLACK
3	CONTACT	BRASS / GOLD	CuZn Ni/ Au
4	PG NUT	PA	BLACK
5	O-RING	VITON	RED
6	GROMMET	CR	BLACK
7	ULTRA-LOCK	BRASS /ST.STEEL	NICKEL PLATED

POL	MATERIAL NO.	ENGINEERING NO.
4	1200850003	WA4006-31
5	1200850004	WA5006-31

**VOLTAGE RATING:** 250 VAC/VDC  
**AMPERAGE RATING:** 4A  
**PROTECTION CLASS:** IP 67/68/69K  
**OPERATING TEMPERATURE:** -25°C / 90°C  
**UL CERTIFICATION:** FILE NO. E152210  
**CSA CERTIFICATIONS:** FILE NO. LR6837

ENTER DESCRIPTION EC NO: WEU2010-0320 DRWN:FPACHER 2009/12/22 CHKD: 2010/02/05 APPR:FPACHER 2010/02/05	DESCRIPTION
	REV
	1

QUALITY SYMBOLS
▽=0
∇=0

GENERAL TOLERANCES (UNLESS SPECIFIED)	
	mm INCH
4 PLACES	± --- ± ---
3 PLACES	± --- ± ---
2 PLACES	± 0.05 ± ---
1 PLACE	± 0.1 ± ---
ANGULAR ± 1 °	

DIMENSION STYLE MM ONLY	
DRAWN BY FPACHER	DATE 2009/12/22
CHECKED BY	DATE
APPROVED BY FPACHER	DATE 2010/02/05
MATERIAL NO.	

SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
TITLE M12U FA MALE STR PG7		
MOLEX INCORPORATED		SHEET NO. 1 OF 1
DOCUMENT NO. SD-120085-001		
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		