Model 72



Features:

- 3/8" square
- Single turn
- Cermet



Electrical

Standard Resistance Range, Ohms	10 to 2Meg
Standard Resistance Tolerance	±10% (<100 Ohms = ±20%)
Input Voltage, Maximum	200 Vdc or rms not to exceed power rating
Slider Current, Maximum	100mA or within rated power, whichever is less
Power Rating, Watts	0.5 at 85°C derating to 0 at 125°C
End Resistance, Maximum	2 Ohms
Actual Electrical Travel, Nominal	244°
Dielectric Strength	900 Vrms
Insulation Resistance, Minimum	1,000 Megohms
Resolution	Essentially infinite
Contact Resistance Variation, Maximum	1% or 1 Ohm, whichever is greater

Environmental

Seal	85°C Fluorinert® (No Leaks)
Temperature Coefficient, Maximum	±100ppm/°C
Operating Temperature Range	−55°C to +125°C
Thermal Shock	5 cycles, -55°C to +125°C (1% ΔRT, 1% ΔVR)
Moisture Resistance	Ten 24 hour cycles (1% Δ RT, IR 100 Megohms Min.)
Shock, 6ms Sawtooth	100G's (1% ΔRT, 1% ΔVR)
Vibration	20G's, 10 to 2,000 Hz (1% ΔRT, 1% ΔVR)
High Temperature Exposure	250 hours at 125°C (2% ΔRT, 2% ΔVR)
Rotational Life	200 cycles (3% ΔRT)
Load Life at 0.5 Watts	1,000 hours at 70°C (2% Δ RT)
Resistance to Solder Heat	260°C for 10 sec. (1% ΔRT)

Mechanical

Mechanical Stops	Solid
Torque, Starting Maximum	3 ozin. (0.021 N-m)
Weight, Nominal	.025 oz. (0.70 grams)

Model 72



Packaging Information

Standard: Boxes

Capacity = 100 Units

Option: Tubes

All units oriented with #1 pin to same side.


	Pin Style		P, PM	X, XL, XW, RW
Magazine	Width	=	0.47"	0.29"
	Height	=	0.54"	0.76"
	Length	=	20.5"	20.1"
	Capacity	=	50 Units	50 Units

Option: Tape & Reel, Ammo Pack (Available only for 72RW only)


All units oriented with #1 pin to the right of the direction of feed.

	Seat Plane to Centerline of Sprocket Hole		.71" (18.03 mm)
Tape	Width	=	18 mm
	Sprocket	=	Single Hole .50" spacing
	Capacity	=	1,000 Units
Reel	Diameter	=	14" (356mm)
Ammo	Tape Fold	=	12" (305mm)
	Box	=	1.8" x 13" x 10" (46mm x 330mm x 254mm)

EXTENDED ROTOR OPTION (Inch/mm)





ADJUSTMENT KNOB OPTION (Inch/mm)








Outline Drawings—Top Adjustment














Model 72



Outline Drawings—Side Adjustment








Model 72



Ordering Information



Standard Resistance Values, Ohms

Circuit Diagram

10	100	1K	10K	50K	250K	2Meg	(2)
20	200	2K	20K	100K	500K	(1)	o—^^/^/ (3)
50	500	5K	25K	200K	1Meg		—→ cw

NOTES Metric equivalents, based on 1 inch = 25.4mm are Merric equivalents, based on a management of significant figures as in the original English units and are provided for general information only.

rances unless otherwise specified: Linear = ± .01 inches (.25mm) Angular = ± 2 degrees



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TT Electronics:

72PMR100K 72PMR10K 72PMR10K 72PMR20K 72PMR20K 72PMR26K 72PR100 72PR100K 72PR10K 72PR10K 72PR10K 72PR10K 72PR20 72PR200 72PR200K 72PR20K 72PMR200 72PMR200K 72PMR250K 72PMR250K 72PMR250K 72PMR250K 72PMR250K 72PMR250K 72PMR250K 72PMR200 72PMR200K 72PMR250K 72PMR250K 72PMR250K 72PMR250K 72PMR200 72PMR200K 72PMR200K 72PMR200K 72PMR200K 72PMR200K 72PMR200K 72PMR200K 72PMR200K 72PMR200K 72PMR20K 72PMR200K 72PMR200K