





- · Universal AC input / Full range
- · Built-in active PFC function
- Energy efficiency Level VI
- · Comply with EISA 2007/DoE, NRCan and EU ErP
- · 125% peak load capability
- · Fanless design, cooling by free air convection
- Protection: Short circuit / Overload / Over voltage / Over temperature
- · 3 years warranty




Applications

- · Land mobile radio system
- Surveillance system
- TV antenna facility

Description

ENP-360 series is a 360W desktop type power supply working perfectly for communication related applications. Observing the standard 7" width size in the land mobile radio field, it provides the most frequently used voltage in the communication field. With the rugged mechanical design along with the high efficiency circuitry, it operates for the ambient temperature range $-30^{\circ}\text{C} \sim +70^{\circ}\text{C}$ under free air convection.

■ Model Encoding






SPECIFICATION

MODEL		ENP-360-12	ENP-360-24	ENP-360-48	
	DC VOLTAGE	13.8V	27.6V	55.2V	
ОИТРИТ	RATED CURRENT	0 ~ 26A	0 ~ 13A	0 ~ 6.5A	
		32.6A	16.3A	8.2A	
	RATED POWER	359W	359W	359W	
		450W	450W	453W	
	RIPPLE & NOISE (max.) Note.2		150mVp-p	350mVp-p	
	VOLTAGE ADJ. RANGE	11.5 ~ 15V	23.5 ~ 30V	47.5 ~ 58.8V	
	VOLTAGE TOLERANCE Note.3		±1.0%	±1.0%	
		±0.5%	±0.5%	±0.5%	
		±2.0%	±1.0%	±0.5%	
		1000ms, 100ms at full load			
	HOLD UP TIME (Typ.)	20ms at full load			
	() . ,	90 ~ 264VAC 127 ~ 370VDC			
INPUT	FREQUENCY RANGE	90 ~ 264 VAC 127 ~ 370 V DC 47 ~ 63 Hz			
	POWER FACTOR (Typ.)	PF>0.98/115VAC, PF>0.95/230VAC at full load			
	EFFICIENCY (Typ.)	91%	93%	94%	
	AC CURRENT (Typ.)	3.8A/115VAC 1.9A/230VAC	9376	34 /6	
	INRUSH CURRENT (Typ.)	COLD START 60A at 230VAC			
	LEAKAGE CURRENT				
	NO LOAD POWER CONSUMPTION	<3.5mA / 240VAC			
	SHORT CIRCUIT				
	SHOKT CIRCUIT	Protection type: Constant current limiting, recovers automatically after fault condition is removed Normally works within 110 ~ 125% rated output power for more than 3 seconds and switches to constant current limiting, with			
	OVERLOAD	auto-recovery after the peak load condition is removed			
PROTECTION	O TENEON D		power, with auto-recovery after the overload condition is removed		
PROTECTION	OVER VOLTAGE	15.5 ~ 18.2V	31 ~ 36.5V	62.1 ~ 72.9V	
		Protection type: Shut down o/p voltage, re-power on to recover			
	OVER TEMPERATURE	Shut down O/P voltage, recovers automatically after temperature goes down			
	WORKING TEMP.	-30 ~ +70°C (Refer to "Derating Curve")			
	WORKING HUMIDITY	20 ~ 95% RH non-condensing			
ENVIRONMENT	STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH			
	TEMP. COEFFICIENT	±0.05%/°C (0~50°C)			
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes			
	SAFETY STANDARDS	UL60950-1 approved			
SAFETY &	WITHSTAND VOLTAGE	I/P-O/P:3KVAC I/P-FG:2KVAC O/P-FG:0.5KVAC			
EMC	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH			
(Note 9)	EMC EMISSION	Compliance to EN55022 (CISPR22) class B, EN61000-3-2,-3, FCC PART 15 / CISPR22 class B			
	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN55024, light industry level, criteria A			
OTHERS	MTBF	147.5K hrs min. MIL-HDBK-217F (25°C	()		
	DIMENSION	192*178*45.5mm (L*W*H)			
	PACKING	1.5Kg; 10pcs/16Kg /1.34CUFT			
NOTE	1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature. 2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. 3. Tolerance: includes set up tolerance, line regulation and load regulation. 4. Line regulation is measured from low line to high line at rated load. 5. Load regulation is measured from 0% to 100% rated load. 6. Length of set up time is measured at cold first start. Turning ON/OFF the power supply very quickly may lead to increase of the set up time. 7. Derating may be needed under low input voltages. Please check the derating curve for more details. 8. Peak current or peak power up to 3 seconds is provided. 9. The power supply is considered as an independent unit, but the final equipment still need to re-confirm that the whole system complies with the EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on http://www.meanwell.com)				




■ Block Diagram




■ Derating Curve


■ Static Characteristics

















Terminal Pin No. Assignment (TB1):

Pin No.	Assignment	
1,2	+V	
3,4	-V	

■ Installation Manual

Please refer to: http://www.meanwell.com/manual.html