

Ultrane Grip & Proof 526

DESCRIPTION AND GENERAL PROPERTIES

- **Material** Nitrile GRIP&PROOF coating
- **Length (cm)** 23-28
- **Wrist** Knitted wrist
- **Colour/Color** Black
- **Interior finish** Seamless textile support
- **Exterior finish** Fully-coated
- **Size / EAN** 7 8 9 10 11
- **Packaging** 1 pair/bag - 12 pairs/bag - 96 pairs/carton
- **Complementary information** Guaranteed DMF free and guaranteed Silicone free on palm and fingers



PERFORMANCE RESULTS

Certification category 2



4121
ISO 13997 :
3.4 N (327 g)

ISO 13997 defines the weight on the blade required to cut in a single movement.

Data was obtained according to ISO 13997, from the average of several measurements. As Individual specimens will obviously have greater or lesser cut resistance than the average, so this result can provide only a general indication of the cut resistance of any protective material.

Legends



MECHANICAL HAZARDS EN 388

PERFORMANCE LEVELS

0-4 0-5 0-4 0-4
Abrasion resistance
Blade cut resistance
Tear resistance
Puncture resistance



LOW CHEMICAL PROTECTION EN 374



MICRO-ORGANISMS EN 374



RADIOACTIVE CONTAMINATION EN 421



SPECIFIC CHEMICAL PROTECTION EN 374

Letter Code	Chemical product
A	Methanol
B	Acetone
C	Acetonitrile
D	Dichloromethane
E	Carbon Disulfide
F	Toluene
G	Diethylamine
H	Tetrahydrofurane
I	Ethyl acetate
J	n-Heptane
K	Sodium hydroxide 40%
L	Sulphuric acid 96%



COLD HAZARDS EN 511

PERFORMANCE LEVELS

0-4 0-4 0 or 1
Convective cold resistance
Contact cold resistance
Water permeability



HEAT AND FIRE EN 407

PERFORMANCE LEVELS

0-4 0-4 0-4 0-4 0-4 0-4
Burning behaviour
Contact heat resistance
Convective heat resistance
Radiant heat resistant
Resistance to small drops of molten metal
Resistance to large quantities of molten metal

For more details: www.mapa-pro.com

Ultrane Grip & Proof 526

DESCRIPTION AND GENERAL PROPERTIES

- Oilproof, fully dipped it repels oil penetration and reduce dermatitis
- Grip and Proof coating ensures an excellent grip in very oily environment . It also reduces muscle strain and boost productivity
- Excellent abrasion resistance due to the nitrile coating
- Unbeatable fingertip.
- Long lasting and cost effective glove: washable, no need to change it so often as oilproof

MAIN FIELDS OF USE

Automotive/mechanical industry

- Mechanical maintenance
- Machining parts using cutting oil
- Handling oily mechanical parts
- Handling and sorting small, sharp parts

Glass industry

- Handling glass sheets

Mechanical industry

- Maintenance in wet environments (water, oil, greases, hydrocarbons)
- Assembly of small oily parts

Local Authorities (Parks and Public Spaces)

- Public park maintenance

INSTRUCTIONS FOR USE

Instructions for use

- It is recommended to check that the gloves are suitable for the intended use, because the conditions of use at workplace may differ from the «CE»-type tests.
- It is not recommended for persons sensitized to dithiocarbamates and to natural latex (wrist with elastic natural rubber).
- Put the gloves on dry, clean hands.
- Ensure the insides of the gloves are dry before putting them on again.

Storage conditions

Store the gloves in their original packaging protected from heat, light and humidity.

Laundering conditions

Wipe gloves contaminated with oil or grease with a dry cloth before removing. Performances of the gloves are guaranteed up to 5 cleaning cycles under the conditions described above: Use of a household or industrial washing machine and a standard liquid detergent, synthetic program temperature 60 ° C and spin drying at 400 rotations per minute. Improper use of the gloves or submitting them to a cleaning or laundering process that is not specifically recommended can alter their performance levels

Drying conditions

Trumble drying at 60°C maximum. Ensure the inside of the gloves is dry before putting them on again

Food contact US

FDA 21CFR 177.2600

LEGISLATION

This product is not classified as hazardous according to the directive 1999/45/EC of the European Parliament and of the Council. This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH)

- CE-Type Examination Certificate
0075/014/162/01/13/0050 ext 02/08/14

- Issued by the notified body nr
0075

C.T.C - 4 rue Hermann Frenkel - 69367 LYON Cedex 07 France