# HLMP-R100, HLMP-0301, HLMP-0401, HLMP-0504

2.5 mm x 7.6 mm Rectangular LED Lamps

# **Data Sheet**





#### Description

The HLMP-R100, -0301, -0401, -0504 are solid state lamps encapsulated in a radial lead rectangular epoxy package. They utilize a tinted, diffused epoxy to provide high on-off contrast and a flat high intensity emitting surface. Borderless package design allows creation of uninterrupted light emitting areas.

The HLMP-R100 uses a double heterojunction (DH) absorbing substrate (AS) aluminum gallium arsenide (AlGaAs) red LED chip in a light red epoxy package. This combination produces outstanding light output over a wide range of drive currents.

The HLMP-0301 has a high efficiency red GaAsP on GaP LED chip in a light red epoxy package.


The HLMP-0401 provides a yellow GaAsP on GaP LED chip in a yellow epoxy package.


The HLMP-0504 provides a green GaP LED chip in a green epoxy package.

# Features

- Rectangular light emitting surface
- Flat high sterance emitting surface
- Stackable on 2.54 mm (0.100 inch) centers
- Ideal as flush mounted panel indicators
- Ideal for backlighting legends
- Long life: solid state reliability
- Choice of 4 bright colors
  - DH AS AlGaAs Red
  - High Efficiency Red
  - Yellow
  - High Performance Green
- IC compatible/low current requirements








- AN EPOXY MENISCUS MAY EXTEND ABOUT 1 mm (0.040") DOWN THE LEADS.
  THERE IS A MXIMUM 1 TAPER FROM
- 3. THERE IS A MXIMUM 1 TAPER FROM BASE TO THE TOP OF LAMP.

#### **Selection Guide**

		Luminous In Iv (mcd) at 2	•
Color	Part Number	Min.	Тур.
DH AlGaAs Red	HLMP-R100	2.1	_
Red	HLMP-0301	2.1	-
	HLMP-0301-C00xx	1.3	-
Yellow	HLMP-0401	3.6	-
	HLMP-0401-B00xx	1.4	-
	HLMP-0401-D00xx	3.6	-
Green	HLMP-0504	2.6	_
	HLMP-0504-B00xx	1.6	-
	HLMP-0504-C00xx	2.6	-

# Part Numbering System



#### Absolute Maximum Ratings at $T_A = 25^{\circ}C$

Parameter	HLMP-R100	HLMP-0301	HLMP-0401	HLMP-0504	Units
Peak Forward Current	300	90	60	90	mA
Average Forward Current <sup>[1]</sup>	20	25	20	25	mA
DC Current <sup>[2]</sup>	30	30	20	30	mA
Power Dissipation	87	135	85	135	mW
Reverse Voltage ( $I_R = 100 \ \mu A$ )	5	5	5	5	V
Transient Forward Current <sup>[3]</sup> (10 μs Pulse)	500	500	500	500	mA
Operating Temperature Range	-20 to +100	-40 to +100	-40 to +100	-20 to +100	°C
Storage Temperature Range	-40 to +100	-40 to +100	-40 to +100	-40 to +100	

Notes:

1. See Figure 5 to establish pulsed operating conditions.

2. For AlGaAs Red, Red, and Green Series derate linearly from 50°C at 0.5 mA/°C. For Yellow Series derate linearly from 50°C at 0.2 mA/°C.

3. The transient peak current is the maximum non-recurring peak current that can be applied to the device without damaging the LED die and wirebond. It is not recommended that the device be operated at peak current beyond the peak forward current listed in the Absolute Maximum Ratings.

## Electrical/Optical Characteristics at $T_A = 25^{\circ}C$

		HLMP-R100		HLMP	P-0301		HLMI	P-0401		HLMP	<b>-0504</b>	04		Test	
Sym. Description	Min.	Тур.	Max.	Min.	Тур.	Max.	Min.	Тур.	Max.	Min.	Тур.	Max.	Units		
2θ <sub>1/2</sub>	Included Angle Between Half Luminous Intensity Points		100			100			100			100		Deg.	Note 1. Fig. 6
λρ	Peak Wavelength		645			635			583			565		nm	Measure- ment at Peak
$\lambda_d$	Dominant Wavelength		637			626			585			569		nm	Note 2.
$\Delta\lambda_{1/2}$	Spectral Line Halfwidth		20			40			36			28		nm	
$\tau_{s}$	Speed of Response		30			90			90			500		ns	
С	Capacitance		30			16			18			18		рF	$V_F = 0;$ f = 1 MHz
Rθ <sub>J-PIN</sub>	Thermal Resistance		260			260			260			260		°C/W	Junction to Cathode Lead
V <sub>F</sub>	Forward Voltage		1.8	2.2		1.9	2.6		2.1	2.6		2.2	3.0	V	l <sub>F</sub> = 20 mA Figure 2.
V <sub>R</sub>	Reverse Breakdown Voltage	5.0			5.0			5.0			5.0			V	I <sub>R</sub> = 100 μA
$\eta_v$	Luminous Efficacy		80			145			500			595		lm/W	Note 3.

Notes:

1.  $\theta_{1/2}$  is the off-axis angle at which the luminous intensity is half the axial luminous intensity.

2. The dominant wavelength,  $\lambda_{d}$ , is derived from the CIE chromaticity diagram and represents the single wavelength which defines the color of the device.

3. Radiant intensity,  $I_e$ , in watts/steradian, may be found from the equation  $I_e = I_v/\eta_v$ , where  $I_v$  is the luminous intensity in candelas and  $\eta_v$  is the luminous efficacy in lumens/watt.




Figure 1. Relative intensity vs. wavelength.




Figure 2. Forward current vs. forward voltage.

 $V_F$  (300 mA) for AlGaAs Red = 2.6 volts typical.




Figure 3. Relative luminous intensity vs. forward current.




Figure 4. Relative efficiency (luminous intensity per unit current) vs. peak current.  $\eta_{v}$  (300 mA) for AlGaAs Red = 0.7.




Figure 5. Maximum tolerable peak current vs. peak duration (IPEAK MAX determined from temperature derated IDC MAX).




Figure 6. Relative luminous intensity vs. angular displacement.

## **Intensity Bin Limits**

## Intensity Bin Limits, continued

Color

Yellow

		Intensity Rang	je (mcd)
Color	Bin	Min.	Max.
ed	С	1.5	2.4
	D	2.4	3.8
	E	3.8	6.1
	F	6.1	9.7
	G	9.7	15.5
	Н	15.5	24.8
	I	24.8	39.6
	J	39.6	63.4
	К	63.4	101.5
	L	101.5	162.4
	Μ	162.4	234.6
	N	234.6	340.0
	0	340.0	540.0
	Р	540.0	850.0
	Q	850.0	1200.0
	R	1200.0	1700.0
	S	1700.0	2400.0
	Т	2400.0	3400.0
	U	3400.0	4900.0
	V	4900.0	7100.0
	W	7100.0	10200.0
	Х	10200.0	14800.0
	Y	14800.0	21400.0
	Z	21400.0	30900.0

Massimasuma	**!***	6	ما ما ما	limit is ±18%.
Maximum	tolerance	ior eac	n bin	111111111111111111111111111111111111

Green

	Intensity Range	e (mcd)
Bin	Min.	Max.
В	1.6	2.5
С	2.5	4.0
D	4.0	6.5
E	6.5	10.3
F	10.3	16.6
G	16.6	26.5
Н	26.5	42.3
I	42.3	67.7
J	67.7	108.2
К	108.2	173.2
L	173.2	250.0
М	250.0	360.0
Ν	360.0	510.0
0	510.0	800.0
Р	800.0	1250.0
Q	1250.0	1800.0
R	1800.0	2900.0
S	2900.0	4700.0
T	4700.0	7200.0
U	7200.0	11700.0
V	11700.0	18000.0
W	18000.0	27000.0
B	1.8	2.9
C	2.9	4.7
D	4.7	7.6
E	7.6	12.0
F	12.0	19.1
G	19.1	30.7
Н	30.7	49.1
Ι	49.1	78.5
J	78.5	125.7
К	125.7	201.1
L	201.1	289.0
Μ	289.0	417.0
Ν	417.0	680.0
0	680.0	1100.0
P	1100.0	1800.0
Q	1800.0	2700.0
R	2700.0	4300.0
S T	4300.0 6800.0	6800.0 10800.0
U	10800.0	16000.0
V	16000.0	25000.0
W	25000.0	40000.0

Maximum tolerance for each bin limit is  $\pm 18\%$ .

## **Color Categories**

		Lambda (nm)	
Color	Category#	Min.	Max.
Green	6	561.5	564.5
	5	564.5	567.5
	4	567.5	570.5
	3	570.5	573.5
	2	573.5	576.5
Yellow	1	582.0	584.5
	3	584.5	587.0
	2	587.0	589.5
	4	589.5	592.0
	5	592.0	593.0

Tolerance for each bin limit is  $\pm 0.5$  nm.

# **Mechanical Option Matrix**

Mechanical Option Code	Definition
00	Bulk Packaging, minimum increment 500 pcs/bag
02	Tape & Reel, straight leads, minimum increment 1300 pcs/reel

Note:

All categories are established for classification of products. Products may not be available in all categories. Please contact your local Avago representative for further clarification/information.

#### Precautions


#### **Lead Forming**

- The leads of an LED lamp may be preformed or cut to length prior to insertion and soldering into PC board.
- If lead forming is required before soldering, care must be taken to avoid any excessive mechanical stress induced to LED package. Otherwise, cut the leads of LED to length after soldering process at room temperature. The solder joint formed will absorb the mechanical stress of the lead cutting from traveling to the LED chip die attach and wirebond.
- It is recommended that tooling made to precisely form and cut the leads to length rather than rely upon hand operation.

#### **Soldering Conditions**

- Care must be taken during PCB assembly and soldering process to prevent damage to LED component.
- The closest LED is allowed to solder on board is 1.59 mm below the body (encapsulant epoxy) for those parts without standoff.
- Recommended soldering conditions:

	Wave Soldering	Manual Solder Dipping
Pre-heat Temperature	105°C Max.	-
Pre-heat Time	30 sec Max.	_
Peak Temperature	250°C Max.	260°C Max.
Dwell Time	3 sec Max.	5 sec Max.



- Wave soldering parameter must be set and maintained according to recommended temperature and dwell time in the solder wave. Customer is advised to periodically check on the soldering profile to ensure the soldering profile used is always conforming to recommended soldering condition.
- If necessary, use fixture to hold the LED component in proper orientation with respect to the PCB during soldering process.
- Proper handling is imperative to avoid excessive thermal stresses to LED components when heated. Therefore, the soldered PCB must be allowed to cool to room temperature, 25°C, before handling.
- Special attention must be given to board fabrication, solder masking, surface plating and lead holes size and component orientation to assure solderability.
- Recommended PC board plated through hole sizes for LED component leads:

LED Component Lead Size	Diagonal	Plated Through Hole Diameter
0.457 x 0.457 mm	0.646 mm	0.976 to 1.078 mm
(0.018 x 0.018 inch)	(0.025 inch)	(0.038 to 0.042 inch)
0.508 x 0.508 mm	0.718 mm	1.049 to 1.150 mm
(0.020 x 0.020 inch)	(0.028 inch)	(0.041 to 0.045 inch)

Note: Refer to application note AN1027 for more information on soldering LED components.

'E Fe	BOTTOM SIDE OF PC BOARD
/ /	CONVEYOR SPEED = 1.83 M/MIN (6 FT/MIN) PREHEAT SETTING = 150°C (100C PCB) SOLDER WAVE TEMPERATURE = 245°C AIR KNIFE AIR TEMPERATURE = 390°C AIR KNIFE DISTANCE = 1.91 mm (0.25 IN.) AIR KNIFE ANGLE = 40 SOLDER: SN63; FLUX: RMA

NOTE: ALLOW FOR BOARDS TO BE SUFFICIENTLY COOLED BEFORE EXERTING MECHANICAL FORCE.

Figure 7. Recommended wave soldering profile

For product information and a complete list of distributors, please go to our web site:

www.avagotech.com

Avago, Avago Technologies, and the A logo are trademarks of Avago Technologies in the United States and other countries. Data subject to change. Copyright © 2005-2015 Avago Technologies. All rights reserved. AV02-1554EN - June 24, 2015



# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Broadcom Limited: <u>HLMP-0301-C0000</u> HLMP-0401-B0000